

## Uni Wall Sconce

10575312



**Uni Wall Mount Sconce: Urban up and down lighting**  
Wall Mounts applies on surface, e.g., parking garages, entrances, outdoor terrace and wall in garden.

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

## Benefits

- Modern streamlined design.
- Multiple mounting option.
- Easy directly mounted over a bracket.

## Applications

- Walkways
- Parks and Plazas
- Outdoor Parking areas

## Versions




Uni Wall Sconce




Uni Wall Sconce

## Dimensional drawing



BWP411 LED WW 220V 40W NB PSU 7012



BWP410 LED NW 220V 40W MB PSU 7012

## General Information

Driver included Yes

## Light Technical

Color rendering index (CRI) 70

## Operating and Electrical

Power Consumption 40 W

## Controls and Dimming

Dimmable No

## Mechanical and Housing

Housing Color Gray

Ingress protection code IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK08 [5 J vandal-protected]

Optical cover type Flat glass

## Approval and Application

CE mark Yes

## Light Technical

| Order Code | Full Product Name                  | Luminous Flux | Correlated Color Temperature (Nom) | Light source color |
|------------|------------------------------------|---------------|------------------------------------|--------------------|
| 61088399   | BWP411 LED WW 220V 40W NB PSU 7012 | 5,000 lm      | 3000 K                             | 730 warm white     |
| 61089099   | BWP411 LED WW 220V 40W MB PSU 7012 | 5,000 lm      | 3000 K                             | 730 warm white     |
| 61091399   | BWP411 LED WW 220V 40W WB PSU 7012 | 5,000 lm      | 3000 K                             | 730 warm white     |
| 61092099   | BWP411 LED NW 220V 40W NB PSU 7012 | 5,400 lm      | 4000 K                             | 740 neutral white  |
| 61093799   | BWP411 LED NW 220V 40W MB PSU 7012 | 5,400 lm      | 4000 K                             | 740 neutral white  |
| 61094499   | BWP411 LED NW 220V 40W WB PSU 7012 | 5,400 lm      | 4000 K                             | 740 neutral white  |
| 61082199   | BWP410 LED WW 220V 40W NB PSU 7012 | 5,000 lm      | 3000 K                             | 730 warm white     |
| 61083899   | BWP410 LED WW 220V 40W MB PSU 7012 | 5,000 lm      | 3000 K                             | 730 warm white     |
| 61084599   | BWP410 LED WW 220V 40W WB PSU 7012 | 5,000 lm      | 3000 K                             | 730 warm white     |
| 61085299   | BWP410 LED NW 220V 40W NB PSU 7012 | 5,400 lm      | 4000 K                             | 740 neutral white  |
| 61086999   | BWP410 LED NW 220V 40W MB PSU 7012 | 5,400 lm      | 4000 K                             | 740 neutral white  |
| 61087699   | BWP410 LED NW 220V 40W WB PSU 7012 | 5,400 lm      | 4000 K                             | 740 neutral white  |