

Uni Wall Sconce

10575312



Uni Wall Mount Sconce: Urban up and down lighting
Wall Mounts applies on surface, e.g. parking garages, entrances, outdoor terrace and wall in garden.

Public areas all seek for the most reliable and professional lighting solutions, e.g. parking areas, entrances, outdoor terrace and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with each scenario, delivering the optimised lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy-efficient and stable choice in the existing wall mounting family.

Benefits

- Modern streamlined design.
- Multiple mounting options.
- Easy direct mounting over a bracket.

Applications

- Walkways
- Parks and squares
- Outdoor Parking areas

Versions




Uni Wall Sconce




Uni Wall Sconce

Dimensional drawing



BWP411 LED NW 220V 40W WB PSU 7012



BWP410 LED WW 220V 40W MB PSU 7012

General Information

Driver included Yes

Light Technical

Colour rendering index (CRI) 70

Operating and Electrical

Power Consumption 40 W

Controls and Dimming

Dimmable No

Mechanical and Housing

Housing Colour Grey

Ingress protection code IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK08 [5 J vandal-protected]

Optical cover type Flat glass

Approval and Application

CE mark Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Colour Temperature (Nom)	Light source colour
911401697308	BWP411 LED WW 220V 40W NB PSU 7012	5,000 lm	3000 K	730 warm white
911401697408	BWP411 LED WW 220V 40W MB PSU 7012	5,000 lm	3000 K	730 warm white
911401697508	BWP411 LED WW 220V 40W WB PSU 7012	5,000 lm	3000 K	730 warm white
911401697608	BWP411 LED NW 220V 40W NB PSU 7012	5,400 lm	4000 K	740 neutral white
911401697708	BWP411 LED NW 220V 40W MB PSU 7012	5,400 lm	4000 K	740 neutral white
911401697808	BWP411 LED NW 220V 40W WB PSU 7012	5,400 lm	4000 K	740 neutral white
911401696708	BWP410 LED WW 220V 40W NB PSU 7012	5,000 lm	3000 K	730 warm white
911401696808	BWP410 LED WW 220V 40W MB PSU 7012	5,000 lm	3000 K	730 warm white
911401696908	BWP410 LED WW 220V 40W WB PSU 7012	5,000 lm	3000 K	730 warm white
911401697008	BWP410 LED NW 220V 40W NB PSU 7012	5,400 lm	4000 K	740 neutral white
911401697108	BWP410 LED NW 220V 40W MB PSU 7012	5,400 lm	4000 K	740 neutral white
911401697208	BWP410 LED NW 220V 40W WB PSU 7012	5,400 lm	4000 K	740 neutral white