



# Stand-alone 3 hours compliant emergency lighting Bulkhead

## Emergency Bulkhead

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Emergency bulkheads EM153C and EM154C offer an easy solution for stand-alone emergency lighting, with maintained/non-maintained mode which leave the choices by customers. The lithium battery (LiFePO4) has many advantages over nickel-based products, as it has a longer lifetime, better discharge behaviors, is produced in a more welfare friendly way and can be recycled.

### Benefits

- Meets European standards for emergency lighting luminaires.
- Lithium based battery type provides longer lifetime, low self discharge and high temperature tolerance.
- Welfare friendly solution versus nickel-based products as the battery can be recycled.

### Features


- Maintained and Non-Maintained Emergency lighting
- 3 hours emergency lighting
- Manual and Self-Test options
- IP65

### Application

- Exit and Emergency
- Offices
- Retail
- Hospitality
- Manufacturing

## Emergency Bulkhead

### Dimensional drawing



# Emergency Bulkhead

| General Information   |                 |
|---|-----------------|
| Driver included   | Yes             |
| Lamp family code  | -               |
| Number of gear units  | Unit            |
| Light Technical   |                 |
| Correlated Colour Temperature (Nom)                           | 6500 K          |
| Colour rendering index (CRI)                                  | >80             |
| Optic type  | -               |
| Operating and Electrical                                      |                 |
| Protection class IEC  | Safety class II |
| Input Voltage   | 220-240 V       |
| Line Frequency  | 50 Hz           |
| Suitable for random switching                                 | Not applicable  |
| Controls and Dimming  |                 |
| Dimmable  | No              |
| Embedded control  | -               |
| Maximum dim level   | Not applicable  |
| Mechanical and Housing  |                 |
| Optical cover type  | -               |
| Housing Colour  | White           |
| Ingress protection code                                       | IP65            |
| Emergency Operation   |                 |
| Central Emergency   | No              |
| Rated duration of the emergency lighting (when fully charged) | 3 h             |
| Approval and Application                                      |                 |
| CE mark   | Yes             |
| ENEC mark   | -               |
| Flammability mark   | -               |
| Glow-wire test  | -               |
| Initial Performance (IEC Compliant)                           |                 |
| Initial chromaticity  | 0.33            |
| Luminous flux tolerance                                       | +/-5%           |

## Light Technical

| Order Code | Full Product Name                   | Luminous efficacy (rated) (nom.) | Upwards light |
|------------|-------------------------------------|----------------------------------|---------------|
|            |                                     | Luminous Flux                    | output ratio  |
| 79894900   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | 50 lm/W                          | 150 lm 0.77   |
| 79895600   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | 50 lm/W                          | 150 lm 0.77   |
| 79896300   | EM154C HO BKD 15S NM3 ELP IP65      | 176 lm/W                         | 1,587 lm 6.82 |
| 79897000   | EM154C HO BKD 15S NM3 ELP IP65      | 176 lm/W                         | 1,587 lm 6.82 |

## Operating and Electrical

| Order Code | Full Product Name                   | Power Consumption |
|------------|-------------------------------------|-------------------|
| 79894900   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | 4 W               |
| 79895600   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | 4 W               |

| Order Code | Full Product Name              | Power Consumption |
|------------|--------------------------------|-------------------|
| 79896300   | EM154C HO BKD 15S NM3 ELP IP65 | 10 W              |
| 79897000   | EM154C HO BKD 15S NM3 ELP IP65 | 10 W              |

## Mechanical and Housing

| Order Code | Full Product Name                   | Mech. impact protection code |
|------------|-------------------------------------|------------------------------|
| 79894900   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | IK06                         |
| 79895600   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | IK06                         |

| Order Code | Full Product Name              | Mech. impact protection code |
|------------|--------------------------------|------------------------------|
| 79896300   | EM154C HO BKD 15S NM3 ELP IP65 | IK08                         |
| 79897000   | EM154C HO BKD 15S NM3 ELP IP65 | IK08                         |

# Emergency Bulkhead

## Emergency Operation

| Order Code | Full Product Name                   | Emergency lighting                                | Emergency flux |
|------------|-------------------------------------|---|----------------|
| 79894900   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | Emergency lighting 3-hour duration Pro version    | 175 lm         |
| 79895600   | EM153C SM BKD EXIT SIGN M3 ELB IP65 | Emergency lighting 3-hours duration basic version | 175 lm         |

| Order Code | Full Product Name              | Emergency lighting                                | Emergency flux |
|------------|--------------------------------|---|----------------|
| 79896300   | EM154C HO BKD 15S NM3 ELP IP65 | Emergency lighting 3-hour duration Pro version    | 1,587 lm       |
| 79897000   | EM154C HO BKD 15S NM3 ELB IP65 | Emergency lighting 3-hours duration basic version | 1,587 lm       |

## Approval and Application

| Order Code | Full Product Name                   | Ambient temperature range |
|------------|-------------------------------------|---------------------------|
| 79894900   | EM153C SM BKD EXIT SIGN M3 ELP IP65 | +5 to +40 °C              |
| 79895600   | EM153C SM BKD EXIT SIGN M3 ELB IP65 | +5 to +40 °C              |

| Order Code | Full Product Name              | Ambient temperature range |
|------------|--------------------------------|---------------------------|
| 79896300   | EM154C HO BKD 15S NM3 ELP IP65 | +5 to +45 °C              |
| 79897000   | EM154C HO BKD 15S NM3 ELB IP65 | +5 to +45 °C              |

