



Essential: The remarkable and truly circular lighting solution

Philips Essential is a functional pendant mount round luminaire with a wide range of color and textures, which can seamlessly blend into any decor, while meeting office lighting requirements. It can be connected to other systems to create a smart office lighting solution with integrated sensors to avoid a 'sensor acne' in your beautifully designed ceilings. This family is available in 3 sizes and can be mounted in 3 different ways. Philips Essential is made from recycled materials, 3D printed carbon neutral, making it a conscious choice for those looking to contribute to a circular economy. So, choose this lighting solution without compromising on style, performance, functionality, or sustainability.

Benefits

- Fabric-inspired textures & colors to match interior styles and to meet design requirements
- Low weight and easy to install
- Save electricity costs with high efficiency
- Office compliant with UGR19 versions
- Clean & beautiful ceilings with integrated sensing options for daylight control, presence detection and more.
- Suitable for various project needs

Applications

- Offices
- Healthcare
- Hospitality
- Retail

Features

- A wide range of colors and textures
- 3 sizes and 3 mounting types (pendant, surface and recessed)


- Includes VPC option for easy installation and perfect rimless ceiling integration
- Efficacy up to 152 lm/W
- DALI or wireless drivers with Interact ready
- Printed parts with at least 55% recycled or mass balanced bio-circular material
- Luminous flux 900 - 8000 lm
- Lifetime 100,000hrs to L80
- Integrated Sensor option with presence detection and day light dimming

Versions



Essential Suspended RTP

Dimensional drawing



TCBRMP 19S/940 DIA OC WH401T102 WH

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Luminous Flux	1,890 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	123 lm/W
Color rendering index (CRI)	>90
Beam angle of light source	90 degree(s)
Optic type	Beam angle 90°

Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Power Consumption	15.4 W
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38, 0.38) SDCM < 3

Product Data

Product family code	TCBRPS [Essential Pendant Surface]
---------------------	------------------------------------