

PHILIPS

Lighting



Essential: The remarkable and truly circular lighting solution

Essential Surface

Philips Essential is a functional surface mount round luminaire with a wide range of color and textures, which can seamlessly blend into any decor, while meeting office lighting requirements. It can be connected to other systems to create a smart office lighting solution with integrated sensors to avoid a 'sensor acne' in your beautifully designed ceilings. This family is available in 3 sizes and can be mounted in 3 different ways. Philips Essential is made from recycled materials, 3D printed carbon neutral, making it a conscious choice for those looking to contribute to a circular economy. So, choose this lighting solution without compromising on style, performance, functionality, or sustainability.

Benefits

- Fabric-inspired textures & colors to match interior styles and to meet design requirements
- Low weight and easy to install
- Save electricity costs with high efficiency
- Office compliant with UGR19 versions
- Clean & beautiful ceilings with integrated sensing options for daylight control, presence detection and more.
- Suitable for various project needs

Essential Surface

Features

- A wide range of colors and textures
- 3 sizes and 3 mounting types (pendant, surface and recessed)
- Includes VPC option for easy installation and perfect rimless ceiling integration
- Efficacy up to 152 lm/W
- DALI or wireless drivers with Interact ready
- Printed parts with at least 55% recycled or mass balanced bio-circular material
- Luminous flux 900 - 8000 lm
- Lifetime 100,000hrs to L80
- Integrated Sensor option with presence detection and day light dimming

Application

- Offices
- Healthcare
- Hospitality
- Retail

Versions







Essential Surface RTP



Essential Surface RTP

Dimensional drawing



Essential Surface

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Beam angle of light source	90 degree(s)
Color rendering index (CRI)	>90
Optic type	Beam angle 90°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK04
Ingress protection code	IP20
Emergency Operation	
Central Emergency	No
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
912500108723	TCBRLS 46S/930 DIA OC WH401T102	3000 K	128 lm/W	4,416 lm
912500108724	TCBRLS 46S/940 DIA OC WH401T102	4000 K	133 lm/W	4,600 lm
912500108727	TCBRMS 19S/930 DIA OC WH401T102	3000 K	118 lm/W	1,817 lm
912500108728	TCBRMS 19S/940 DIA OC WH401T102	4000 K	123 lm/W	1,890 lm
912500108781	TCBRMS 19S/930 IA5 OC WH401T102	3000 K	118 lm/W	1,817 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
912500108723	TCBRLS 46S/930 DIA OC WH401T102	34.5 W	No
912500108724	TCBRLS 46S/940 DIA OC WH401T102	34.5 W	No
912500108727	TCBRMS 19S/930 DIA OC WH401T102	15.4 W	No
912500108728	TCBRMS 19S/940 DIA OC WH401T102	15.4 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
912500108781	TCBRMS 19S/930 IA5 OC WH401T102	15.4 W	Yes (relates to presence/ movement detection and daylight harvesting)

Controls and Dimming

Essential Surface

Order Code	Full Product Name	Embedded control
912500108723	TCBRLS 46S/930 DIA OC WH401T102	-
912500108724	TCBRLS 46S/940 DIA OC WH401T102	-
912500108727	TCBRMS 19S/930 DIA OC WH401T102	-

Order Code	Full Product Name	Embedded control
912500108728	TCBRMS 19S/940 DIA OC WH401T102	-
912500108781	TCBRMS 19S/930 IA5 OC WH401T102	Interact SC1500 Multi-sensor bundle

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
912500108723	TCBRLS 46S/930 DIA OC WH401T102	(0.44, 0.40) SDCM < 3
912500108724	TCBRLS 46S/940 DIA OC WH401T102	(0.38, 0.38) SDCM < 3
912500108727	TCBRMS 19S/930 DIA OC WH401T102	(0.44, 0.40) SDCM < 3

Order Code	Full Product Name	Initial chromaticity
912500108728	TCBRMS 19S/940 DIA OC WH401T102	(0.38, 0.38) SDCM < 3
912500108781	TCBRMS 19S/930 IA5 OC WH401T102	(0.44, 0.40) SDCM < 3

