



# **GentleSpace – High-quality, efficient lighting engineered for excellence in tough environments**

## **GentleSpace gen4**

GentleSpace gen4 is the ultimate lighting solution for industrial settings and indoor sports facilities. It exceeds expectations by ensuring superior light quality, improving employee safety and productivity, and complying with all the relevant safety regulations. Engineered for longevity, GentleSpace gen4 reduces the frequency, hassle, and costs of maintenance, making it ideal for high-ceiling installations. Its energy-efficient design cuts operational expenses, offering maximum application efficiency and an attractive total cost of ownership (TCO). This product range offers a wide variety of optics, beam angles (from very narrow to wide), lumen packages, and connectivity options. With GentleSpace gen4 you can easily create a tailor-made lighting solution for every high-ceiling application. Its modern, flat design makes it easier to install, clean, and maintain. The single optical window design provides superior visual performance. A variety of mounting possibilities and connectors, like the pre-mounted IP65 connector, enable quick and easy installation. The robust design allows it to withstand harsh conditions in all sorts of environments. You can choose between various cover materials, including specialized variants for extreme temperatures (XT), hazardous areas (ATEX 2/22), and sports applications. Additionally, GentleSpace gen4 offers advanced connectivity options. It's ready to use in connected lighting systems like Interact. Reliable, high-efficiency lighting with smart connectivity – a bright choice for a better future. Embrace sustainability with GentleSpace gen4, the highbay lighting solution that complies with the principles of the circular economy by prioritising durability and recyclability. The luminaire is serviceable, with all the information available at your fingertips via the Signify Service tag app. Whether you are looking

## GentleSpace gen4

for a reliable "fit and forget" solution or one that can be adapted and controlled after installation, GentleSpace gen4 is the right choice for you.

### Benefits

- Robust design, created to withstand harsh conditions in all sorts of environments
- Compact product architecture, resistant to high impact (IK08), water, and dust (IP65)
- Excellent light uniformity and low glare for optimised working conditions with improved safety and greater visual comfort
- Attractive total cost of ownership thanks to its high luminous efficacy (up to 189 lm/W), long lifetime (100,000 hours @L85), and optimized lighting plan that requires fewer luminaires per application
- Easy installation. Single-piece, lighter architecture (approximately 20% lighter than the previous generation) with multiple mounting options for flexible installation in various environments and conditions
- Interact Ready connectivity for smart lighting. Connect to the cloud and discover additional ways to save energy through optimised efficiency, motion sensing and daylight harvesting, as well as improved lighting management, productivity and safety
- Engineered with sustainability in mind. Meets lighting for circularity criteria to help you achieve your sustainability goals

### Features

- Exceptional performance with UltraEfficient (UE, 189 lm/W) and High-Efficiency (HE, 183 lm/W) versions
- Long service life of 100,000 hours at L85
- High water (IP65) and impact protection (IK08)
- Wide variety of optics (wide beam/medium beam/narrow beam/extrnarrow beam/high-rack/asymmetrical)
- Special options for a broad range of applications: Extreme version (XT) up to 70°C, Safety Class I or II, swimming pool protected version (SWP), marine protection (MSP), VDE certified ball-proof (BP) option, ATEX 2/22 certified version. Tested against a broad list of chemical substances that may be present in industrial settings
- Detachable mounting system for easy installation, including various mounting options and connectors (IP65 pre-mounted connector, or fly-wire cable)
- Robust, die-cast aluminum housing with efficient thermal management and flat front and rear design for easy installation, cleaning, and maintenance
- Single LED module design for superior light quality
- Access to the Signify Service tag app with service and maintenance information

### Application

- Manufacturing sites (from food and beverage to heavy industry)
- Warehouses and logistics centres
- Indoor sports facilities, swimming pools, and exhibition halls

# GentleSpace gen4

## Versions



GentleSpace gen4-large, suspension







GentleSpace gen4-large, wall-bracket

## Dimensional drawing

BY580X suspended






BY581X suspended




With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

BY581P, BY583P Wallmounted bracket




7005 Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

BY581P, BY583P suspended



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

General Information	
Driver included	Yes
Number of gear units	Unit
Light Technical	
Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Colour	Silver
Ingress protection code	IP65
Emergency Operation	
Central Emergency	No
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on easily flammable surfaces
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

## General Information

Order Code	Full Product Name	Service Tag
58952000	BY581P 700S/840 DIA HE WB GC SI BR	Yes
59393000	BY580X 170S/840 SIA WB GC SI H4	Yes
59395400	BY581X 350S/840 SIA WB GC SI H4	Yes
59396100	BY580X 130S/840 SIA HE WB GC SI H4	Yes
59398500	BY581X 250S/840 SIA HE WB GC SI H4	Yes
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	Yes
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	-
59411100	BY581P 250S/840 PSU HE WB GC SI	Yes
59417300	BY581P 350S/840 DIA WB GC SI	Yes
59431900	BY581P 250S/840 DIA WB GC SI ELD3	Yes
58915500	BY581P 250S/840 DIA HE XNB GC SI	-
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	-

## Light Technical

Order Code	Full Product Name	Luminous efficacy (rated)		
		(nom.)	Flux	Optic type
58952000	BY581P 700S/840 DIA HE WB GC SI BR	177 lm/W	70,000 lm	Wide beam
59393000	BY580X 170S/840 SIA WB GC SI H4	167 lm/W	17,000 lm	Wide beam
59395400	BY581X 350S/840 SIA WB GC SI H4	167 lm/W	35,000 lm	Wide beam
59396100	BY580X 130S/840 SIA HE WB GC SI H4	178 lm/W	13,000 lm	Wide beam
59398500	BY581X 250S/840 SIA HE WB GC SI H4	184 lm/W	25,000 lm	Wide beam
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	184 lm/W	25,000 lm	Wide beam

Order Code	Full Product Name	Luminous efficacy (rated)		
		(nom.)	Flux	Optic type
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	176 lm/W	25,000 lm	Assymmetric beam angle
59411100	BY581P 250S/840 PSU HE WB GC SI	184 lm/W	25,000 lm	Wide beam
59417300	BY581P 350S/840 DIA WB GC SI	167 lm/W	35,000 lm	Wide beam
59431900	BY581P 250S/840 DIA WB GC SI ELD3	174 lm/W	25,000 lm	Wide beam
58915500	BY581P 250S/840 DIA HE XNB GC SI	181 lm/W	25,000 lm	Narrow beam
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	177 lm/W	35,000 lm	Wide beam

## Operating and Electrical

## GentleSpace gen4

Order Code	Full Product Name	Power Consumption	Suitable for random switching
58952000	BY581P 700S/840 DIA HE WB GC SI BR	397 W	No
59393000	BY580X 170S/840 SIA WB GC SI H4	102 W	Yes (relates to presence/movement detection and daylight harvesting)
59395400	BY581X 350S/840 SIA WB GC SI H4	210 W	Yes (relates to presence/movement detection and daylight harvesting)
59396100	BY580X 130S/840 SIA HE WB GC SI H4	73 W	Yes (relates to presence/movement detection and daylight harvesting)
59398500	BY581X 250S/840 SIA HE WB GC SI H4	136 W	Yes (relates to presence/movement

Order Code	Full Product Name	Power Consumption	Suitable for random switching
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	136 W	detection and daylight harvesting)
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	142 W	Yes (relates to presence/movement detection and daylight harvesting)
59411100	BY581P 250S/840 PSU HE WB GC SI	136 W	No
59417300	BY581P 350S/840 DIA WB GC SI	210 W	No
59431900	BY581P 250S/840 DIA WB GC SI ELD3	144 W	No
58915500	BY581P 250S/840 DIA HE XNB GC SI	138 W	No
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	198 W	No

### Controls and Dimming

Order Code	Full Product Name	Embedded control	Maximum dim level
58952000	BY581P 700S/840 DIA HE WB GC SI BR	Yes	-
59393000	BY580X 170S/840 SIA WB GC SI H4	Yes	Sensor SNH (R) 210
59395400	BY581X 350S/840 SIA WB GC SI H4	Yes	Sensor SNH (R) 210
59396100	BY580X 130S/840 SIA HE WB GC SI H4	Yes	Sensor SNH (R) 210
59398500	BY581X 250S/840 SIA HE WB GC SI H4	Yes	Sensor SNH (R) 210
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	Yes	Sensor SNH (R) 210

Order Code	Full Product Name	Embedded control	Maximum dim level
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	Yes	-
59411100	BY581P 250S/840 PSU HE WB GC SI	No	-
59417300	BY581P 350S/840 DIA WB GC SI	Yes	-
59431900	BY581P 250S/840 DIA WB GC SI ELD3	Yes	-
58915500	BY581P 250S/840 DIA HE XNB GC SI	Yes	-
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	Yes	-

### Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code
58952000	BY581P 700S/840 DIA HE WB GC SI BR	IK07
59393000	BY580X 170S/840 SIA WB GC SI H4	IK03
59395400	BY581X 350S/840 SIA WB GC SI H4	IK03
59396100	BY580X 130S/840 SIA HE WB GC SI H4	IK03
59398500	BY581X 250S/840 SIA HE WB GC SI H4	IK03
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	IK03

Order Code	Full Product Name	Mech. impact protection code
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	IK07
59411100	BY581P 250S/840 PSU HE WB GC SI	IK07
59417300	BY581P 350S/840 DIA WB GC SI	IK07
59431900	BY581P 250S/840 DIA WB GC SI ELD3	IK07
58915500	BY581P 250S/840 DIA HE XNB GC SI	IK07
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	IK07

### Emergency Operation (1/2)

Order Code	Full Product Name	Power consumption during Central emergency				
		Emergency lighting	Emergency flux	lighting battery	DC emergency mode	
58952000	BY581P 700S/840 DIA HE WB GC SI BR	-	-	-	-	
59393000	BY580X 170S/840 SIA WB GC SI H4	-	-	-	-	
59395400	BY581X 350S/840 SIA WB GC SI H4	-	-	-	-	
59396100	BY580X 130S/840 SIA HE WB GC SI H4	-	-	-	-	
59398500	BY581X 250S/840 SIA HE WB GC SI H4	-	-	-	-	
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	Emergency lighting 3 hours	850 lm	Lithium	5 W	

Order Code	Full Product Name	Power consumption during Central emergency				
		Emergency lighting	Emergency flux	lighting battery	DC emergency mode	
		Wireless Interface				
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	-	-	-	-	
59411100	BY581P 250S/840 PSU HE WB GC SI	-	-	-	-	
59417300	BY581P 350S/840 DIA WB GC SI	-	-	-	-	
59431900	BY581P 250S/840 DIA WB GC SI ELD3	Emergency lighting 3 hours	850 lm	Lithium	5 W	
58915500	BY581P 250S/840 DIA HE XNB GC SI	-	-	-	-	
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	-	-	-	-	

## Emergency Operation (2/2)

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)		
58952000	BY581P 700S/840 DIA HE WB GC SI BR	-		
59393000	BY580X 170S/840 SIA WB GC SI H4	-		
59395400	BY581X 350S/840 SIA WB GC SI H4	-		
59396100	BY580X 130S/840 SIA HE WB GC SI H4	-		
59398500	BY581X 250S/840 SIA HE WB GC SI H4	-		
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	3 h		

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)		
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	-		
59411100	BY581P 250S/840 PSU HE WB GC SI	-		
59417300	BY581P 350S/840 DIA WB GC SI	-		
59431900	BY581P 250S/840 DIA WB GC SI ELD3	3 h		
58915500	BY581P 250S/840 DIA HE XNB GC SI	-		
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	-		

## Approval and Application

Order Code	Full Product Name	Ambient temperature		Flickering	
		Name	range	Glow-wire test	(PstLM) Stroboscopic effect
58952000	BY581P 700S/840	-30 to +55 °C	Temperature	0.22	0.01
			650 °C, duration		
			30 s		

Order Code	Full Product Name	Ambient temperature		Flickering	
		Name	range	Glow-wire test	(PstLM) Stroboscopic effect
		DIA HE WB			
		GC SI BR			

# GentleSpace gen4

Order	Full Product	Ambient		Flickering	
		temperature	value	Stroboscopic	value
Code	Name	range	Glow-wire test	(PstLM)	Stroboscopic
59393000	BY580X	-30 to +55 °C	Temperature	1	0.4
	170S/840		650 °C, duration		
	SIA WB GC SI		30 s		
	H4				
59395400	BY581X	-30 to +55 °C	Temperature	1	0.4
	350S/840		650 °C, duration		
	SIA WB GC SI		30 s		
	H4				
59396100	BY580X	-30 to +55 °C	Temperature	1	0.4
	130S/840		650 °C, duration		
	SIA HE WB		30 s		
	GC SI H4				
59398500	BY581X	-30 to +55 °C	Temperature	1	0.4
	250S/840		650 °C, duration		
	SIA HE WB		30 s		
	GC SI H4				
59407400	BY581X	0°C to 25°C	Temperature	1	0.4
	250S/840		850 °C, duration		
	SIA HE WB		30 s		
	GC SI ELW3				
	H4				
58907000	BY581P	-30 to +55 °C	Temperature	0.12	0.07
	250S/840		650 °C, duration		
	DIA HE		30 s		
	ASYM GC SI				
	MBW				

Order	Full Product	Ambient		Flickering	
		temperature	value	Stroboscopic	value
Code	Name	range	Glow-wire test	(PstLM)	Stroboscopic
59411100	BY581P	-30 to +55 °C	Temperature	0.04	0.07
	250S/840		650 °C, duration		
	PSU HE WB		30 s		
	GC SI				
59417300	BY581P	-30 to +55 °C	Temperature	0.22	0.01
	350S/840		650 °C, duration		
	DIA WB GC		30 s		
	SI				
59431900	BY581P	0°C to 25°C	Temperature	0.12	0.07
	250S/840		850 °C, duration		
	DIA WB GC		30 s		
	SI ELD3				
58915500	BY581P	-30 to +55 °C	Temperature	0.12	0.07
	250S/840		650 °C, duration		
	DIA HE XNB		30 s		
	GC SI				
58931500	BY581P	-30°C to 55°C	Temperature	0.22	0.01
	350S/840		650 °C, duration		
	DIA HE WB		30 s		
	GC SI XT 1m				

## Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
58952000	BY581P 700S/840 DIA HE WB GC SI BR	(0.383, 0.377) SDCM 3
59393000	BY580X 170S/840 SIA WB GC SI H4	(0.380, 0.375) SDCM 3
59395400	BY581X 350S/840 SIA WB GC SI H4	(0.380, 0.375) SDCM 3
59396100	BY580X 130S/840 SIA HE WB GC SI H4	(0.383, 0.377) SDCM 3
59398500	BY581X 250S/840 SIA HE WB GC SI H4	(0.383, 0.377) SDCM 3
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	(0.383, 0.377) SDCM 3


Order Code	Full Product Name	Initial chromaticity
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	(0.383, 0.377) SDCM 3
59411100	BY581P 250S/840 PSU HE WB GC SI	(0.383, 0.377) SDCM 3
59417300	BY581P 350S/840 DIA WB GC SI	(0.380, 0.375) SDCM 3
59431900	BY581P 250S/840 DIA WB GC SI ELD3	(0.380, 0.375) SDCM 3
58915500	BY581P 250S/840 DIA HE XNB GC SI	(0.383, 0.377) SDCM 3
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	(0.383, 0.377) SDCM 3

## Product Data


Order Code	Full Product Name	Product family code
58952000	BY581P 700S/840 DIA HE WB GC SI BR	BY581P
59393000	BY580X 170S/840 SIA WB GC SI H4	BY580X
59395400	BY581X 350S/840 SIA WB GC SI H4	BY581X
59396100	BY580X 130S/840 SIA HE WB GC SI H4	BY580X
59398500	BY581X 250S/840 SIA HE WB GC SI H4	BY581X
59407400	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	BY581X

Order Code	Full Product Name	Product family code
58907000	BY581P 250S/840 DIA HE ASYM GC SI MBW	BY581P
59411100	BY581P 250S/840 PSU HE WB GC SI	BY581P
59417300	BY581P 350S/840 DIA WB GC SI	BY581P
59431900	BY581P 250S/840 DIA WB GC SI ELD3	BY581P
58915500	BY581P 250S/840 DIA HE XNB GC SI	BY581P
58931500	BY581P 350S/840 DIA HE WB GC SI XT 1m	BY581P


## Polar Wide Diagrams




Polar Normal (separate) - BY580PI -  
910505102895




Polar Normal (separate) - BY580PI -  
910505102881




Polar Normal (separate) - BY580PI -  
910505102857




Polar Normal (separate) - BY580PI -  
910505102875




Polar Normal (separate) - BY580PI -  
910505102871




Polar Normal (separate) - BY580PI -  
910505102862



Polar Normal (separate) - BY580PI -  
910505102921




Polar Normal (separate) - BY580PI -  
910505102859




Polar Normal (separate) - BY580PI -  
910505102860


## Polar Wide Diagrams



Polar Normal (separate) - BY580PI -  
910505102937



Polar Normal (separate) - BY580PI -  
910505102913



Polar Normal (separate) - null - 910505102956

