



GentleSpace – High-quality, efficient lighting engineered for excellence in tough environments

GentleSpace gen4 is the ultimate lighting solution for industrial settings and indoor sports facilities. It exceeds expectations by ensuring superior light quality, improving employee safety and productivity, and complying with all the relevant safety regulations. Engineered for longevity, GentleSpace gen4 reduces the frequency, hassle, and costs of maintenance, making it ideal for high-ceiling installations. Its energy-efficient design cuts operational expenses, offering maximum application efficiency and an attractive total cost of ownership (TCO). This product range offers a wide variety of optics, beam angles (from very narrow to wide), lumen packages, and connectivity options. With GentleSpace gen4 you can easily create a tailor-made lighting solution for every high-ceiling application. Its modern, flat design makes it easier to install, clean, and maintain. The single optical window design provides superior visual performance. A variety of mounting possibilities and connectors, like the pre-mounted IP65 connector, enable quick and easy installation. The robust design

allows to withstand harsh conditions in all sorts of environments. You can choose between various cover materials, including specialized variants for extreme temperatures (XT), hazardous areas (ATEX 2/22), and sports applications. Additionally, GentleSpace gen4 offers advanced connectivity options. It's ready to use in connected lighting systems like Interact. Reliable, high-efficiency lighting with smart connectivity – a bright choice for a better future. Embrace sustainability with GentleSpace gen4, the highbay lighting solution that complies with the principles of the circular economy by prioritizing durability and recyclability. The luminaire is serviceable, with all the information available at your fingertips via the Signify Service tag app. Whether you are looking for a reliable “fit and forget” solution or one that can be adapted and controlled after installation, GentleSpace gen4 is the right choice for you.

Benefits

- Robust design, created to withstand harsh conditions in all sorts of environments
- Compact product architecture, resistant to high impact (IK08), water, and dust (IP65)
- Excellent light uniformity and low glare for optimized working conditions with improved safety and greater visual comfort
- Attractive total cost of ownership thanks to its high luminous efficacy (up to 189 lm/W), long lifetime (100,000 hours @L85), and optimized lighting plan that requires fewer luminaires per application
- Easy installation. Single-piece, lighter architecture (approximately 20% lighter than the previous generation) with multiple mounting options for flexible installation in various environments and conditions
- Interact Ready connectivity for smart lighting. Connect to the cloud and discover additional ways to save energy through optimized efficiency, motion sensing and daylight harvesting, as well as improved lighting management, productivity, and safety
- Engineered with sustainability in mind. Meets lighting for circularity criteria to help you achieve your sustainability goals

Applications

- Manufacturing sites (from food and beverage to heavy industry)
- Warehouses and logistics centers
- Indoor sports facilities, swimming pools, and exhibition halls

Features

- Exceptional performance with UltraEfficient (UE, 189 lm/W) and High-Efficiency (HE, 183 lm/W) versions
- Long service life of 100,000 hours at L85
- High water (IP65) and impact protection (IK08)
- Wide variety of optics (wide beam/medium beam/narrow beam/extra narrow beam/high-rack/asymmetrical)
- Special options for a broad range of applications: Extreme version (XT) up to 70°C, Safety Class I or II, swimming pool protected version (SWP), marine protection (MSP), VDE certified ball-proof (BP) option, ATEX 2/22 certified version. Tested against a broad list of chemical substances that may be present in industrial settings
- Detachable mounting system for easy installation, including various mounting options and connectors (IP65 pre-mounted connector, or fly-wire cable)
- Robust, die-cast aluminum housing with efficient thermal management and flat front and rear design for easy installation, cleaning, and maintenance
- Single LED module design for superior light quality
- Access to the Signify Service tag app with service and maintenance information

Versions



GentleSpace gen4-large,
suspension



GentleSpace gen4-large,
bracket, Interact ready



GentleSpace gen4-large,
suspension, Interact ready



GentleSpace gen4-small,
bracket, Interact ready



GentleSpace gen4-large, wall-
bracket



GentleSpace gen4-small,
suspension



GentleSpace gen4-small,
bracket



GentleSpace gen4-large,
bracket



GentleSpace gen4



GentleSpace gen4-small, wall-
bracket




GentleSpace gen4-large,
suspension



GentleSpace gen4, Interact
Ready

Dimensional drawing


BY580X suspended



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY580X 170S/840 SIA WB GC SI H4


700s suspended



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY581P 700S/840 DIA HE WB GC SI


BY581X suspended



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY581X 250S/840 SIA HE WB GC SI ELW3 H4


BY580P, BY582P suspended



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY580P 170S/840 DIA MB GC SI


BY581P, BY583P Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY581P 250S/840 DIA HEWBGCSICHEMMBW1mCW5


BY580P, BY582P Wallmounted bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY580P 170S/840 DIA HE ASYM GC SI MBW


BY580P, BY582P Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY580P 170S/840 DIA HE WB GC SI BR


BY581X Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY581X 250S/840 SIA WB GC SI H4 BR


BY580X Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY580X 170S/840 SIA HE WB GC SI H4 BR


BY581P, BY583P Wallmounted bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY581P 250S/840 DIA HE ASYM GC SI MBW


700S Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY581P 700S/840 DIA WB GC SI BR


BY581P, BY583P suspended




With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m. or 2m

BY581P 250S/840 DIA MB GC SI

Product details



GentleSpace gen4-large,
suspension



GentleSpace gen4-small,
suspension

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Beam angle of light source	10 or 24 degree(s)
----------------------------	--------------------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Controls and Dimming

Maximum dim level	10%
Embedded control	Sensor SNH (R) 210

Mechanical and Housing

Housing Color	Silver
Impact resistance for specific applications	Ball-proof/ball-impact resistant lighting
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Explosion hazard class	Zone 2 and 22

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	No
Type of emergency lighting battery	Lithium

Approval and Application

Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505102953	BY581P 700S/840 DIA WB GC SI	70,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102954	BY581P 700S/840 DIA HE WB GC SI	70,000 lm	4000 K	177 lm/W	>80	Wide beam
910505102955	BY581P 700S/840 DIA WB GC SI BR	70,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	70,000 lm	4000 K	177 lm/W	>80	Wide beam
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	25,000 lm	4000 K	184 lm/W	>80	Wide beam
910505102858	BY581X 250S/840 SIA WB GC SI H4	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102859	BY581X 350S/840 SIA WB GC SI H4	35,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	25,000 lm	4000 K	184 lm/W	>80	Wide beam
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	35,000 lm	4000 K	177 lm/W	>80	Wide beam
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	25,000 lm	4000 K	184 lm/W	>80	Wide beam
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	25,000 lm	4000 K	184 lm/W	>80	Wide beam
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	17,000 lm	4000 K	167 lm/W	>80	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505104565	BY581P 250S/840 DIA HEWBGCSICHEMMBW1mCW5	25,000 lm	4000 K	181 lm/W	>80	Wide beam
910505102872	BY580P 170S/840 PSU WB GC SI	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102874	BY580P 170S/840 PSU HE WB GC SI	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505102876	BY580P 100S/840 DIA UE WB GC SI	10,000 lm	4000 K	182 lm/W	>80	Wide beam
910505102878	BY580P 130S/840 DIA WB GC SI	13,000 lm	4000 K	171 lm/W	>80	Wide beam
910505102879	BY580P 170S/840 DIA WB GC SI	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102882	BY580P 130S/840 DIA HE WB GC SI	13,000 lm	4000 K	178 lm/W	>80	Wide beam
910505102883	BY580P 170S/840 DIA HE WB GC SI	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505102886	BY580P 170S/840 DIA WB PC SI	17,000 lm	4000 K	155 lm/W	>80	Wide beam
910505102890	BY580P 170S/840 DIA HE WB PC SI	17,000 lm	4000 K	164 lm/W	>80	Wide beam
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505102898	BY580P 130S/840 DIA MB GC SI	13,000 lm	4000 K	169 lm/W	>80	Medium beam
910505102899	BY580P 170S/840 DIA MB GC SI	17,000 lm	4000 K	164 lm/W	>80	Medium beam
910505102903	BY580P 130S/840 DIA HE MB GC SI	13,000 lm	4000 K	178 lm/W	>80	Medium beam
910505102904	BY580P 170S/840 DIA HE MB GC SI	17,000 lm	4000 K	174 lm/W	>80	Medium beam
910505102914	BY580P 170S/840 DIA NB GC SI	17,000 lm	4000 K	164 lm/W	>80	Narrow beam
910505102916	BY580P 170S/840 DIA HE NB GC SI	17,000 lm	4000 K	174 lm/W	>80	Narrow beam
910505102918	BY580P 170S/840 DIA XNB GC SI	17,000 lm	4000 K	164 lm/W	>80	Narrow beam
910505102920	BY580P 170S/840 DIA HE XNB GC SI	17,000 lm	4000 K	174 lm/W	>80	Narrow beam
910505102922	BY580P 170S/840 DIA HRO GC SI	17,000 lm	4000 K	164 lm/W	>80	High-rack optic
910505102924	BY580P 170S/840 DIA HE HRO GC SI	17,000 lm	4000 K	174 lm/W	>80	High-rack optic
910505102926	BY580P 170S/865 DIA WB GC SI	17,000 lm	6500 K	164 lm/W	>80	Wide beam
910505102928	BY580P 170S/865 DIA HE WB GC SI	17,000 lm	6500 K	172 lm/W	>80	Wide beam
910505102930	BY580P 170S/830 DIA WB GC SI	17,000 lm	3000 K	155 lm/W	>80	Wide beam
910505102932	BY580P 170S/830 DIA HE WB GC SI	17,000 lm	3000 K	159 lm/W	>80	Wide beam
910505102934	BY580P 170S/940 DIA WB GC SI	17,000 lm	4000 K	157 lm/W	>90	Wide beam
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505104558	BY580X 170S/840 SIA WB GC SI IA9	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	17,000 lm	4000 K	157 lm/W	>80	Assymetric Beam angle
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	17,000 lm	4000 K	170 lm/W	>80	Assymetric Beam angle
910505102889	BY581P 250S/840 DIA WB GC SI BR	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	25,000 lm	4000 K	181 lm/W	>80	Wide beam
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	25,000 lm	4000 K	165 lm/W	>80	Assymetric Beam angle

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	25,000 lm	4000 K	176 lm/W	>80	Assymetric Beam angle
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	25,000 lm	4000 K	165 lm/W	>80	Assymetric Beam angle
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	25,000 lm	4000 K	176 lm/W	>80	Assymetric Beam angle
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	35,000 lm	4000 K	177 lm/W	>80	Wide beam
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	25,000 lm	4000 K	181 lm/W	>80	Wide beam
910505104553	BY581P 250S/840 PSD WB GC II SI BR	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505104563	BY581P 250S/840 DIA HE WBGCSICHEMBR1mCW5	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102888	BY580P 170S/840 DIA WB GC SI BR	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	17,000 lm	4000 K	170 lm/W	>80	Assymetric Beam angle
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505104562	BY580P 170S/840 DIA HE WBGCSICHEMBR1mCW5	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505104564	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5	17,000 lm	4000 K	175 lm/W	>80	Wide beam
910505102873	BY581P 250S/840 PSU WB GC SI	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102875	BY581P 250S/840 PSU HE WB GC SI	25,000 lm	4000 K	184 lm/W	>80	Wide beam
910505102877	BY581P 200S/840 DIA UE WB GC SI	20,000 lm	4000 K	189 lm/W	>80	Wide beam
910505102880	BY581P 250S/840 DIA WB GC SI	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102881	BY581P 350S/840 DIA WB GC SI	35,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102884	BY581P 250S/840 DIA HE WB GC SI	25,000 lm	4000 K	181 lm/W	>80	Wide beam
910505102885	BY581P 350S/840 DIA HE WB GC SI	35,000 lm	4000 K	177 lm/W	>80	Wide beam
910505102887	BY581P 250S/840 DIA WB PC SI	25,000 lm	4000 K	162 lm/W	>80	Wide beam
910505102891	BY581P 250S/840 DIA HE WB PC SI	25,000 lm	4000 K	171 lm/W	>80	Wide beam
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	25,000 lm	4000 K	181 lm/W	>80	Wide beam
910505102901	BY581P 250S/840 DIA MB GC SI	25,000 lm	4000 K	171 lm/W	>80	Medium beam
910505102902	BY581P 350S/840 DIA MB GC SI	35,000 lm	4000 K	167 lm/W	>80	Medium beam
910505102905	BY581P 250S/840 DIA HE MB GC SI	25,000 lm	4000 K	181 lm/W	>80	Medium beam
910505102906	BY581P 350S/840 DIA HE MB GC SI	35,000 lm	4000 K	175 lm/W	>80	Medium beam
910505102915	BY581P 250S/840 DIA NB GC SI	25,000 lm	4000 K	171 lm/W	>80	Narrow beam
910505102917	BY581P 250S/840 DIA HE NB GC SI	25,000 lm	4000 K	181 lm/W	>80	Narrow beam
910505102919	BY581P 250S/840 DIA XNB GC SI	25,000 lm	4000 K	171 lm/W	>80	Narrow beam
910505102921	BY581P 250S/840 DIA HE XNB GC SI	25,000 lm	4000 K	181 lm/W	>80	Narrow beam
910505102923	BY581P 250S/840 DIA HRO GC SI	25,000 lm	4000 K	171 lm/W	>80	High-rack optic
910505102925	BY581P 250S/840 DIA HE HRO GC SI	25,000 lm	4000 K	181 lm/W	>80	High-rack optic
910505102927	BY581P 250S/865 DIA WB GC SI	25,000 lm	6500 K	171 lm/W	>80	Wide beam
910505102929	BY581P 250S/865 DIA HE WB GC SI	25,000 lm	6500 K	179 lm/W	>80	Wide beam
910505102931	BY581P 250S/830 DIA WB GC SI	25,000 lm	3000 K	162 lm/W	>80	Wide beam
910505102933	BY581P 250S/830 DIA HE WB GC SI	25,000 lm	3000 K	171 lm/W	>80	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficiency (rated) (Nom)	Color rendering index (CRI)	Optic type
910505102935	BY581P 250S/940 DIA WB GC SI	25,000 lm	4000 K	165 lm/W	>90	Wide beam
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	25,000 lm	4000 K	181 lm/W	>80	Wide beam
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	35,000 lm	4000 K	177 lm/W	>80	Wide beam
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	25,000 lm	4000 K	174 lm/W	>80	Wide beam
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	25,000 lm	4000 K	181 lm/W	>80	Wide beam
910505102856	BY580X 130S/840 SIA WB GC SI H4	13,000 lm	4000 K	171 lm/W	>80	Wide beam
910505102857	BY580X 170S/840 SIA WB GC SI H4	17,000 lm	4000 K	167 lm/W	>80	Wide beam
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	13,000 lm	4000 K	178 lm/W	>80	Wide beam
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	17,000 lm	4000 K	175 lm/W	>80	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching	Protection class IEC
910505102953	BY581P 700S/840 DIA WB GC SI	420 W	No	Safety class I
910505102954	BY581P 700S/840 DIA HE WB GC SI	397 W	No	Safety class I
910505102955	BY581P 700S/840 DIA WB GC SI BR	420 W	No	Safety class I
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	397 W	No	Safety class I
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	144 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	136 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102858	BY581X 250S/840 SIA WB GC SI H4	144 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102859	BY581X 350S/840 SIA WB GC SI H4	210 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	136 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	198 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	144 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	144 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	136 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	136 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	102 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	97 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505104565	BY581P 250S/840 DIA HEWBGCSICHEMMBW1mCW5	138 W	No	Safety class I
910505102872	BY580P 170S/840 PSU WB GC SI	102 W	No	Safety class I
910505102874	BY580P 170S/840 PSU HE WB GC SI	97 W	No	Safety class I

Order Code	Full Product Name	Power Consumption	Suitable for random switching	Protection class IEC
910505102876	BY580P 100S/840 DIA UE WB GC SI	55 W	No	Safety class I
910505102878	BY580P 130S/840 DIA WB GC SI	76 W	No	Safety class I
910505102879	BY580P 170S/840 DIA WB GC SI	102 W	No	Safety class I
910505102882	BY580P 130S/840 DIA HE WB GC SI	73 W	No	Safety class I
910505102883	BY580P 170S/840 DIA HE WB GC SI	97 W	No	Safety class I
910505102886	BY580P 170S/840 DIA WB PC SI	110 W	No	Safety class I
910505102890	BY580P 170S/840 DIA HE WB PC SI	104 W	No	Safety class I
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	102 W	No	Safety class I
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	97 W	No	Safety class I
910505102898	BY580P 130S/840 DIA MB GC SI	77 W	No	Safety class I
910505102899	BY580P 170S/840 DIA MB GC SI	104 W	No	Safety class I
910505102903	BY580P 130S/840 DIA HE MB GC SI	73 W	No	Safety class I
910505102904	BY580P 170S/840 DIA HE MB GC SI	98 W	No	Safety class I
910505102914	BY580P 170S/840 DIA NB GC SI	104 W	No	Safety class I
910505102916	BY580P 170S/840 DIA HE NB GC SI	98 W	No	Safety class I
910505102918	BY580P 170S/840 DIA XNB GC SI	104 W	No	Safety class I
910505102920	BY580P 170S/840 DIA HE XNB GC SI	98 W	No	Safety class I
910505102922	BY580P 170S/840 DIA HRO GC SI	104 W	No	Safety class I
910505102924	BY580P 170S/840 DIA HE HRO GC SI	98 W	No	Safety class I
910505102926	BY580P 170S/865 DIA WB GC SI	104 W	No	Safety class I
910505102928	BY580P 170S/865 DIA HE WB GC SI	99 W	No	Safety class I
910505102930	BY580P 170S/830 DIA WB GC SI	110 W	No	Safety class I
910505102932	BY580P 170S/830 DIA HE WB GC SI	104 W	No	Safety class I
910505102934	BY580P 170S/940 DIA WB GC SI	108 W	No	Safety class I
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	102 W	No	Safety class I
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	102 W	No	Safety class I
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	102 W	No	Safety class I
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	97 W	No	Safety class I
910505104558	BY580X 170S/840 SIA WB GC SI IA9	102 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	108 W	No	Safety class I
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	100 W	No	Safety class I
910505102889	BY581P 250S/840 DIA WB GC SI BR	144 W	No	Safety class I
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	138 W	No	Safety class I
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	152 W	No	Safety class I
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	142 W	No	Safety class I
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	152 W	No	Safety class I
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	142 W	No	Safety class I
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	198 W	No	Safety class I
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	138 W	No	Safety class I
910505104553	BY581P 250S/840 PSD WB GC II SI BR	144 W	No	Safety class II
910505104563	BY581P 250S/840 DIA HE WBGCSICHEMBR1mCW5	144 W	No	Safety class I
910505102888	BY580P 170S/840 DIA WB GC SI BR	102 W	No	Safety class I

Order Code	Full Product Name	Power Consumption	Suitable for random switching	Protection class IEC
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	97 W	No	Safety class I
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	100 W	No	Safety class I
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	97 W	No	Safety class I
910505104562	BY580P 170S/840 DIA HE WBGCSICHEMBR1mCW5	102 W	No	Safety class I
910505104564	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5	97 W	No	Safety class I
910505102873	BY581P 250S/840 PSU WB GC SI	144 W	No	Safety class I
910505102875	BY581P 250S/840 PSU HE WB GC SI	136 W	No	Safety class I
910505102877	BY581P 200S/840 DIA UE WB GC SI	106 W	No	Safety class I
910505102880	BY581P 250S/840 DIA WB GC SI	144 W	No	Safety class I
910505102881	BY581P 350S/840 DIA WB GC SI	210 W	No	Safety class I
910505102884	BY581P 250S/840 DIA HE WB GC SI	138 W	No	Safety class I
910505102885	BY581P 350S/840 DIA HE WB GC SI	198 W	No	Safety class I
910505102887	BY581P 250S/840 DIA WB PC SI	154 W	No	Safety class I
910505102891	BY581P 250S/840 DIA HE WB PC SI	146 W	No	Safety class I
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	144 W	No	Safety class I
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	138 W	No	Safety class I
910505102901	BY581P 250S/840 DIA MB GC SI	146 W	No	Safety class I
910505102902	BY581P 350S/840 DIA MB GC SI	210 W	No	Safety class I
910505102905	BY581P 250S/840 DIA HE MB GC SI	138 W	No	Safety class I
910505102906	BY581P 350S/840 DIA HE MB GC SI	200 W	No	Safety class I
910505102915	BY581P 250S/840 DIA NB GC SI	146 W	No	Safety class I
910505102917	BY581P 250S/840 DIA HE NB GC SI	138 W	No	Safety class I
910505102919	BY581P 250S/840 DIA XNB GC SI	146 W	No	Safety class I
910505102921	BY581P 250S/840 DIA HE XNB GC SI	138 W	No	Safety class I
910505102923	BY581P 250S/840 DIA HRO GC SI	146 W	No	Safety class I
910505102925	BY581P 250S/840 DIA HE HRO GC SI	138 W	No	Safety class I
910505102927	BY581P 250S/865 DIA WB GC SI	146 W	No	Safety class I
910505102929	BY581P 250S/865 DIA HE WB GC SI	140 W	No	Safety class I
910505102931	BY581P 250S/830 DIA WB GC SI	154 W	No	Safety class I
910505102933	BY581P 250S/830 DIA HE WB GC SI	146 W	No	Safety class I
910505102935	BY581P 250S/940 DIA WB GC SI	152 W	No	Safety class I
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	138 W	No	Safety class I
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	198 W	No	Safety class I
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	144 W	No	Safety class I
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	144 W	No	Safety class I
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	138 W	No	Safety class I
910505102856	BY580X 130S/840 SIA WB GC SI H4	76 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102857	BY580X 170S/840 SIA WB GC SI H4	102 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	73 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	97 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class I

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505102953	BY581P 700S/840 DIA WB GC SI	Yes
910505102954	BY581P 700S/840 DIA HE WB GC SI	Yes
910505102955	BY581P 700S/840 DIA WB GC SI BR	Yes
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	Yes
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	Yes
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	Yes
910505102858	BY581X 250S/840 SIA WB GC SI H4	Yes
910505102859	BY581X 350S/840 SIA WB GC SI H4	Yes
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	Yes
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	Yes
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	Yes
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	Yes
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	Yes
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	Yes
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	Yes
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	Yes
910505104565	BY581P 250S/840 DIA HEWBGCSICHEMMBW1mCW5	Yes
910505102872	BY580P 170S/840 PSU WB GC SI	No
910505102874	BY580P 170S/840 PSU HE WB GC SI	No
910505102876	BY580P 100S/840 DIA UE WB GC SI	Yes
910505102878	BY580P 130S/840 DIA WB GC SI	Yes
910505102879	BY580P 170S/840 DIA WB GC SI	Yes
910505102882	BY580P 130S/840 DIA HE WB GC SI	Yes
910505102883	BY580P 170S/840 DIA HE WB GC SI	Yes
910505102886	BY580P 170S/840 DIA WB PC SI	Yes
910505102890	BY580P 170S/840 DIA HE WB PC SI	Yes
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	Yes
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	Yes
910505102898	BY580P 130S/840 DIA MB GC SI	Yes
910505102899	BY580P 170S/840 DIA MB GC SI	Yes
910505102903	BY580P 130S/840 DIA HE MB GC SI	Yes
910505102904	BY580P 170S/840 DIA HE MB GC SI	Yes
910505102914	BY580P 170S/840 DIA NB GC SI	Yes
910505102916	BY580P 170S/840 DIA HE NB GC SI	Yes
910505102918	BY580P 170S/840 DIA XNB GC SI	Yes
910505102920	BY580P 170S/840 DIA HE XNB GC SI	Yes
910505102922	BY580P 170S/840 DIA HRO GC SI	Yes
910505102924	BY580P 170S/840 DIA HE HRO GC SI	Yes
910505102926	BY580P 170S/865 DIA WB GC SI	Yes
910505102928	BY580P 170S/865 DIA HE WB GC SI	Yes
910505102930	BY580P 170S/830 DIA WB GC SI	Yes

Order Code	Full Product Name	Dimmable
910505102932	BY580P 170S/830 DIA HE WB GC SI	Yes
910505102934	BY580P 170S/940 DIA WB GC SI	Yes
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	Yes
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	Yes
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	Yes
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	Yes
910505104558	BY580X 170S/840 SIA WB GC SI IA9	Yes
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	Yes
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	Yes
910505102889	BY581P 250S/840 DIA WB GC SI BR	Yes
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	Yes
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	Yes
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	Yes
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	Yes
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	Yes
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	Yes
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	Yes
910505104553	BY581P 250S/840 PSD WB GC II SI BR	Yes
910505104563	BY581P 250S/840 DIA HE WBGCSICHEMBR1mCW5	Yes
910505102888	BY580P 170S/840 DIA WB GC SI BR	Yes
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	Yes
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	Yes
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	Yes
910505104562	BY580P 170S/840 DIA HE WBGCSICHEMBR1mCW5	Yes
910505104564	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5	Yes
910505102873	BY581P 250S/840 PSU WB GC SI	No
910505102875	BY581P 250S/840 PSU HE WB GC SI	No
910505102877	BY581P 200S/840 DIA UE WB GC SI	Yes
910505102880	BY581P 250S/840 DIA WB GC SI	Yes
910505102881	BY581P 350S/840 DIA WB GC SI	Yes
910505102884	BY581P 250S/840 DIA HE WB GC SI	Yes
910505102885	BY581P 350S/840 DIA HE WB GC SI	Yes
910505102887	BY581P 250S/840 DIA WB PC SI	Yes
910505102891	BY581P 250S/840 DIA HE WB PC SI	Yes
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	Yes
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	Yes
910505102901	BY581P 250S/840 DIA MB GC SI	Yes
910505102902	BY581P 350S/840 DIA MB GC SI	Yes
910505102905	BY581P 250S/840 DIA HE MB GC SI	Yes
910505102906	BY581P 350S/840 DIA HE MB GC SI	Yes
910505102915	BY581P 250S/840 DIA NB GC SI	Yes
910505102917	BY581P 250S/840 DIA HE NB GC SI	Yes

Order Code	Full Product Name	Dimmable
910505102919	BY581P 250S/840 DIA XNB GC SI	Yes
910505102921	BY581P 250S/840 DIA HE XNB GC SI	Yes
910505102923	BY581P 250S/840 DIA HRO GC SI	Yes
910505102925	BY581P 250S/840 DIA HE HRO GC SI	Yes
910505102927	BY581P 250S/865 DIA WB GC SI	Yes
910505102929	BY581P 250S/865 DIA HE WB GC SI	Yes
910505102931	BY581P 250S/830 DIA WB GC SI	Yes
910505102933	BY581P 250S/830 DIA HE WB GC SI	Yes
910505102935	BY581P 250S/940 DIA WB GC SI	Yes
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	Yes
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	Yes
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	Yes
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	Yes
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	Yes
910505102856	BY580X 130S/840 SIA WB GC SI H4	Yes
910505102857	BY580X 170S/840 SIA WB GC SI H4	Yes
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	Yes
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	Yes

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code
910505102953	BY581P 700S/840 DIA WB GC SI	IK07
910505102954	BY581P 700S/840 DIA HE WB GC SI	IK07
910505102955	BY581P 700S/840 DIA WB GC SI BR	IK07
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	IK07
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	IK03
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	IK03
910505102858	BY581X 250S/840 SIA WB GC SI H4	IK03
910505102859	BY581X 350S/840 SIA WB GC SI H4	IK03
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	IK03
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	IK03
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	IK03
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	IK03
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	IK03
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	IK03
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	IK03
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	IK03
910505104565	BY581P 250S/840 DIA HEWBGC SICHEMMBW1mCW5	IK07
910505102872	BY580P 170S/840 PSU WB GC SI	IK07
910505102874	BY580P 170S/840 PSU HE WB GC SI	IK07
910505102876	BY580P 100S/840 DIA UE WB GC SI	IK07
910505102878	BY580P 130S/840 DIA WB GC SI	IK07

Order Code	Full Product Name	Mech. impact protection code
910505102879	BY580P 170S/840 DIA WB GC SI	IK07
910505102882	BY580P 130S/840 DIA HE WB GC SI	IK07
910505102883	BY580P 170S/840 DIA HE WB GC SI	IK07
910505102886	BY580P 170S/840 DIA WB PC SI	IK07
910505102890	BY580P 170S/840 DIA HE WB PC SI	IK07
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	IK07
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	IK07
910505102898	BY580P 130S/840 DIA MB GC SI	IK07
910505102899	BY580P 170S/840 DIA MB GC SI	IK07
910505102903	BY580P 130S/840 DIA HE MB GC SI	IK07
910505102904	BY580P 170S/840 DIA HE MB GC SI	IK07
910505102914	BY580P 170S/840 DIA NB GC SI	IK07
910505102916	BY580P 170S/840 DIA HE NB GC SI	IK07
910505102918	BY580P 170S/840 DIA XNB GC SI	IK07
910505102920	BY580P 170S/840 DIA HE XNB GC SI	IK07
910505102922	BY580P 170S/840 DIA HRO GC SI	IK07
910505102924	BY580P 170S/840 DIA HE HRO GC SI	IK07
910505102926	BY580P 170S/865 DIA WB GC SI	IK07
910505102928	BY580P 170S/865 DIA HE WB GC SI	IK07
910505102930	BY580P 170S/830 DIA WB GC SI	IK07
910505102932	BY580P 170S/830 DIA HE WB GC SI	IK07
910505102934	BY580P 170S/940 DIA WB GC SI	IK07
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	IK07
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	IK07
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	IK07
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	IK07
910505104558	BY580X 170S/840 SIA WB GC SI IA9	IK03
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	IK07
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	IK07
910505102889	BY581P 250S/840 DIA WB GC SI BR	IK07
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	IK07
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	IK07
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	IK07
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	IK07
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	IK07
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	IK07
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	IK07
910505104553	BY581P 250S/840 PSD WB GC II SI BR	IK07
910505104563	BY581P 250S/840 DIA HE WBGCICHEMBR1mCW5	IK07
910505102888	BY580P 170S/840 DIA WB GC SI BR	IK07
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	IK07
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	IK07

Order Code	Full Product Name	Mech. impact protection code
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	IK07
910505104562	BY580P 170S/840 DIA HE WBGCSCHEMBR1mCW5	IK07
910505104564	BY580P 170S/840 DIA HEWBGCSCHEMMBW1mCW5	IK07
910505102873	BY581P 250S/840 PSU WB GC SI	IK07
910505102875	BY581P 250S/840 PSU HE WB GC SI	IK07
910505102877	BY581P 200S/840 DIA UE WB GC SI	IK07
910505102880	BY581P 250S/840 DIA WB GC SI	IK07
910505102881	BY581P 350S/840 DIA WB GC SI	IK07
910505102884	BY581P 250S/840 DIA HE WB GC SI	IK07
910505102885	BY581P 350S/840 DIA HE WB GC SI	IK07
910505102887	BY581P 250S/840 DIA WB PC SI	IK07
910505102891	BY581P 250S/840 DIA HE WB PC SI	IK07
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	IK07
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	IK07
910505102901	BY581P 250S/840 DIA MB GC SI	IK07
910505102902	BY581P 350S/840 DIA MB GC SI	IK07
910505102905	BY581P 250S/840 DIA HE MB GC SI	IK07
910505102906	BY581P 350S/840 DIA HE MB GC SI	IK07
910505102915	BY581P 250S/840 DIA NB GC SI	IK07
910505102917	BY581P 250S/840 DIA HE NB GC SI	IK07
910505102919	BY581P 250S/840 DIA XNB GC SI	IK07
910505102921	BY581P 250S/840 DIA HE XNB GC SI	IK07
910505102923	BY581P 250S/840 DIA HRO GC SI	IK07
910505102925	BY581P 250S/840 DIA HE HRO GC SI	IK07
910505102927	BY581P 250S/865 DIA WB GC SI	IK07
910505102929	BY581P 250S/865 DIA HE WB GC SI	IK07
910505102931	BY581P 250S/830 DIA WB GC SI	IK07
910505102933	BY581P 250S/830 DIA HE WB GC SI	IK07
910505102935	BY581P 250S/940 DIA WB GC SI	IK07
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	IK07
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	IK07
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	IK07
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	IK07
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	IK07
910505102856	BY580X 130S/840 SIA WB GC SI H4	IK03
910505102857	BY580X 170S/840 SIA WB GC SI H4	IK03
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	IK03
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	IK03

Emergency Operation

Order Code	Full Product Name	Emergency flux	Power consumption during Central DC emergency mode	Emergency lighting
910505102953	BY581P 700S/840 DIA WB GC SI	-	-	-
910505102954	BY581P 700S/840 DIA HE WB GC SI	-	-	-
910505102955	BY581P 700S/840 DIA WB GC SI BR	-	-	-
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	-	-	-
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	-	-	-
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	-	-	-
910505102858	BY581X 250S/840 SIA WB GC SI H4	-	-	-
910505102859	BY581X 350S/840 SIA WB GC SI H4	-	-	-
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	-	-	-
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	-	-	-
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	850 lm	5 W	Emergency lighting 3 hours duration Pro version
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	850 lm	5 W	Emergency lighting 3 hours duration with Wireless Interface
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	850 lm	5 W	Emergency lighting 3 hours duration Pro version
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	850 lm	5 W	Emergency lighting 3 hours duration with Wireless Interface
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	-	-	-
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	-	-	-
910505104565	BY581P 250S/840 DIA HEWBGCSICHEMMBW1mCW5	-	-	-
910505102872	BY580P 170S/840 PSU WB GC SI	-	-	-
910505102874	BY580P 170S/840 PSU HE WB GC SI	-	-	-
910505102876	BY580P 100S/840 DIA UE WB GC SI	-	-	-
910505102878	BY580P 130S/840 DIA WB GC SI	-	-	-
910505102879	BY580P 170S/840 DIA WB GC SI	-	-	-
910505102882	BY580P 130S/840 DIA HE WB GC SI	-	-	-
910505102883	BY580P 170S/840 DIA HE WB GC SI	-	-	-
910505102886	BY580P 170S/840 DIA WB PC SI	-	-	-
910505102890	BY580P 170S/840 DIA HE WB PC SI	-	-	-
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	450 lm	3 W	Emergency lighting 3 hours duration Pro version
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	450 lm	3 W	Emergency lighting 3 hours duration Pro version
910505102898	BY580P 130S/840 DIA MB GC SI	-	-	-
910505102899	BY580P 170S/840 DIA MB GC SI	-	-	-
910505102903	BY580P 130S/840 DIA HE MB GC SI	-	-	-
910505102904	BY580P 170S/840 DIA HE MB GC SI	-	-	-
910505102914	BY580P 170S/840 DIA NB GC SI	-	-	-
910505102916	BY580P 170S/840 DIA HE NB GC SI	-	-	-
910505102918	BY580P 170S/840 DIA XNB GC SI	-	-	-

Order Code	Full Product Name	Emergency flux	Power consumption during Central DC emergency mode	Emergency lighting
910505102920	BY580P 170S/840 DIA HE XNB GC SI	-	-	-
910505102922	BY580P 170S/840 DIA HRO GC SI	-	-	-
910505102924	BY580P 170S/840 DIA HE HRO GC SI	-	-	-
910505102926	BY580P 170S/865 DIA WB GC SI	-	-	-
910505102928	BY580P 170S/865 DIA HE WB GC SI	-	-	-
910505102930	BY580P 170S/830 DIA WB GC SI	-	-	-
910505102932	BY580P 170S/830 DIA HE WB GC SI	-	-	-
910505102934	BY580P 170S/940 DIA WB GC SI	-	-	-
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	-	-	-
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	-	-	-
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	-	-	-
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	-	-	-
910505104558	BY580X 170S/840 SIA WB GC SI IA9	-	-	-
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	-	-	-
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	-	-	-
910505102889	BY581P 250S/840 DIA WB GC SI BR	-	-	-
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	-	-	-
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	-	-	-
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	-	-	-
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	-	-	-
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	-	-	-
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	-	-	-
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	-	-	-
910505104553	BY581P 250S/840 PSD WB GC II SI BR	-	-	-
910505104563	BY581P 250S/840 DIA HE WBGCSICHEMBR1mCW5	-	-	-
910505102888	BY580P 170S/840 DIA WB GC SI BR	-	-	-
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	-	-	-
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	-	-	-
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	-	-	-
910505104562	BY580P 170S/840 DIA HE WBGCSICHEMBR1mCW5	-	-	-
910505104564	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5	-	-	-
910505102873	BY581P 250S/840 PSU WB GC SI	-	-	-
910505102875	BY581P 250S/840 PSU HE WB GC SI	-	-	-
910505102877	BY581P 200S/840 DIA UE WB GC SI	-	-	-
910505102880	BY581P 250S/840 DIA WB GC SI	-	-	-
910505102881	BY581P 350S/840 DIA WB GC SI	-	-	-
910505102884	BY581P 250S/840 DIA HE WB GC SI	-	-	-
910505102885	BY581P 350S/840 DIA HE WB GC SI	-	-	-
910505102887	BY581P 250S/840 DIA WB PC SI	-	-	-
910505102891	BY581P 250S/840 DIA HE WB PC SI	-	-	-

Order Code	Full Product Name	Emergency flux	Power consumption during Central DC emergency mode	Emergency lighting
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	850 lm	5 W	Emergency lighting 3 hours duration with DALI interface
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	850 lm	5 W	Emergency lighting 3 hours duration with DALI interface
910505102901	BY581P 250S/840 DIA MB GC SI	-	-	-
910505102902	BY581P 350S/840 DIA MB GC SI	-	-	-
910505102905	BY581P 250S/840 DIA HE MB GC SI	-	-	-
910505102906	BY581P 350S/840 DIA HE MB GC SI	-	-	-
910505102915	BY581P 250S/840 DIA NB GC SI	-	-	-
910505102917	BY581P 250S/840 DIA HE NB GC SI	-	-	-
910505102919	BY581P 250S/840 DIA XNB GC SI	-	-	-
910505102921	BY581P 250S/840 DIA HE XNB GC SI	-	-	-
910505102923	BY581P 250S/840 DIA HRO GC SI	-	-	-
910505102925	BY581P 250S/840 DIA HE HRO GC SI	-	-	-
910505102927	BY581P 250S/865 DIA WB GC SI	-	-	-
910505102929	BY581P 250S/865 DIA HE WB GC SI	-	-	-
910505102931	BY581P 250S/830 DIA WB GC SI	-	-	-
910505102933	BY581P 250S/830 DIA HE WB GC SI	-	-	-
910505102935	BY581P 250S/940 DIA WB GC SI	-	-	-
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	-	-	-
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	-	-	-
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	-	-	-
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	-	-	-
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	-	-	-
910505102856	BY580X 130S/840 SIA WB GC SI H4	-	-	-
910505102857	BY580X 170S/840 SIA WB GC SI H4	-	-	-
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	-	-	-
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	-	-	-

Approval and Application

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)	Ambient temperature range
910505102953	BY581P 700S/840 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C
910505102954	BY581P 700S/840 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C
910505102955	BY581P 700S/840 DIA WB GC SI BR	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Strobo-scopic effect visibility measure (SVM)	Ambient temperature range
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102858	BY581X 250S/840 SIA WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102859	BY581X 350S/840 SIA WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	Temperature 850 °C, duration 30 s	1	0.4	0 °C to 25 °C
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	Temperature 850 °C, duration 30 s	1	0.4	0 °C to 25 °C
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	Temperature 850 °C, duration 30 s	1	0.4	0 °C to 25 °C
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	Temperature 850 °C, duration 30 s	1	0.4	0 °C to 25 °C
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505104565	BY581P 250S/840 DIA HEWBGCSICHEMMBW1mCW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102872	BY580P 170S/840 PSU WB GC SI	Temperature 650 °C, duration 30 s	0.04	0.07	-30 to +55 °C
910505102874	BY580P 170S/840 PSU HE WB GC SI	Temperature 650 °C, duration 30 s	0.04	0.07	-30 to +55 °C
910505102876	BY580P 100S/840 DIA UE WB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102878	BY580P 130S/840 DIA WB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102879	BY580P 170S/840 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102882	BY580P 130S/840 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102883	BY580P 170S/840 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102886	BY580P 170S/840 DIA WB PC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102890	BY580P 170S/840 DIA HE WB PC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	Temperature 850 °C, duration 30 s	0.12	0.07	0 °C to 25 °C

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Strobe-scopic effect visibility measure (SVM)	Ambient temperature range
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	Temperature 850 °C, duration 30 s	-	-	0 °C to 25 °C
910505102898	BY580P 130S/840 DIA MB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102899	BY580P 170S/840 DIA MB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102903	BY580P 130S/840 DIA HE MB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102904	BY580P 170S/840 DIA HE MB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102914	BY580P 170S/840 DIA NB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102916	BY580P 170S/840 DIA HE NB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102918	BY580P 170S/840 DIA XNB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102920	BY580P 170S/840 DIA HE XNB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102922	BY580P 170S/840 DIA HRO GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102924	BY580P 170S/840 DIA HE HRO GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102926	BY580P 170S/865 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102928	BY580P 170S/865 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102930	BY580P 170S/830 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102932	BY580P 170S/830 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102934	BY580P 170S/940 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505104558	BY580X 170S/840 SIA WB GC SI IA9	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102889	BY581P 250S/840 DIA WB GC SI BR	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Strobo-scopic effect visibility measure (SVM)	Ambient temperature range
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	Temperature 650 °C, duration 30 s	0.22	0.01	-30 °C to 55 °C
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104553	BY581P 250S/840 PSD WB GC II SI BR	Temperature 650 °C, duration 30 s	0.35	0.07	-30 to +55 °C
910505104563	BY581P 250S/840 DIA HE WBGCSICHEMBR1mCW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102888	BY580P 170S/840 DIA WB GC SI BR	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505104562	BY580P 170S/840 DIA HE WBGCSICHEMBR1mCW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104564	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5	Temperature 650 °C, duration 30 s	-	-	-30 to +55 °C
910505102873	BY581P 250S/840 PSU WB GC SI	Temperature 650 °C, duration 30 s	0.04	0.07	-30 to +55 °C
910505102875	BY581P 250S/840 PSU HE WB GC SI	Temperature 650 °C, duration 30 s	0.04	0.07	-30 to +55 °C
910505102877	BY581P 200S/840 DIA UE WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102880	BY581P 250S/840 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102881	BY581P 350S/840 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C
910505102884	BY581P 250S/840 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102885	BY581P 350S/840 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C
910505102887	BY581P 250S/840 DIA WB PC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102891	BY581P 250S/840 DIA HE WB PC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Strobo-scopic effect visibility measure (SVM)	Ambient temperature range
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	Temperature 850 °C, duration 30 s	0.12	0.07	0 °C to 25 °C
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	Temperature 850 °C, duration 30 s	0.12	0.07	0 °C to 25 °C
910505102901	BY581P 250S/840 DIA MB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102902	BY581P 350S/840 DIA MB GC SI	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C
910505102905	BY581P 250S/840 DIA HE MB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102906	BY581P 350S/840 DIA HE MB GC SI	Temperature 650 °C, duration 30 s	0.22	0.01	-30 to +55 °C
910505102915	BY581P 250S/840 DIA NB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102917	BY581P 250S/840 DIA HE NB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102919	BY581P 250S/840 DIA XNB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102921	BY581P 250S/840 DIA HE XNB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102923	BY581P 250S/840 DIA HRO GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102925	BY581P 250S/840 DIA HE HRO GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102927	BY581P 250S/865 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102929	BY581P 250S/865 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102931	BY581P 250S/830 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102933	BY581P 250S/830 DIA HE WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102935	BY581P 250S/940 DIA WB GC SI	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	Temperature 650 °C, duration 30 s	0.12	0.07	-30 °C to 65 °C
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	Temperature 650 °C, duration 30 s	0.22	0.01	-30 °C to 55 °C
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	Temperature 650 °C, duration 30 s	0.12	0.07	-30 to +55 °C
910505102856	BY580X 130S/840 SIA WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102857	BY580X 170S/840 SIA WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Strobo-scopic effect visibility measure (SVM)	Ambient temperature range
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	Temperature 650 °C, duration 30 s	1	0.4	-30 to +55 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102953	BY581P 700S/840 DIA WB GC SI	(0.380, 0.375) SDCM 3
910505102954	BY581P 700S/840 DIA HE WB GC SI	(0.383, 0.377) SDCM 3
910505102955	BY581P 700S/840 DIA WB GC SI BR	(0.380, 0.375) SDCM 3
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	(0.383, 0.377) SDCM 3
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	(0.380, 0.375) SDCM 3
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	(0.383, 0.377) SDCM 3
910505102858	BY581X 250S/840 SIA WB GC SI H4	(0.380, 0.375) SDCM 3
910505102859	BY581X 350S/840 SIA WB GC SI H4	(0.380, 0.375) SDCM 3
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	(0.383, 0.377) SDCM 3
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	(0.383, 0.377) SDCM 3
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	(0.380, 0.375) SDCM 3
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	(0.380, 0.375) SDCM 3
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	(0.383, 0.377) SDCM 3
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	(0.383, 0.377) SDCM 3
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	(0.380, 0.375) SDCM 3
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	(0.383, 0.377) SDCM 3
910505104565	BY581P 250S/840 DIA HEWBGC SICHEMMBW1mCW5	(0.383, 0.377) SDCM 3
910505102872	BY580P 170S/840 PSU WB GC SI	(0.380, 0.375) SDCM 3
910505102874	BY580P 170S/840 PSU HE WB GC SI	(0.383, 0.377) SDCM 3
910505102876	BY580P 100S/840 DIA UE WB GC SI	(0.383, 0.377) SDCM 3
910505102878	BY580P 130S/840 DIA WB GC SI	(0.380, 0.375) SDCM 3
910505102879	BY580P 170S/840 DIA WB GC SI	(0.380, 0.375) SDCM 3
910505102882	BY580P 130S/840 DIA HE WB GC SI	(0.383, 0.377) SDCM 3
910505102883	BY580P 170S/840 DIA HE WB GC SI	(0.383, 0.377) SDCM 3
910505102886	BY580P 170S/840 DIA WB PC SI	(0.380, 0.375) SDCM 3
910505102890	BY580P 170S/840 DIA HE WB PC SI	(0.383, 0.377) SDCM 3
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	(0.380, 0.375) SDCM 3
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	(0.383, 0.377) SDCM 3
910505102898	BY580P 130S/840 DIA MB GC SI	(0.380, 0.375) SDCM 3
910505102899	BY580P 170S/840 DIA MB GC SI	(0.380, 0.375) SDCM 3
910505102903	BY580P 130S/840 DIA HE MB GC SI	(0.383, 0.377) SDCM 3

Order Code	Full Product Name	Initial chromaticity
910505102904	BY580P 170S/840 DIA HE MB GC SI	(0.383, 0.377) SDCM 3
910505102914	BY580P 170S/840 DIA NB GC SI	(0.380, 0.375) SDCM 3
910505102916	BY580P 170S/840 DIA HE NB GC SI	(0.383, 0.377) SDCM 3
910505102918	BY580P 170S/840 DIA XNB GC SI	(0.380, 0.375) SDCM 3
910505102920	BY580P 170S/840 DIA HE XNB GC SI	(0.383, 0.377) SDCM 3
910505102922	BY580P 170S/840 DIA HRO GC SI	(0.380, 0.375) SDCM 3
910505102924	BY580P 170S/840 DIA HE HRO GC SI	(0.383, 0.377) SDCM 3
910505102926	BY580P 170S/865 DIA WB GC SI	(0.312, 0.327) SDCM 3
910505102928	BY580P 170S/865 DIA HE WB GC SI	(0.312, 0.325) SDCM 3
910505102930	BY580P 170S/830 DIA WB GC SI	(0.432, 0.400) SDCM 3
910505102932	BY580P 170S/830 DIA HE WB GC SI	(0.435, 0.401) SDCM 3
910505102934	BY580P 170S/940 DIA WB GC SI	(0.380, 0.375) SDCM 3
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	(0.380, 0.375) SDCM 3
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	(0.380, 0.375) SDCM 3
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	(0.380, 0.375) SDCM 3
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	(0.383, 0.377) SDCM 3
910505104558	BY580X 170S/840 SIA WB GC SI IA9	(0.380, 0.375) SDCM 3
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	(0.380, 0.375) SDCM 3
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	(0.383, 0.377) SDCM 3
910505102889	BY581P 250S/840 DIA WB GC SI BR	(0.380, 0.375) SDCM 3
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	(0.383, 0.377) SDCM 3
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	(0.380, 0.375) SDCM 3
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	(0.383, 0.377) SDCM 3
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	(0.380, 0.375) SDCM 3
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	(0.383, 0.377) SDCM 3
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	(0.383, 0.377) SDCM 3
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	(0.383, 0.377) SDCM 3
910505104553	BY581P 250S/840 PSD WB GC II SI BR	(0.380, 0.375) SDCM 3
910505104563	BY581P 250S/840 DIA HE WBGCSICHEMBR1mCW5	(0.383, 0.377) SDCM 3
910505102888	BY580P 170S/840 DIA WB GC SI BR	(0.380, 0.375) SDCM 3
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	(0.383, 0.377) SDCM 3
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	(0.383, 0.377) SDCM 3
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	(0.383, 0.377) SDCM 3
910505104562	BY580P 170S/840 DIA HE WBGCSICHEMBR1mCW5	(0.383, 0.377) SDCM 3
910505104564	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5	(0.383, 0.377) SDCM 3
910505102873	BY581P 250S/840 PSU WB GC SI	(0.380, 0.375) SDCM 3
910505102875	BY581P 250S/840 PSU HE WB GC SI	(0.383, 0.377) SDCM 3
910505102877	BY581P 200S/840 DIA UE WB GC SI	(0.383, 0.377) SDCM 3
910505102880	BY581P 250S/840 DIA WB GC SI	(0.380, 0.375) SDCM 3
910505102881	BY581P 350S/840 DIA WB GC SI	(0.380, 0.375) SDCM 3
910505102884	BY581P 250S/840 DIA HE WB GC SI	(0.383, 0.377) SDCM 3
910505102885	BY581P 350S/840 DIA HE WB GC SI	(0.383, 0.377) SDCM 3

Order Code	Full Product Name	Initial chromaticity
910505102887	BY581P 250S/840 DIA WB PC SI	(0.380, 0.375) SDCM 3
910505102891	BY581P 250S/840 DIA HE WB PC SI	(0.383, 0.377) SDCM 3
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	(0.380, 0.375) SDCM 3
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	(0.383, 0.377) SDCM 3
910505102901	BY581P 250S/840 DIA MB GC SI	(0.380, 0.375) SDCM 3
910505102902	BY581P 350S/840 DIA MB GC SI	(0.380, 0.375) SDCM 3
910505102905	BY581P 250S/840 DIA HE MB GC SI	(0.383, 0.377) SDCM 3
910505102906	BY581P 350S/840 DIA HE MB GC SI	(0.383, 0.377) SDCM 3
910505102915	BY581P 250S/840 DIA NB GC SI	(0.380, 0.375) SDCM 3
910505102917	BY581P 250S/840 DIA HE NB GC SI	(0.383, 0.377) SDCM 3
910505102919	BY581P 250S/840 DIA XNB GC SI	(0.380, 0.375) SDCM 3
910505102921	BY581P 250S/840 DIA HE XNB GC SI	(0.383, 0.377) SDCM 3
910505102923	BY581P 250S/840 DIA HRO GC SI	(0.380, 0.375) SDCM 3
910505102925	BY581P 250S/840 DIA HE HRO GC SI	(0.383, 0.377) SDCM 3
910505102927	BY581P 250S/865 DIA WB GC SI	(0.312, 0.327) SDCM 3
910505102929	BY581P 250S/865 DIA HE WB GC SI	(0.312, 0.325) SDCM 3
910505102931	BY581P 250S/830 DIA WB GC SI	(0.432, 0.400) SDCM 3
910505102933	BY581P 250S/830 DIA HE WB GC SI	(0.435, 0.401) SDCM 3
910505102935	BY581P 250S/940 DIA WB GC SI	(0.380, 0.375) SDCM 3
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	(0.383, 0.377) SDCM 3
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	(0.383, 0.377) SDCM 3
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	(0.380, 0.375) SDCM 3
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	(0.380, 0.375) SDCM 3
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	(0.383, 0.377) SDCM 3
910505102856	BY580X 130S/840 SIA WB GC SI H4	(0.380, 0.375) SDCM 3
910505102857	BY580X 170S/840 SIA WB GC SI H4	(0.380, 0.375) SDCM 3
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	(0.383, 0.377) SDCM 3
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	(0.383, 0.377) SDCM 3

Product Data


Order Code	Full Product Name	Product family code
910505102953	BY581P 700S/840 DIA WB GC SI	BY581P
910505102954	BY581P 700S/840 DIA HE WB GC SI	BY581P
910505102955	BY581P 700S/840 DIA WB GC SI BR	BY581P
910505102956	BY581P 700S/840 DIA HE WB GC SI BR	BY581P
910505102865	BY581X 250S/840 SIA WB GC SI H4 BR	BY580X
910505102866	BY581X 250S/840 SIA HE WB GC SI H4 BR	BY581X
910505102858	BY581X 250S/840 SIA WB GC SI H4	BY580X
910505102859	BY581X 350S/840 SIA WB GC SI H4	BY581X
910505102862	BY581X 250S/840 SIA HE WB GC SI H4	BY581X
910505102863	BY581X 350S/840 SIA HE WB GC SI H4	BY581X
910505102868	BY581X 250S/840 SIA WB GC SI ELP3 H4	BY581X

Order Code	Full Product Name	Product family code
910505102869	BY581X 250S/840 SIA WB GC SI ELW3 H4	BY581X
910505102870	BY581X 250S/840 SIA HE WB GC SI ELP3 H4	BY581X
910505102871	BY581X 250S/840 SIA HE WB GC SI ELW3 H4	BY581X
910505102864	BY580X 170S/840 SIA WB GC SI H4 BR	BY580X
910505102867	BY580X 170S/840 SIA HE WB GC SI H4 BR	BY580X
910505104565	BY581P 250S/840 DIA HEWBGCSICHEMMBW1mCW5	BY581P
910505102872	BY580P 170S/840 PSU WB GC SI	BY580P
910505102874	BY580P 170S/840 PSU HE WB GC SI	BY580P
910505102876	BY580P 100S/840 DIA UE WB GC SI	BY580P
910505102878	BY580P 130S/840 DIA WB GC SI	BY580P
910505102879	BY580P 170S/840 DIA WB GC SI	BY580P
910505102882	BY580P 130S/840 DIA HE WB GC SI	BY580P
910505102883	BY580P 170S/840 DIA HE WB GC SI	BY580P
910505102886	BY580P 170S/840 DIA WB PC SI	BY580P
910505102890	BY580P 170S/840 DIA HE WB PC SI	BY580P
910505102894	BY580P 170S/840 DIA WB GC SI ELP3	BY580P
910505102896	BY580P 170S/840 DIA HE WB GC SI ELP3	BY580P
910505102898	BY580P 130S/840 DIA MB GC SI	BY580P
910505102899	BY580P 170S/840 DIA MB GC SI	BY580P
910505102903	BY580P 130S/840 DIA HE MB GC SI	BY580P
910505102904	BY580P 170S/840 DIA HE MB GC SI	BY580P
910505102914	BY580P 170S/840 DIA NB GC SI	BY580P
910505102916	BY580P 170S/840 DIA HE NB GC SI	BY580P
910505102918	BY580P 170S/840 DIA XNB GC SI	BY580P
910505102920	BY580P 170S/840 DIA HE XNB GC SI	BY580P
910505102922	BY580P 170S/840 DIA HRO GC SI	BY580P
910505102924	BY580P 170S/840 DIA HE HRO GC SI	BY580P
910505102926	BY580P 170S/865 DIA WB GC SI	BY580P
910505102928	BY580P 170S/865 DIA HE WB GC SI	BY580P
910505102930	BY580P 170S/830 DIA WB GC SI	BY580P
910505102932	BY580P 170S/830 DIA HE WB GC SI	BY580P
910505102934	BY580P 170S/940 DIA WB GC SI	BY580P
910505104540	BY582P 170S/840 DIA HE WB GC SI 0.5m CW5	BY582P
910505104542	BY582P 170S/840 DIA HE WB GC SI 1m CW5	BY582P
910505104554	BY580P 170S/840 DIA WB GC SI BP 1m CW5	BY580P
910505104556	BY580P 170S/840 DIA HE WB GC SI BP 1mCW5	BY580P
910505104558	BY580X 170S/840 SIA WB GC SI IA9	BY580X
910505102910	BY580P 170S/840 DIA ASYM GC SI MBW	BY580P
910505102912	BY580P 170S/840 DIA HE ASYM GC SI MBW	BY580P
910505102889	BY581P 250S/840 DIA WB GC SI BR	BY581P
910505102893	BY581P 250S/840 DIA HE WB GC SI BR	BY581P
910505102907	BY581P 250S/840 DIA ASYM GC SI BR	BY581P

Order Code	Full Product Name	Product family code
910505102909	BY581P 250S/840 DIA HE ASYM GC SI BR	BY581P
910505102911	BY581P 250S/840 DIA ASYM GC SI MBW	BY581P
910505102913	BY581P 250S/840 DIA HE ASYM GC SI MBW	BY581P
910505102938	BY581P 350S/840 DIA HE WB GC SI BR XT 1m	BY581P
910505104551	BY581P 250S/840 DIA HE WB GC SI MSP BR	BY581P
910505104553	BY581P 250S/840 PSD WB GC II SI BR	BY581P
910505104563	BY581P 250S/840 DIA HE WBGCSICHEMBR1mCW5	BY581P
910505102888	BY580P 170S/840 DIA WB GC SI BR	BY580P
910505102892	BY580P 170S/840 DIA HE WB GC SI BR	BY580P
910505102908	BY580P 170S/840 DIA HE ASYM GC SI BR	BY580P
910505104550	BY580P 170S/840 DIA HE WB GC SI MSP BR	BY580P
910505104562	BY580P 170S/840 DIA HE WBGCSICHEMBR1mCW5	BY580P
910505104564	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5	BY580P
910505102873	BY581P 250S/840 PSU WB GC SI	BY581P
910505102875	BY581P 250S/840 PSU HE WB GC SI	BY581P
910505102877	BY581P 200S/840 DIA UE WB GC SI	BY581P
910505102880	BY581P 250S/840 DIA WB GC SI	BY581P
910505102881	BY581P 350S/840 DIA WB GC SI	BY581P
910505102884	BY581P 250S/840 DIA HE WB GC SI	BY581P
910505102885	BY581P 350S/840 DIA HE WB GC SI	BY581P
910505102887	BY581P 250S/840 DIA WB PC SI	BY581P
910505102891	BY581P 250S/840 DIA HE WB PC SI	BY581P
910505102895	BY581P 250S/840 DIA WB GC SI ELD3	BY581P
910505102897	BY581P 250S/840 DIA HE WB GC SI ELD3	BY581P
910505102901	BY581P 250S/840 DIA MB GC SI	BY581P
910505102902	BY581P 350S/840 DIA MB GC SI	BY581P
910505102905	BY581P 250S/840 DIA HE MB GC SI	BY581P
910505102906	BY581P 350S/840 DIA HE MB GC SI	BY581P
910505102915	BY581P 250S/840 DIA NB GC SI	BY581P
910505102917	BY581P 250S/840 DIA HE NB GC SI	BY581P
910505102919	BY581P 250S/840 DIA XNB GC SI	BY581P
910505102921	BY581P 250S/840 DIA HE XNB GC SI	BY581P
910505102923	BY581P 250S/840 DIA HRO GC SI	BY581P
910505102925	BY581P 250S/840 DIA HE HRO GC SI	BY581P
910505102927	BY581P 250S/865 DIA WB GC SI	BY581P
910505102929	BY581P 250S/865 DIA HE WB GC SI	BY581P
910505102931	BY581P 250S/830 DIA WB GC SI	BY581P
910505102933	BY581P 250S/830 DIA HE WB GC SI	BY581P
910505102935	BY581P 250S/940 DIA WB GC SI	BY581P
910505102936	BY581P 250S/840 DIA HE WB GC SI XT 1m	BY581P
910505102937	BY581P 350S/840 DIA HE WB GC SI XT 1m	BY581P
910505104541	BY583P 250S/840 DIA HE WB GC SI 0.5m CW5	BY583P

Order Code	Full Product Name	Product family code
910505104555	BY581P 250S/840 DIA WB GC SI BP 1m CW5	BY581P
910505104557	BY581P 250S/840 DIA HE WB GC SI BP 1mCW5	BY581P
910505102856	BY580X 130S/840 SIA WB GC SI H4	BY580X
910505102857	BY580X 170S/840 SIA WB GC SI H4	BY580X
910505102860	BY580X 130S/840 SIA HE WB GC SI H4	BY580X
910505102861	BY580X 170S/840 SIA HE WB GC SI H4	BY580X


Polar normal diagrams



BY580PI - 910505104540

BY580PI - 910505104542


BY580PI - 910505104541




BY580PI - 910505102872

BY580PI - 910505102863


BY580PI - 910505102914




BY580PI - 910505102899




BY580PI - 910505102869




BY580PI - 910505102915




BY580PI - 910505102865




BY580PI - 910505102895




BY580PI - 910505102898




BY580PI - 910505102856




BY580PI - 910505102924




BY580PI - 910505102881




BY580PI - 910505102925




BY580PI - 910505102857




BY580PI - 910505102933




BY580PI - 910505102873




BY580PI - 910505102902




BY580PI - 910505102884




BY580PI - 910505102874




BY580PI - 910505102896




BY580PI - 910505102875




BY580PI - 910505102868




BY580PI - 910505102923




BY580PI - 910505102858




BY580PI - 910505102871




BY580PI - 910505102901




BY580PI - 910505102922




BY580PI - 910505102862




BY580PI - 910505102906




BY580PI - 910505102921




BY580PI - 910505102920




BY580PI - 910505102932




BY580PI - 910505102864




BY580PI - 910505102934




BY580PI - 910505102878




BY580PI - 910505102866




BY580PI - 910505102885




BY580PI - 910505102883




BY580PI - 910505102918




BY580PI - 910505102882




BY580PI - 910505102916




BY580PI - 910505102926




BY580PI - 910505102928




BY580PI - 910505102935




BY580PI - 910505102903




BY580PI - 910505102891




BY580PI - 910505102904




BY580PI - 910505102886




BY580PI - 910505102867




BY580PI - 910505102905




BY580PI - 910505102890




BY580PI - 910505102894




BY580PI - 910505102930




BY580PI - 910505102919




BY580PI - 910505102879




BY580PI - 910505102870




BY580PI - 910505102887




BY580PI - 910505102859




BY580PI - 910505102892




BY580PI - 910505102893




BY580PI - 910505102860




BY580PI - 910505102929




BY580PI - 910505102931




BY580PI - 910505102917




BY580PI - 910505102877




BY580PI - 910505102889




BY580PI - 910505102927




BY580PI - 910505102861




BY580PI - 910505102888




BY580PI - 910505102880




BY580PI - 910505102897




BY580PI - 910505102876




BY580PI - 910505102938




BY580PI - 910505102936




BY580PI - 910505102937




BY580PI - 910505104550




BY580PI - 910505104551




BY580PI - 910505102907




BY580PI - 910505102913




BY580PI - 910505102912




BY580PI - 910505102909




BY580PI - 910505102908




BY580PI - 910505102910




BY580PI - 910505102911




BY580PI - 910505104557




BY580PI - 910505104554




BY580PI - 910505104555




BY580PI - 910505104563




BY580PI - 910505104556




BY580PI - 910505104564




BY580PI - 910505104565



BY580PI - 910505104562



BY580PI - 910505104553



BY580PI - 910505104558

