

Classic LED spotMV

2125544



Classic heritage design

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Benefits

- Long lifetime
- Huge energy savings
- Low heat generation.

Applications

- Operating temperature range is between -20 °C and 45 °C ambient
- Only to be used in dry indoor environments; can be used in most open fixtures with GU10 lamp holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency lighting fixtures or exit lights

Features

- Classic heritage design


- Easy retrofit
- Energy-efficient

Versions



LEDspot 25W GU10 MR11 827
36D ND

Dimensional drawing



Product	D	C
MR11 GU10 3.5W-35W WW 36D 2700K SRT6	36 mm	50 mm

General Information

Cap-Base	GU10
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	25,000 hour(s)

Light Technical

Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	240 lm
Luminous Intensity (Nom)	450 cd
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3.5 W
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	MR11

Approval and Application

Energy Consumption kWh/1000 h	4 kWh
Ambient temperature range	-20 to +40 °C