

Classic LED spotMV

2125544



Classic heritage design

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Benefits

- Long lifetime
- Huge energy savings
- Low heat generation.

Applications

- Operating temperature range is between -20 °C and 45 °C ambient
- Only to be used in dry indoor environments; can be used in most open fixtures with GU10 lamp holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency lighting fixtures or exit lights

Features

- Classic heritage design


- Easy retrofit
- Energy-efficient

Versions



LED 40W G9 WW 230V Dim
SRT6

Dimensional drawing



Product	D	C
LED 40W G9 WW 230V Dim SRT6	18 mm	59 mm

General Information

Cap-Base	G9
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000

Light Technical

Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	320 degree(s)
Luminous Flux	480 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Power Consumption	4 W
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	93 °C
----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	G9

Approval and Application

Energy Consumption kWh/1000 h	4 kWh
Ambient temperature range	-20 to +45 °C