

Classic LED spotMV

2125544



Classic heritage design

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Benefits

- Long lifetime
- Huge energy savings
- Low heat generation.

Applications

- Operating temperature range is between -20 °C and 45 °C ambient
- Only to be used in dry indoor environments; can be used in most open fixtures with GU10 lamp holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency lighting fixtures or exit lights

Features

- Classic heritage design

- Easy retrofit
- Energy-efficient

Versions




CorePro LEDspot MV 25W
GU10 830 36D




LEDspots MAS EU PAR16
GU10

Dimensional drawing



Product	D	C
LEDClassic 4.6W GU10 830 60D 2pack	50 mm	54 mm
LEDClassic 4.6W GU10 840 60D 2pack	50 mm	54 mm
LEDspots 4.6W GU10 830 60D	50 mm	54 mm
LEDspots 4.6W GU10 840 60D	50 mm	54 mm



Product	D	C
LEDClassic 2.1W GU10 CW 36D ND UE SRT6	50 mm	54 mm
LEDClassic 2.1W GU10 WH 36D ND UE SRT6	50 mm	54 mm

General Information

Cap-Base	GU10
Switching Cycle	50,000

Light Technical

Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	PAR16

Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

General Information

Order Code	Full Product Name	Nominal lifetime
929001287691	LEDspots 4.6W GU10 830 60D	15,000 hour(s)
929001287692	LEDClassic 4.6W GU10 830 60D 2pack	15,000 hour(s)
929001287791	LEDspots 4.6W GU10 840 60D	15,000 hour(s)
929001287792	LEDClassic 4.6W GU10 840 60D 2pack	15,000 hour(s)
929003610019	LEDClassic 2.1W GU10 WH 36D ND UE SRT6	50,000 hour(s)
929003610119	LEDClassic 2.1W GU10 CW 36D ND UE SRT6	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Luminous Intensity (Nom)	Correlated Color Temperature (Nom)
929001287691	LEDspots 4.6W GU10 830 60D	830	60 degree(s)	410 lm	450 cd	3000 K
929001287692	LEDClassic 4.6W GU10 830 60D 2pack	830	60 degree(s)	410 lm	450 cd	3000 K
929001287791	LEDspots 4.6W GU10 840 60D	840	60 degree(s)	430 lm	450 cd	4000 K
929001287792	LEDClassic 4.6W GU10 840 60D 2pack	840	60 degree(s)	430 lm	450 cd	4000 K
929003610019	LEDClassic 2.1W GU10 WH 36D ND UE SRT6	830	36 degree(s)	400 lm	680 cd	3000 K
929003610119	LEDClassic 2.1W GU10 CW 36D ND UE SRT6	840	36 degree(s)	400 lm	680 cd	4000 K

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929001287691	LEDspots 4.6W GU10 830 60D	4.6 W
929001287692	LEDClassic 4.6W GU10 830 60D 2pack	4.6 W
929001287791	LEDspots 4.6W GU10 840 60D	4.6 W
929001287792	LEDClassic 4.6W GU10 840 60D 2pack	4.6 W
929003610019	LEDClassic 2.1W GU10 WH 36D ND UE SRT6	2.1 W
929003610119	LEDClassic 2.1W GU10 CW 36D ND UE SRT6	2.1 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001287691	LEDspots 4.6W GU10 830 60D	80 °C
929001287692	LEDClassic 4.6W GU10 830 60D 2pack	80 °C
929001287791	LEDspots 4.6W GU10 840 60D	80 °C
929001287792	LEDClassic 4.6W GU10 840 60D 2pack	80 °C
929003610019	LEDClassic 2.1W GU10 WH 36D ND UE SRT6	60 °C
929003610119	LEDClassic 2.1W GU10 CW 36D ND UE SRT6	60 °C