

Maxos LED

4MX850



Maxos LED Industry – innovative, flexible solution delivers ideal light output

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED Industry offers best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED Industry system comprises exchangeable mid-power LED boards mounted on a standard Maxos trunking rail. A choice of wide and medium-beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: the use of our upgradable LED engine platform makes Maxos LED Industry a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven Maxos trunking system

Applications

- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers
- Showrooms

Versions



IPPR 4MX850i 0003




Maxos LED Industry




IPPR 4MX850i 0007

Dimensional drawing



Maxos Led Industry - 1 unit for TL-D 58 W - LED Module, system flux 5500 lm - 830 warm white - Power supply unit with DALI interface - Wide beam - Silver



Maxos Led Industry - 1 unit for TL5 49 W - LED module, system flux 4000 lm - 840 neutral white - Power supply unit with DALI interface - Wide beam - White

Product details



IPDP_4MX850i_0001-Detail photo



IPDP_4MX850i_0003-Detail photo



IPDP_4MX850i_0005-Detail photo

General Information	
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	120 degree(s)
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polymethyl methacrylate bowl/cover

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Product Data

Product family code	4MX850 [Maxos Led Industry]
---------------------	-----------------------------

General Information

Order Code	Full Product Name	Lamp family code
67282099	4MX850 491 LED80S/840 PSD WB WH	LED80S
66127599	4MX850 491 LED55S/830 PSD WB SI	LED55S
66128299	4MX850 491 LED55S/840 PSD WB SI	LED55S
66131299	4MX850 581 LED55S/830 PSD WB SI	LED55S
66132999	4MX850 581 LED55S/840 PSD WB SI	LED55S
66118399	4MX850 491 LED55S/840 PSD NB WH	LED55S
66119099	4MX850 491 LED55S/830 PSD WB WH	LED55S
66120699	4MX850 491 LED55S/840 PSD WB WH	LED55S
66124499	4MX850 581 LED55S/840 PSD WB WH	LED55S
66168899	4MX850 491 LED40S/840 PSD WB WH	LED40S

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
67282099	4MX850 491 LED80S/840 PSD WB WH	8,000 lm	4000 K	166 lm/W	Wide beam
66127599	4MX850 491 LED55S/830 PSD WB SI	5,500 lm	3000 K	169 lm/W	Wide beam
66128299	4MX850 491 LED55S/840 PSD WB SI	5,500 lm	4000 K	169 lm/W	Wide beam
66131299	4MX850 581 LED55S/830 PSD WB SI	5,500 lm	3000 K	169 lm/W	Wide beam
66132999	4MX850 581 LED55S/840 PSD WB SI	5,500 lm	4000 K	169 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
66118399	4MX850 491 LED55S/840 PSD NB WH	5,500 lm	4000 K	169 lm/W	Narrow beam
66119099	4MX850 491 LED55S/830 PSD WB WH	5,500 lm	3000 K	169 lm/W	Wide beam
66120699	4MX850 491 LED55S/840 PSD WB WH	5,500 lm	4000 K	169 lm/W	Wide beam
66124499	4MX850 581 LED55S/840 PSD WB WH	5,500 lm	4000 K	169 lm/W	Wide beam
66168899	4MX850 491 LED40S/840 PSD WB WH	4,000 lm	4000 K	166 lm/W	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
67282099	4MX850 491 LED80S/840 PSD WB WH	48 W
66127599	4MX850 491 LED55S/830 PSD WB SI	32.5 W
66128299	4MX850 491 LED55S/840 PSD WB SI	32.5 W
66131299	4MX850 581 LED55S/830 PSD WB SI	32.5 W
66132999	4MX850 581 LED55S/840 PSD WB SI	32.5 W
66118399	4MX850 491 LED55S/840 PSD NB WH	32.5 W
66119099	4MX850 491 LED55S/830 PSD WB WH	32.5 W
66120699	4MX850 491 LED55S/840 PSD WB WH	32.5 W
66124499	4MX850 581 LED55S/840 PSD WB WH	32.5 W
66168899	4MX850 491 LED40S/840 PSD WB WH	24 W

Mechanical and Housing


Order Code	Full Product Name	Housing Color
67282099	4MX850 491 LED80S/840 PSD WB WH	White
66127599	4MX850 491 LED55S/830 PSD WB SI	Silver
66128299	4MX850 491 LED55S/840 PSD WB SI	Silver
66131299	4MX850 581 LED55S/830 PSD WB SI	Silver
66132999	4MX850 581 LED55S/840 PSD WB SI	Silver
66118399	4MX850 491 LED55S/840 PSD NB WH	White
66119099	4MX850 491 LED55S/830 PSD WB WH	White
66120699	4MX850 491 LED55S/840 PSD WB WH	White
66124499	4MX850 581 LED55S/840 PSD WB WH	White
66168899	4MX850 491 LED40S/840 PSD WB WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
67282099	4MX850 491 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66127599	4MX850 491 LED55S/830 PSD WB SI	(0.43, 0.40) SDCM <3.5
66128299	4MX850 491 LED55S/840 PSD WB SI	(0.38, 0.38) SDCM <3.5
66131299	4MX850 581 LED55S/830 PSD WB SI	(0.43, 0.40) SDCM <3.5
66132999	4MX850 581 LED55S/840 PSD WB SI	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
66118399	4MX850 491 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66119099	4MX850 491 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
66120699	4MX850 491 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66124499	4MX850 581 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66168899	4MX850 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5


Polar normal diagrams



4MX850I - 910629121126

4MX850I - 910629167526


4MX850I - 910629121926



4MX850I - 910629121526

4MX850I - 910629120126

4MX850I - 910629120726



4MX850I - 910629120326