

Maxos LED

4MX850



Maxos LED Industry 4MX850 – innovative, flexible solution delivers ideal light output

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED Industry offers best-in-class energy savings while delivering high lux levels at the required colour temperatures and glare factors. The minimalistic Maxos LED Industry system comprises exchangeable mid-power LED boards mounted on a standard Maxos trunking rail. A choice of wide and medium-beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: the use of our upgradable LED engine platform makes Maxos LED Industry a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven Maxos trunking system

Applications

- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers
- Showrooms



Versions

Features


- Mid-power LED boards; exchangeable LED unit
- Up to 165 lm/W efficiency
- LED gear trays for T5 and TL-D-length trunkings (high lumen output); replacement LED gear trays with same lumen packages as installed T5 and TL-D solutions (lower wattage)
- Choice of narrow, medium, double asymmetric and asymmetric lenses
- Compatible with our standard Maxos LED rails and TTX400 rails for TL5 49 W and TL-D 58 W lengths



Dimensional drawing



Product details





General Information

Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes
Service Tag	Yes

Light Technical

Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	120 degree(s)

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Housing Colour	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polymethyl methacrylate bowl/cover

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5

Product Data

Product family code	4MX850 [Maxos Led Industry]
---------------------	-----------------------------

General Information

Order Code	Full Product Name	Lamp family code
910629167526	4MX850 491 LED80S/840 PSD WB WH	LED80S
910629120326	4MX850 491 LED55S/840 PSD WB WH	LED55S
910629120726	4MX850 581 LED55S/840 PSD WB WH	LED55S
910629121926	4MX850 491 LED40S/840 PSD WB WH	LED40S
910629158226	4MX850 491 LED66S/840 PSD NB WH	LED66S
910629160326	4MX850 581 LED66S/840 PSD WB WH	LED66S


Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous efficacy (rated) (nom.)	Optic type
910629167526	4MX850 491 LED80S/840 PSD WB WH	8,000 lm	166 lm/W	Wide beam
910629120326	4MX850 491 LED55S/840 PSD WB WH	5,500 lm	169 lm/W	Wide beam
910629120726	4MX850 581 LED55S/840 PSD WB WH	5,500 lm	169 lm/W	Wide beam
910629121926	4MX850 491 LED40S/840 PSD WB WH	4,000 lm	166 lm/W	Wide beam
910629158226	4MX850 491 LED66S/840 PSD NB WH	6,600 lm	166 lm/W	Narrow beam
910629160326	4MX850 581 LED66S/840 PSD WB WH	6,600 lm	166 lm/W	Wide beam


Operating and Electrical

Order Code	Full Product Name	Power Consumption
910629167526	4MX850 491 LED80S/840 PSD WB WH	48 W
910629120326	4MX850 491 LED55S/840 PSD WB WH	32.5 W
910629120726	4MX850 581 LED55S/840 PSD WB WH	32.5 W
910629121926	4MX850 491 LED40S/840 PSD WB WH	24 W
910629158226	4MX850 491 LED66S/840 PSD NB WH	39 W
910629160326	4MX850 581 LED66S/840 PSD WB WH	39 W


Polar normal diagrams




4MX850I - 910629167526




4MX850I - 910629121926




4MX850I - 910629158226



4MX850I - 910629160326



4MX850I - 910629120726



4MX850I - 910629120326