



Your everyday LEDspot MR16

Essential LED spot MR16

Essential LEDspots MR16 are compatible with most existing fixtures with a GU5.3 socket and are designed as a retrofit replacement for halogen spots. Essential LEDspots MR16 deliver significant energy savings and minimize initial investment.

Benefits

- Up to 90% energy saving compared with traditional halogen lamps
- Lower maintenance costs
- Low initial investment

Features

- Easy retrofit
- Lifetime up to 15,000 hours
- Non-dimmable
- UV- and IR-free light

Application

- Hotels, restaurants, bars, cafés, shops
- Lobbies, corridors, stairwells, washrooms, reception areas


Essential LED spot MR16

Versions



5W (50W) GU5.3 cap Warm white
Spot - RFT

Dimensional drawing



Product	D	C
5W (50W) GU5.3 cap Warm white Non-dimmable Spot	50 mm	46 mm
ESS LED MR16 4.5-50W 36D 830 100-240V	50.5 mm	46.5 mm
ESS LED MR16 4.5-50W 36D 865 SO 100-240V	50.5 mm	46.5 mm

General Information	
Cap-Base	GU5.3
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	400 lm
Operating and Electrical	
Starting Time (Nom)	0.5 s
Wattage Equivalent	50 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16

General Information

Order Code	Full Product Name	Rated Lifetime (Hours)
929001240108	5W (50W) GU5.3 cap Warm white Non-dimmable Spot	15,000 hour(s)
929001874068	ESS LED MR16 4.5-50W 36D 830 100-240V	-
929001874108	ESS LED MR16 4.5-50W 36D 865 SO 100-240V	-

Light Technical

Essential LED spot MR16

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)		Luminous Intensity (Nom)
			Color Code	Temperature (K)	
929001240108	5W (50W) GU5.3 cap Warm white Non-dimmable Spot	24 degree(s)	827	2700 K	1,700 cd
929001874068	ESS LED MR16 4.5-50W 36D 830 100-240V	36 degree(s)	830	3000 K	700 cd

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)		Luminous Intensity (Nom)
			Color Code	Temperature (K)	
929001874108	ESS LED MR16 4.5-50W 36D 865 SO 100-240V	36 degree(s)	865	6500 K	700 cd

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption
929001240108	5W (50W) GU5.3 cap Warm white Non-dimmable Spot	- Hz	- Hz	5 W
929001874068	ESS LED MR16 4.5-50W 36D 830 100-240V	50 to 60 Hz	50 to 60 Hz	4.5 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption
929001874108	ESS LED MR16 4.5-50W 36D 865 SO 100-240V	50 to 60 Hz	50 to 60 Hz	4.5 W


Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001240108	5W (50W) GU5.3 cap Warm white Non-dimmable Spot	76 °C
929001874068	ESS LED MR16 4.5-50W 36D 830 100-240V	65 °C


Order Code	Full Product Name	T-Case Maximum (Nom)
929001874108	ESS LED MR16 4.5-50W 36D 865 SO 100-240V	65 °C

Approval and Application


Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001240108	5W (50W) GU5.3 cap Warm white Non-dimmable Spot	-20 to +45 °C	-
929001874068	ESS LED MR16 4.5-50W 36D 830 100-240V	-20 to +40 °C	-
929001874108	ESS LED MR16 4.5-50W 36D 865 SO 100-240V	-20 to +40 °C	4.5 kWh




Essential LED spot MR16



Accent Diagrams




Accent Diagram - ESS LED MR16 4.5-50W 36D 865 SO 100-240V




Accent Diagram - Essential LED 5-50W 2700K MR16 24D

Beam Diagrams



Beam diagram - Essential LED 5-50W 2700K MR16 24D



Beam diagram - ESS LED MR16 4.5-50W 36D 865 SO 100-240V

