



EcoAccent - Enhance the Retail Experience

EcoAccent ST271T

EcoAccent is the LED solution for shop targeting energy savings. With a system efficacy of 95 lm/W in average, delivering more than 40% energy efficient compared to CDM solution. EcoAccent helps save energy and at the same time provides excellent lighting for retail environment thus enhancing the retail experience. The option of different light distribution for Accent light and variety of lumen packs and colour temperatures makes it an ideal solution for retail lighting.

Benefits

- Plenty of choices in form factor, lumen output and optics
- Energy saving: more than 40% energy efficient compared to CDM solution
- 1 on 1 replacement over conventional CDM light

Features

- System efficacy up to 95 lm/W
- CRI 80
- CRI 90 optional for 3000K (CrispWhite Tech)
- High reliability 30k hours


Application

- Office
- Shop
- Hospitality
- Healthcare
- Industrial
- Public indoor space

Warnings and Safety

- To be used in Indoor Environment only

Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	100 lm/W
Optic type	Beam angle 12 to 36°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Aluminum and polycarbonate
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	0 to +45 °C
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Beam angle of	Correlated Color	Luminous Flux
		light source	Temperature (Nom)	
919515810925	ST271T LED20/830 PSU-E NB 1C BK	12 degree(s)	3000 K	2,000 lm
919515810926	ST271T LED20/830 PSU-E MB 1C BK	24 degree(s)	3000 K	2,000 lm
919515810927	ST271T LED20/830 PSU-E WB 1C BK	36 degree(s)	3000 K	2,000 lm
919515810928	ST271T LED20/840 PSU-E NB 1C BK	12 degree(s)	4000 K	2,000 lm
919515810929	ST271T LED20/840 PSU-E MB 1C BK	24 degree(s)	4000 K	2,000 lm
919515810930	ST271T LED20/840 PSU-E WB 1C BK	36 degree(s)	4000 K	2,000 lm
919515810933	ST271T LED20/850 PSU-E WB 1C BK	36 degree(s)	5000 K	2,000 lm
919515810934	ST271T LED40/830 PSU-E NB 1C BK	12 degree(s)	3000 K	4,000 lm
919515810936	ST271T LED40/830 PSU-E WB 1C BK	36 degree(s)	3000 K	4,000 lm
919515810938	ST271T LED40/840 PSU-E MB 1C BK	24 degree(s)	4000 K	4,000 lm
919515810939	ST271T LED40/840 PSU-E WB 1C BK	36 degree(s)	4000 K	4,000 lm
919515810940	ST271T LED40/850 PSU-E NB 1C BK	12 degree(s)	5000 K	4,000 lm
919515810941	ST271T LED40/850 PSU-E MB 1C BK	24 degree(s)	5000 K	4,000 lm
919515811221	ST271T LED20/840 PSU-E MB 1C WH	24 degree(s)	4000 K	2,000 lm
919515811222	ST271T LED20/830 PSU-E MB 1C WH	24 degree(s)	3000 K	2,000 lm
919515811224	ST271T LED20/840 PSU-E WB 1C WH	36 degree(s)	4000 K	2,000 lm
919515811229	ST271T LED40/850 PSU-E MB 1C WH	24 degree(s)	5000 K	4,000 lm
919515811230	ST271T LED40/840 PSU-E MB 1C WH	24 degree(s)	4000 K	4,000 lm
919515811231	ST271T LED40/830 PSU-E MB 1C WH	24 degree(s)	3000 K	4,000 lm
919515811233	ST271T LED40/840 PSU-E WB 1C WH	36 degree(s)	4000 K	4,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
919515810925	ST271T LED20/830 PSU-E NB 1C BK	22 W	919515810933	ST271T LED20/850 PSU-E WB 1C BK	22 W
919515810926	ST271T LED20/830 PSU-E MB 1C BK	22 W	919515810934	ST271T LED40/830 PSU-E NB 1C BK	42 W
919515810927	ST271T LED20/830 PSU-E WB 1C BK	22 W	919515810936	ST271T LED40/830 PSU-E WB 1C BK	42 W
919515810928	ST271T LED20/840 PSU-E NB 1C BK	22 W	919515810938	ST271T LED40/840 PSU-E MB 1C BK	42 W
919515810929	ST271T LED20/840 PSU-E MB 1C BK	22 W	919515810939	ST271T LED40/840 PSU-E WB 1C BK	42 W
919515810930	ST271T LED20/840 PSU-E WB 1C BK	22 W	919515810940	ST271T LED40/850 PSU-E NB 1C BK	42 W

EcoAccent ST271T

Order Code	Full Product Name	Power Consumption
919515810941	ST271T LED40/850 PSU-E MB 1C BK	42 W
919515811221	ST271T LED20/840 PSU-E MB 1C WH	22 W
919515811222	ST271T LED20/830 PSU-E MB 1C WH	22 W
919515811224	ST271T LED20/840 PSU-E WB 1C WH	22 W

Order Code	Full Product Name	Power Consumption
919515811229	ST271T LED40/850 PSU-E MB 1C WH	42 W
919515811230	ST271T LED40/840 PSU-E MB 1C WH	42 W
919515811231	ST271T LED40/830 PSU-E MB 1C WH	42 W
919515811233	ST271T LED40/840 PSU-E WB 1C WH	42 W

Mechanical and Housing

Order Code	Full Product Name	Housing Color
919515810925	ST271T LED20/830 PSU-E NB 1C BK	Black
919515810926	ST271T LED20/830 PSU-E MB 1C BK	Black
919515810927	ST271T LED20/830 PSU-E WB 1C BK	Black
919515810928	ST271T LED20/840 PSU-E NB 1C BK	Black
919515810929	ST271T LED20/840 PSU-E MB 1C BK	Black
919515810930	ST271T LED20/840 PSU-E WB 1C BK	Black
919515810933	ST271T LED20/850 PSU-E WB 1C BK	Black
919515810934	ST271T LED40/830 PSU-E NB 1C BK	Black
919515810936	ST271T LED40/830 PSU-E WB 1C BK	Black
919515810938	ST271T LED40/840 PSU-E MB 1C BK	Black

Order Code	Full Product Name	Housing Color
919515810939	ST271T LED40/840 PSU-E WB 1C BK	Black
919515810940	ST271T LED40/850 PSU-E NB 1C BK	Black
919515810941	ST271T LED40/850 PSU-E MB 1C BK	Black
919515811221	ST271T LED20/840 PSU-E MB 1C WH	White
919515811222	ST271T LED20/830 PSU-E MB 1C WH	White
919515811224	ST271T LED20/840 PSU-E WB 1C WH	White
919515811229	ST271T LED40/850 PSU-E MB 1C WH	White
919515811230	ST271T LED40/840 PSU-E MB 1C WH	White
919515811231	ST271T LED40/830 PSU-E MB 1C WH	White
919515811233	ST271T LED40/840 PSU-E WB 1C WH	White

