PHILIPS

SceneSwitch LED spot

7178651

Switch light settings without switching spots

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LEDspot, you can have different light settings from just one spot. And you don’t need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that’s your existing switch! No extra installation is required.

Benefits

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Auto memory: recall your last setting automatically

Applications

- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)
- Accent and general lighting (e.g. hotels, shops and offices)

Features

- Multiple light settings in one lamp
- Plug and play
- Built-in memory chip

Versions

CorePro LEDspot MV 25W
GU10 830 36D

Dimensional drawing



Product	D	C
LED SSW 50W GU10 WW 36D RF ND SRT4	50 mm	54 mm

General Information

Cap-Base	GU10
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)

Light Technical

Color Code	827/825/822 [CCT of 2700K/2500K/2200K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	355 lm
Luminous Intensity (Nom)	600 cd
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.8 W
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	75 °C

Controls and Dimming

Dimmable	No

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	PAR16

Approval and Application

Energy Consumption kWh/1000 h	5 kWh

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)
30778000	LED SceneSwitch 50W GU10 WW 36D RF ND SRT4	2700 K 2500 K 2200 K

© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.