



The professional LEDtube T5 rewiring solution

CorePro LED tube Mains T5

The professional LEDtube MainsFit is a better LED solution suitable for replacing T5 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Benefits

- Low total cost of ownership
- Easy upgrade to LED lighting technology
- Great solution to replace all existing fluorescent T5 lamps without consideration of ballast compatibility

Features

- DLC certified
- Reliable performance throughout 50,000hrs
- Easy double-end rewiring installation to replace existing T5 lamps
- T5 form factor to fit into most of the existing luminaires
- No mercury

Application

- Office
- Retail stores
- Industrial workshop
- Warehouses


CorePro LED tube Mains T5

Versions



ESSENTIAL LEDtube 8-16W G5
830-865 APR

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 16W830 G5 I APR	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
CorePro LEDtube 1200mm 16W840 G5 I APR	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
CorePro LEDtube 1200mm 16W865 G5 I APR	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
CorePro LEDtube 600mm 8W830 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
CorePro LEDtube 600mm 8W840 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
CorePro LEDtube 600mm 8W865 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm

General Information

Cap-Base	G5
Switching Cycle	50,000
Nominal lifetime	30,000 hour(s)

Light Technical

Beam Angle (Nom)	200 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Shape	T5
------------	----

Approval and Application

Ambient temperature range	-20 °C to 45 °C
---------------------------	-----------------

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	3000 K	830	1,000 lm
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	4000 K	840	1,050 lm
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	6500 K	865	1,050 lm
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	3000 K	830	2,000 lm
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	4000 K	840	2,100 lm
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	6500 K	865	2,100 lm

Operating and Electrical







CorePro LED tube Mains T5

Order Code	Full Product Name	Power Consumption
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	8 W
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	8 W
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	8 W

Order Code	Full Product Name	Power Consumption
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	16 W
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	16 W
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	16 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001380608	CorePro LEDtube 600mm 8W830 G5 I APR	8 kWh
929001380708	CorePro LEDtube 600mm 8W840 G5 I APR	8 kWh
929001380808	CorePro LEDtube 600mm 8W865 G5 I APR	8 kWh
929001380908	CorePro LEDtube 1200mm 16W830 G5 I APR	16 kWh
929001381008	CorePro LEDtube 1200mm 16W840 G5 I APR	16 kWh
929001381108	CorePro LEDtube 1200mm 16W865 G5 I APR	16 kWh



CorePro LED tube Mains T5

