

LED PAR38

7403300



Everything you value in a Halogen PAR38 with the benefits of LED. Accent your merchandise or space without distraction.

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 8 to 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Applications

- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Features


- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

Versions



LEDspots GM 1 PAR38 E27

Dimensional drawing



Product	D	C
13PAR38/S/13W/927 40D E27 ND/G/110-277V	122 mm	137 mm

General Information

Cap-Base	E27
Nominal lifetime	15,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h

Light Technical

Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	1,200 lm
Luminous Intensity (Nom)	2,231 cd
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	13 W
Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	65 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	PAR38

Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------