

LED BR40

7403317



Attractive, dimmable, and affordable LED BR40 lamp solution

Philips BR40 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with available high 90+ color rendering (CRI)
- Certain offerings feature a warm glow effect that provides an incandescent-like glow, while maintaining CRI throughout dimming range

Applications

- Hotels/Motels
- Restaurants
- Offices

Features

- Available smooth dimming options
- Traditional look and feel of size, shape, and material


- Up to 25,000-hour rated average life
- Instant on

Versions



LEDbulb, Basic BR40 E26

Dimensional drawing



Product	D	C
13.3BR40/PER/927-22/P/E26/WG 6/1CT T20	125 mm	162 mm
13.3BR40/PER/927/P/E26/DIM 6/1CT T20	125 mm	162 mm
13.3BR40/PER/930/P/E26/DIM 6/1CT T20	125 mm	162 mm
13.3BR40/PER/940/P/E26/DIM 6/1CT T20	125 mm	162 mm
13.3BR40/PER/950/P/E26/DIM 6/1CT T20	125 mm	162 mm

General Information

Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000

Light Technical

Beam Angle (Nom)	110 degree(s)
Luminous Flux	1,204 lm
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	13.3 W
Wattage Equivalent	86 W
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	BR40

Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Light Technical

Order Code	Full Product Name	Color Code	Correlated Color Temperature (Nom)
929003477104	13.3BR40/PER/927-22/P/E26/WG 6/1CT T20	922-927	2200 K 2700 K
929003477204	13.3BR40/PER/927/P/E26/DIM 6/1CT T20	927	2700 K
929003477304	13.3BR40/PER/930/P/E26/DIM 6/1CT T20	930	3000 K
929003477404	13.3BR40/PER/940/P/E26/DIM 6/1CT T20	940	4000 K
929003477504	13.3BR40/PER/950/P/E26/DIM 6/1CT T20	950	5000 K