



Robust, connectable luminaire with outstanding performance.

The Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in car parks and warehouses. The Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and a broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimised light scheme planning. They are also designed with a circular approach, which means that these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick-and-easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency,

energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

Applications

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

Versions

Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.
- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.



Pacific LED gen5, L1800



Pacific LED gen5, L1200




Pacific LED gen5, L1600




Pacific LED gen5, L700


Dimensional drawing




PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole




PACIFIC LED PRO - 840 neutral white - Power supply unit with DALI interface - Wide beam - Push-in connector 7-pole




PACIFIC LED PRO - 840 neutral white - Sensor ready driver InterAct System ready - Wide beam - Push-in connector 5-pole




PACIFIC LED PRO - 840 neutral white - Power supply unit with DALI interface - Wide beam - Push-in connector 5-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit with DALI interface - Wide beam - Push-in connector 5-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit with DALI interface - Wide beam - Push-in connector 7-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole

Product details



Pacific LED gen5, looping connection, 2 entry on one side



Pacific LED gen5 with push in 7-pole (PI7) connector



Pacific LED gen5 with push in 5-pole (PI5) connecto

General Information

Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Embedded control	InterAct SC100 sensor
------------------	-----------------------

Mechanical and Housing

Housing Color	White
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC plus mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-25 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3

Product Data

Product family code	WT490C [Pacific LED gen5]
---------------------	---------------------------

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)	Optic type
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	8,000 lm	165 lm/W	Wide beam
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	8,000 lm	165 lm/W	Wide beam
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	8,000 lm	165 lm/W	Wide beam
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	8,000 lm	165 lm/W	Very wide beam
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	8,000 lm	165 lm/W	Very wide beam
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	8,000 lm	165 lm/W	Wide beam
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	8,000 lm	165 lm/W	Wide beam
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	4,200 lm	162 lm/W	Wide beam
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	6,400 lm	160 lm/W	Wide beam
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	6,400 lm	160 lm/W	Wide beam
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	6,400 lm	160 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)	Optic type
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	6,400 lm	162 lm/W	Wide beam
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	6,400 lm	162 lm/W	Wide beam
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	6,400 lm	162 lm/W	Wide beam
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	6,400 lm	160 lm/W	Very wide beam
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	6,400 lm	162 lm/W	Very wide beam
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	8,000 lm	157 lm/W	Wide beam
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	8,000 lm	157 lm/W	Wide beam
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	8,000 lm	157 lm/W	Wide beam
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	8,000 lm	157 lm/W	Wide beam
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	8,000 lm	157 lm/W	Wide beam
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	8,000 lm	157 lm/W	Very wide beam
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	8,000 lm	157 lm/W	Very wide beam
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	4,200 lm	165 lm/W	Wide beam
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	6,400 lm	160 lm/W	Wide beam
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	8,000 lm	157 lm/W	Wide beam
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	4,200 lm	162 lm/W	Very wide beam
910925868412	WT490C 64S/840 PSD HE WB PI5 L1600	6,400 lm	162 lm/W	Wide beam
910925868413	WT490C 64S/840 PSU HE WB TW3 PI5L1600	6,400 lm	160 lm/W	Wide beam
910925868414	WT490C 64S/840 PSU HE WB PI5 L1600	6,400 lm	160 lm/W	Wide beam
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	8,000 lm	157 lm/W	Wide beam
910925868416	WT490C 80S/840 PSD HE WB PI5 L1600	8,000 lm	157 lm/W	Wide beam
910925868417	WT490C 80S/840 PSU HE WB TW3 PI5L1600	8,000 lm	157 lm/W	Wide beam
910925868692	WT490C 35S/840 PSU HE WB PI5 L1600	3,500 lm	159 lm/W	Wide beam
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	2,300 lm	160 lm/W	Wide beam
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	2,300 lm	151 lm/W	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	48.5 W
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	48.5 W
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	48.5 W
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	48.5 W
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	48.5 W
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	48.5 W
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	48.5 W
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	26 W
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	40 W
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	40 W
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	40 W
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	39.5 W
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	39.5 W


Order Code	Full Product Name	Power Consumption
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	39.5 W
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	40 W
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	39.5 W
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	51 W
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	51 W
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	51 W
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	51 W
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	51 W
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	51 W
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	51 W
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	25.5 W
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	40 W
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	51 W
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	26 W
910925868412	WT490C 64S/840 PSD HE WB PI5 L1600	39.5 W
910925868413	WT490C 64S/840 PSU HE WB TW3 PI5L1600	40 W
910925868414	WT490C 64S/840 PSU HE WB PI5 L1600	40 W
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	51 W
910925868416	WT490C 80S/840 PSD HE WB PI5 L1600	51 W
910925868417	WT490C 80S/840 PSU HE WB TW3 PI5L1600	51 W
910925868692	WT490C 35S/840 PSU HE WB PI5 L1600	22 W
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	14.4 W
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	15.2 W

Controls and Dimming


Order Code	Full Product Name	Dimmable
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	No
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	Yes
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	Yes
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	No
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	Yes
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	No
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	Yes
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	Yes
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	No
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	No
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	No
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	Yes
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	Yes
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	Yes
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	No

Order Code	Full Product Name	Dimmable
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	Yes
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	No
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	No
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	Yes
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	Yes
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	Yes
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	No
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	Yes
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	No
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	No
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	No
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	Yes
910925868412	WT490C 64S/840 PSD HE WB PI5 L1600	Yes
910925868413	WT490C 64S/840 PSU HE WB TW3 PI5L1600	No
910925868414	WT490C 64S/840 PSU HE WB PI5 L1600	No
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	No
910925868416	WT490C 80S/840 PSD HE WB PI5 L1600	Yes
910925868417	WT490C 80S/840 PSU HE WB TW3 PI5L1600	No
910925868692	WT490C 35S/840 PSU HE WB PI5 L1600	No
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	Yes
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	No


Polar normal diagrams




WT490CI - 910925868292




WT490CI - 910925868413




WT490CI - 910925868692




WT490CI - 910925868288




WT490CI - 910925868414




WT490CI - 910925868516




WT490CI - 910925868509




WT490CI - 910925867704




WT490CI - 910925867735




WT490CI - 910925867712




WT490CI - 910925867724




WT490CI - 910925867726




WT490CI - 910925867738




WT490CI - 910925867713




WT490CI - 910925867717




WT490CI - 910925867714




WT490CI - 910925867739




WT490CI - 910925867708




WT490CI - 910925867725




WT490CI - 910925867718




WT490CI - 910925867721




WT490CI - 910925867729




WT490CI - 910925868287




WT490CI - 910925868289




WT490CI - 910925868290




WT490CI - 910925868412




WT490CI - 910925868416




WT490CI - 910925867703




WT490CI - 910925867707




WT490CI - 910925867709




WT490CI - 910925867722




WT490CI - 910925867728




WT490CI - 910925867733



WT490CI - 910925867736



WT490CI - 910925868415



WT490CI - 910925868417