



# Robust, connectable luminaire with outstanding performance.

## Pacific LED Gen5

Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in parking garages and warehouses. Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency, and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency, energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

# Pacific LED Gen5

## Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

## Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.

## Application

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

## Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.




## Versions



Pacific LED gen5, ATEX 2/22,  
Wieland connector

# Pacific LED Gen5

## Dimensional drawing



## Product details



Pacific LED gen5 with Wieland connector

# Pacific LED Gen5

## General Information

Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes

## Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Optic type	Wide beam

## Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Explosion hazard class	Zone 2 and 22
Housing Color	White
Mech. impact protection code	IK08
Ingress protection code	IP66

## Approval and Application

Ambient temperature range	-25 to +45 °C
CE mark	Yes
ENEC mark	ENEC plus mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

## Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-7%

## Product Data

Product family code	WT492C
---------------------	--------

## Light Technical


Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868704	WT492C 64S/840 PSU WB W5 L1200	160 lm/W	6,400 lm
910925868705	WT492C 80S/840 PSU WB W5 L1800	165 lm/W	8,000 lm

## Operating and Electrical


Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910925868704	WT492C 64S/840 PSU WB W5 L1200	40 W	910925868705	WT492C 80S/840 PSU WB W5 L1800	49 W

# Pacific LED Gen5

## Polar Wide Diagrams



**Polar Normal (separate) - WT490C1 - 910925868705**



**Polar Normal (separate) - WT490C1 - 910925868704**

