



The cost-effective LED replacement for HID and SON Road lamps with MASTER - LED HID SON-T

CorePro - LED HID SON-T

The Philips CorePro LED HID SON-T lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. This new generation of products brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant saving with a low initial investment.

Furthermore, they're designed to have the same lamp size and light distribution as other HID lamps, so you will never know the difference. All thanks to our HighPower LED filament technology. Plus, its unique IP65 design means it can be used for outdoor applications

Benefits

- Cost-saving lamps with short payback time
- Low initial investment
- Easy way to enhance lighting quality

CorePro - LED HID SON-T

Features

- High Energy efficient lamps
- Long lifetime - 25,000 hrs
- Surge protection 2KV
- Pleasant white light with CRI 70
- Omnidirectional light around lamp
- Additional Energy saving by Direct Mains connection
- IP65 product (IP rated sockets required for outdoor application)

Application

- Road and Street
- Tunnel
- Parking Garages

Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Versions




LEDTForce Core road Tshape E27 1



LEDTForce MAS SONT EU1




Dimensional drawing



Product	D	C
TForce Core LED road 49W 740 E40 MV	53.5 mm	232 mm

CorePro - LED HID SON-T

Dimensional drawing



Product	D	C
TForce Core LED road 40W 730 E40 MV	46 mm	225 mm
TForce Core LED road 40W 740 E40 MV	46 mm	225 mm

Product	D	C
TForce Core LED road 17W 730 E27 MV	38.5 mm	168 mm
TForce Core LED road 17W 740 E27 MV	38.5 mm	168 mm

Product	D	C
TForce Core LED road 26W 740 E27 MV	38.5 mm	213 mm

CorePro - LED HID SON-T

General Information

Nominal lifetime	25,000 hour(s)
------------------	----------------

Light Technical

Beam Angle (Nom)	330 degree(s)
------------------	---------------

Color rendering index (CRI)	70
-----------------------------	----

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical

Input Frequency	50 to 60 Hz
-----------------	-------------

Starting Time (Nom)	0.5 s
---------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Approval and Application

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
929002485102	TForce Core LED road 26W 740 E27 MV	E27	15,000
929002484802	TForce Core LED road 17W 730 E27 MV	E27	50,000
929002484902	TForce Core LED road 17W 740 E27 MV	E27	50,000
929002485202	TForce Core LED road 40W 730 E40 MV	E40	50,000
929002485302	TForce Core LED road 40W 740 E40 MV	E40	50,000
929003775702	TForce Core LED road 49W 740 E40 MV	E40	50,000

Light Technical

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929002485102	TForce Core LED road 26W 740 E27 MV	4000 K	740	4,500 lm
929002484802	TForce Core LED road 17W 730 E27 MV	3000 K	730	2,800 lm
929002484902	TForce Core LED road 17W 740 E27 MV	4000 K	740	3,000 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929002485202	TForce Core LED road 40W 730 E40 MV	3000 K	730	7,200 lm
929002485302	TForce Core LED road 40W 740 E40 MV	4000 K	740	7,500 lm
929003775702	TForce Core LED road 49W 740 E40 MV	4000 K	740	10,000 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002485102	TForce Core LED road 26W 740 E27 MV	50 to 60 Hz	26 W
929002484802	TForce Core LED road 17W 730 E27 MV	50 to 60 Hz	17 W
929002484902	TForce Core LED road 17W 740 E27 MV	50 to 60 Hz	17 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002485202	TForce Core LED road 40W 730 E40 MV	50 to 60 Hz	40 W
929002485302	TForce Core LED road 40W 740 E40 MV	50 to 60 Hz	40 W
929003775702	TForce Core LED road 49W 740 E40 MV	-	49 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002485102	TForce Core LED road 26W 740 E27 MV	44.55 °C
929002484802	TForce Core LED road 17W 730 E27 MV	36.8 °C
929002484902	TForce Core LED road 17W 740 E27 MV	36.8 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002485202	TForce Core LED road 40W 730 E40 MV	49 °C
929002485302	TForce Core LED road 40W 740 E40 MV	49 °C
929003775702	TForce Core LED road 49W 740 E40 MV	45 °C

Mechanical and Housing

CorePro - LED HID SON-T

Order Code	Full Product Name	Bulb Shape
929002485102	TForce Core LED road 26W 740 E27 MV	T-shape
929002484802	TForce Core LED road 17W 730 E27 MV	Tubular
929002484902	TForce Core LED road 17W 740 E27 MV	Tubular

Order Code	Full Product Name	Bulb Shape
929002485202	TForce Core LED road 40W 730 E40 MV	Tubular
929002485302	TForce Core LED road 40W 740 E40 MV	Tubular
929003775702	TForce Core LED road 49W 740 E40 MV	Tubular

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002485102	TForce Core LED road 26W 740 E27 MV	26 kWh
929002484802	TForce Core LED road 17W 730 E27 MV	17 kWh
929002484902	TForce Core LED road 17W 740 E27 MV	17 kWh
929002485202	TForce Core LED road 40W 730 E40 MV	40 kWh
929002485302	TForce Core LED road 40W 740 E40 MV	40 kWh
929003775702	TForce Core LED road 49W 740 E40 MV	49 kWh

