



Our most efficient LED Spot

MASTER LEDspot GU10 UltraEfficient

With Philips Ultra Efficient GU10 LED spots, you have the perfect retrofit lamp to help your customers save energy and money with high quality, long-lasting and ultra energy-efficient LED.

Benefits

- Create warm and comfortable ambience
- A hassle-free retrofit solution for greater energy efficiency and sustainability
- Interior decor, furnishings and fabrics look great

Features

- Customised colour spectrum replicates halogen light colour
- Easy retrofitable with GU10 socket
- Long lifetime of 50,000 hours

Application

- Hospitality: hotel guest rooms, corridors, lobbies, reception areas, restaurants, bars, cafes
- Home: living room, bedrooms, hallway
- Retail: exhibitions, display cabinets, shops, dressing rooms



MASTER LEDspot GU10 UltraEfficient

Versions



LEDspots MAS EU PAR16 GU10

Dimensional drawing



Product	D	C
MAS LEDspot UE 2.1-50W GU10 ND 827 EELA	50 mm	54 mm
MAS LEDspot UE 2.1-50W GU10 ND 840 EELA	50 mm	54 mm

Product	D	C
MAS LEDspot UE 2.1-50W GU10 DIM 827 EELA	50 mm	54 mm
MAS LEDspot UE 2.1-50W GU10 DIM 830 EELA	50 mm	54 mm
MAS LEDspot UE 2.1-50W GU10 DIM 840 EELA	50 mm	54 mm

MASTER LEDspot GU10 UltraEfficient

General Information

Cap base	GU10
Switching Cycle	50,000
Nominal lifetime	50,000 h

Light Technical

Beam angle (nom.)	36 degree(s)
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux	375 lm

Operating and Electrical

Input frequency	50 to 60 Hz
Power Consumption	2.1 W
Starting time (nom.)	0.5 s
Wattage equivalent	50 W

Temperature

T-Case maximum (nom.)	50 °C
-----------------------	-------

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	PAR16

Approval and Application

Ambient temperature range	-20 to +45 °C
Energy consumption kWh/1,000 hours	3 kWh

Light Technical

Order Code	Full Product Name	Correlated Colour Temperature (Nom)	Colour Code	Luminous intensity (nom.)
929003610102	MAS LEDspot UE 2.1-50W GU10 ND 840 EELA	4000 K	840	680 cd
929003634602	MAS LEDspot UE 2.1-50W GU10 ND 827 EELA	2700 K	827	680 cd
929003795902	MAS LEDspot UE 2.1-50W GU10 DIM 827 EELA	2700 K	827	650 cd
929003796002	MAS LEDspot UE 2.1-50W GU10 DIM 830 EELA	3000 K	830	650 cd
929003796102	MAS LEDspot UE 2.1-50W GU10 DIM 840 EELA	4000 K	840	650 cd


Operating and Electrical

Order Code	Full Product Name	Line Frequency
929003610102	MAS LEDspot UE 2.1-50W GU10 ND 840 EELA	50 to 60 Hz
929003634602	MAS LEDspot UE 2.1-50W GU10 ND 827 EELA	50 to 60 Hz
929003795902	MAS LEDspot UE 2.1-50W GU10 DIM 827 EELA	-



Order Code	Full Product Name	Line Frequency
929003796002	MAS LEDspot UE 2.1-50W GU10 DIM 830 EELA	-
929003796102	MAS LEDspot UE 2.1-50W GU10 DIM 840 EELA	-

Controls and Dimming


Order Code	Full Product Name	Dimmable
929003610102	MAS LEDspot UE 2.1-50W GU10 ND 840 EELA	No
929003634602	MAS LEDspot UE 2.1-50W GU10 ND 827 EELA	No
929003795902	MAS LEDspot UE 2.1-50W GU10 DIM 827 EELA	Only with specific dimmers
929003796002	MAS LEDspot UE 2.1-50W GU10 DIM 830 EELA	Only with specific dimmers
929003796102	MAS LEDspot UE 2.1-50W GU10 DIM 840 EELA	Only with specific dimmers




MASTER LEDspot GU10 UltraEfficient




Accent Diagrams




Accent Diagram - MAS LEDspot UE 2.1-50W
GU10 ND 840 EELA



Accent Diagram - MAS LEDspot UE 2.1-50W
GU10 DIM 840 EELA



Accent Diagram - MAS LEDspot UE 2.1-50W
GU10 DIM 830 EELA




Accent Diagram - MAS LEDspot UE 2.1-50W
GU10 ND 827 EELA




Accent Diagram - MAS LEDspot UE 2.1-50W
GU10 DIM 827 EELA

MASTER LEDspot GU10 UltraEfficient


Beam Diagrams




Beam diagram - MAS LEDspot UE 2.1-50W
GU10 ND 840 EELA




Beam diagram - MAS LEDspot UE 2.1-50W
GU10 DIM 840 EELA



Beam diagram - MAS LEDspot UE 2.1-50W
GU10 DIM 827 EELA



Beam diagram - MAS LEDspot UE 2.1-50W
GU10 ND 827 EELA



Beam diagram - MAS LEDspot UE 2.1-50W
GU10 DIM 830 EELA

