



Creating attractive inner-city landscapes

OptiSpace is a creative bollard solution which enables you to build a more attractive, citizen-centric inner-city space by avoiding verticalization of the urban landscape. OptiSpace delivers all this and more while delivering an attractive TCO for your investment. Enabled by the different control options you can reduce energy consumption and minimize TCO further and thanks to the excellent and optimized light distribution options you can maximize spacing between the bollards, thereby minimizing the number of light points needed to be installed. To support different design schemes, OptiSpace is also available in different colors: Ultra Dark Grey is the standard color and other colors are available on request.

Benefits

- Discreet design nicely blending into modern inner-city spaces
- Attractive Total Cost of Ownership
- Compliant with key national and international regulation in Europe

Applications

- Parks and plazas
- Pedestrian and cycle paths
- Building fronts and car parks

Features

- Enabling wide spacing, up to 20 meters
- Delivering up to 4300 lm light output
- IP66 and IK10 ratings

- Warm White (WW) / Neutral White (NW) color temperature options
- Choice of both asymmetric and symmetric optics
- Ground section accessory

Versions



OptiSpace-BCB500 ANB


Dimensional drawing



OPTISPACE BOLLARD – LED module 2700 lm



OPTISPACE BOLLARD – LED module 2700 lm



OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD - LED module 2700 lm




OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD – LED module 2700 lm

Product details

OptiSpace-BCB500
-5DPP.TIF



OptiSpace-BCB500
-1DPP.TIF



OptiSpace-BCB500
-9DPP.TIF



OptiSpace-BCB500
-7DPP.TIF





OptiSpace-BCB500
-2DPP.TIF



OptiSpace-BCB500
-3DPP.TIF



OptiSpace-BCB500
-4DPP.TIF



OptiSpace Sparepart



OptiSpace-BCB500
-6DPP.TIF



OptiSpace-BCB500
-10DPP.TIF

General Information

Lamp family code	LED27 [LED module 2700 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	2,400 lm
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	70
Light source color	740 neutral white
Luminaire light beam spread	7° - 9° x 177°
Optic type outdoor	Asymmetrical

Operating and Electrical

Power Consumption	20 W
Surge Protection (Common/Differential)	Surge protection level until 6 kV differential mode and 6 kV common mode

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Black
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Polycarbonate cover and gloss high-reflective optic

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes


Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
-------------------------------	-------

Product Data

Product family code	BCB500 [OPTISPACE BOLLARD]
---------------------	----------------------------

Polar normal diagrams



BCB500I - 912300024103