

UniStrip G4

BCP385



UniStrip G4 - Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection


Applications

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort
- For outdoor use only

Versions



Dimensional drawing




BCP386 L300

BCP386 L1000




BCP381

Product details







UniStrip G4 Detail Photo




UniStrip G4 Detail Photo




UniStrip G4 Detail Photo





UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3731 Detail Photo



UniStrip G4 Detail Photo



159A3710 Detail Photo



159A3691 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



General Information

Light source replaceable	No
Driver included	No

Light Technical

Color rendering index (CRI)	80
Luminaire light beam spread	40° x 40°

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
51371699	BCP386 12LED 30K 24V A11 L30	195 lm	3000 K	Warm white
51417199	BCP386 60LED 40K 24V 60 L100	1,045 lm	4000 K	Neutral white
72675899	BCP381 24LED 40K 24V 40 L100	1,783 lm	4000 K	Neutral white

Operating and Electrical

Order Code	Full Product Name	Power Consumption
51371699	BCP386 12LED 30K 24V A11 L30	3 W
51417199	BCP386 60LED 40K 24V 60 L100	15 W
72675899	BCP381 24LED 40K 24V 40 L100	24 W

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
51371699	BCP386 12LED 30K 24V A11 L30	Clear glass
51417199	BCP386 60LED 40K 24V 60 L100	Clear glass
72675899	BCP381 24LED 40K 24V 40 L100	Clear flat

