



# **UniStrip G4 - Best in Class Linear LED Surface Mounted Luminaires for Exterior Fixed and Dynamic Architectural Lighting Applications**

## **UniStrip G4**

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### **Benefits**

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection

# UniStrip G4

## Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort




## Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

## Warnings and Safety

- For outdoor use only

## Dimensional drawing



## Product details

UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



# UniStrip G4

## Product details

UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3710 Detail Photo



UniStrip G4 Detail Photo



159A3691 Detail Photo



UniStrip G4 Detail Photo

UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo

159A3731 Detail Photo



# UniStrip G4

General Information	
Driver included	No
Light Technical	
Color rendering index (CRI)	80
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes

## General Information

Order Code	Full Product Name	Light source replaceable
51371699	BCP386 12LED 30K 24V A11 L30	-
51417199	BCP386 60LED 40K 24V 60 L100	-

Order Code	Full Product Name	Light source replaceable
72675899	BCP381 24LED 40K 24V 40 L100	No
72598099	BCP382 18LED 40K 24V 17 L50	No

## Light Technical

Order Code	Name	Correlated				
		Luminaire	Light	Color	Temperature	Luminous
		Full Product	light beam	source	(Nom)	Flux
51371699	BCP386 12LED	-	Warm	3000 K	195 lm	
	30K 24V A11		white			
	L30					
51417199	BCP386 60LED	-	Neutral	4000 K	1,045 lm	
	40K 24V 60		white			
	L100					

Order Code	Name	Correlated				
		Luminaire	Light	Color	Temperature	Luminous
		Full Product	light beam	source	(Nom)	Flux
72675899	BCP381 24LED	40° x 40°	Neutral	4000 K	1,783 lm	
	40K 24V 40		white			
	L100					
72598099	BCP382 18LED	17° x 17°	Neutral	4000 K	1,292 lm	
	40K 24V 17 L50		white			

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
51371699	BCP386 12LED 30K 24V A11 L30	3 W
51417199	BCP386 60LED 40K 24V 60 L100	15 W

Order Code	Full Product Name	Power Consumption
72675899	BCP381 24LED 40K 24V 40 L100	24 W
72598099	BCP382 18LED 40K 24V 17 L50	18 W

## Mechanical and Housing

Order Code	Full Product Name	Optical cover type
51371699	BCP386 12LED 30K 24V A11 L30	Clear glass
51417199	BCP386 60LED 40K 24V 60 L100	Clear glass

Order Code	Full Product Name	Optical cover type
72675899	BCP381 24LED 40K 24V 40 L100	Clear flat
72598099	BCP382 18LED 40K 24V 17 L50	Clear flat

## Approval and Application

## UniStrip G4

Order Code	Full Product Name	Flammability mark
51371699	BCP386 12LED 30K 24V A11 L30	-
51417199	BCP386 60LED 40K 24V 60 L100	-
72675899	BCP381 24LED 40K 24V 40 L100	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
72598099	BCP382 18LED 40K 24V 17 L50	For mounting on normally flammable surfaces

