

UniStrip G4

BCP385



UniStrip G4 - Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

UniStrip G4 is a surface-mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colours, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection


Applications

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas


Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort
- For outdoor use only

Versions




Dimensional drawing



Product details




UniStrip G4 Detail Photo




UniStrip G4 Detail Photo




UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3710 Detail Photo



UniStrip G4 Detail Photo



159A3691 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3731 Detail Photo



General Information

Light source replaceable	No
Driver included	No

Mechanical and Housing

Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread
911401779982	BCP386 12LED 27K 24V 60 L30	200 lm	2700 K	80	Warm white	-
911401780062	BCP386 12LED 30K 24V A11 L30	195 lm	3000 K	80	Warm white	-
911401780082	BCP386 12LED 40K 24V A11 L30	205 lm	4000 K	80	Neutral white	-
911401780192	BCP386 30LED 30K 24V 45 L50	490 lm	3000 K	80	Warm white	-
911401780232	BCP386 30LED 27K 24V 60 L50	495 lm	2700 K	80	Warm white	-
911401780292	BCP386 30LED 27K 24V A11 L50	485 lm	2700 K	80	Warm white	-
911401780312	BCP386 30LED 30K 24V A11 L50	485 lm	3000 K	80	Warm white	-
911401780332	BCP386 30LED 40K 24V A11 L50	515 lm	4000 K	80	Neutral white	-
911401780442	BCP386 60LED 30K 24V 45 L100	975 lm	3000 K	80	Warm white	-
911401780482	BCP386 60LED 27K 24V 60 L100	985 lm	2700 K	80	Warm white	-
911401780502	BCP386 60LED 30K 24V 60 L100	985 lm	3000 K	80	Warm white	-

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread
911401780522	BCP386 60LED 40K 24V 60 L100	1,045 lm	4000 K	80	Neutral white	-
911401780562	BCP386 60LED 30K 24V A11 L100	960 lm	3000 K	80	Warm white	-
911401780582	BCP386 60LED 40K 24V A11 L100	1,020 lm	4000 K	80	Neutral white	-
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	730 lm	-	-	Red, green, blue and white	-
911401739422	BCP382 36LED 30K 24V 17 L100	2,345 lm	3000 K	80	Warm white	17° x 17°
911401738642	BCP381 12LED 30K 24V A2 L50	848 lm	3000 K	80	Warm white	16° x 35°
911401738802	BCP381 24LED 30K 24V A2 L100	1,663 lm	3000 K	80	Warm white	16° x 35°

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401779982	BCP386 12LED 27K 24V 60 L30	3 W
911401780062	BCP386 12LED 30K 24V A11 L30	3 W
911401780082	BCP386 12LED 40K 24V A11 L30	3 W
911401780192	BCP386 30LED 30K 24V 45 L50	7.5 W
911401780232	BCP386 30LED 27K 24V 60 L50	7.5 W
911401780292	BCP386 30LED 27K 24V A11 L50	7.5 W
911401780312	BCP386 30LED 30K 24V A11 L50	7.5 W
911401780332	BCP386 30LED 40K 24V A11 L50	7.5 W
911401780442	BCP386 60LED 30K 24V 45 L100	15 W
911401780482	BCP386 60LED 27K 24V 60 L100	15 W
911401780502	BCP386 60LED 30K 24V 60 L100	15 W
911401780522	BCP386 60LED 40K 24V 60 L100	15 W
911401780562	BCP386 60LED 30K 24V A11 L100	15 W
911401780582	BCP386 60LED 40K 24V A11 L100	15 W
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	15 W
911401739422	BCP382 36LED 30K 24V 17 L100	36 W
911401738642	BCP381 12LED 30K 24V A2 L50	12 W
911401738802	BCP381 24LED 30K 24V A2 L100	24 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401779982	BCP386 12LED 27K 24V 60 L30	No
911401780062	BCP386 12LED 30K 24V A11 L30	No
911401780082	BCP386 12LED 40K 24V A11 L30	No
911401780192	BCP386 30LED 30K 24V 45 L50	No
911401780232	BCP386 30LED 27K 24V 60 L50	No
911401780292	BCP386 30LED 27K 24V A11 L50	No
911401780312	BCP386 30LED 30K 24V A11 L50	No

Order Code	Full Product Name	Dimmable
911401780332	BCP386 30LED 40K 24V A11 L50	No
911401780442	BCP386 60LED 30K 24V 45 L100	No
911401780482	BCP386 60LED 27K 24V 60 L100	No
911401780502	BCP386 60LED 30K 24V 60 L100	No
911401780522	BCP386 60LED 40K 24V 60 L100	No
911401780562	BCP386 60LED 30K 24V A11 L100	No
911401780582	BCP386 60LED 40K 24V A11 L100	No
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	Yes
911401739422	BCP382 36LED 30K 24V 17 L100	No
911401738642	BCP381 12LED 30K 24V A2 L50	No
911401738802	BCP381 24LED 30K 24V A2 L100	No

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
911401779982	BCP386 12LED 27K 24V 60 L30	Clear glass
911401780062	BCP386 12LED 30K 24V A11 L30	Clear glass
911401780082	BCP386 12LED 40K 24V A11 L30	Clear glass
911401780192	BCP386 30LED 30K 24V 45 L50	Clear glass
911401780232	BCP386 30LED 27K 24V 60 L50	Clear glass
911401780292	BCP386 30LED 27K 24V A11 L50	Clear glass
911401780312	BCP386 30LED 30K 24V A11 L50	Clear glass
911401780332	BCP386 30LED 40K 24V A11 L50	Clear glass
911401780442	BCP386 60LED 30K 24V 45 L100	Clear glass
911401780482	BCP386 60LED 27K 24V 60 L100	Clear glass
911401780502	BCP386 60LED 30K 24V 60 L100	Clear glass
911401780522	BCP386 60LED 40K 24V 60 L100	Clear glass
911401780562	BCP386 60LED 30K 24V A11 L100	Clear glass
911401780582	BCP386 60LED 40K 24V A11 L100	Clear glass
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	Clear glass
911401739422	BCP382 36LED 30K 24V 17 L100	Clear flat
911401738642	BCP381 12LED 30K 24V A2 L50	Clear flat
911401738802	BCP381 24LED 30K 24V A2 L100	Clear flat