

UniStrip G4

BCP385



UniStrip G4 - Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

UniStrip G4 is a surface-mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colours, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection

Applications

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas


Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort
- For outdoor use only


Versions



Dimensional drawing



Product details



159A3731 Detail Photo



General Information

Driver included No

Light Technical

Color rendering index (CRI) 80

Controls and Dimming

Dimmable No

Mechanical and Housing

Housing Color Dark gray

Ingress protection code IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK06 [1 J]

Optical cover type Clear glass

Approval and Application

CE mark Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
911401779982	BCP386 12LED 27K 24V 60 L30	200 lm	2700 K	Warm white
911401780062	BCP386 12LED 30K 24V A11 L30	195 lm	3000 K	Warm white
911401780082	BCP386 12LED 40K 24V A11 L30	205 lm	4000 K	Neutral white
911401780192	BCP386 30LED 30K 24V 45 L50	490 lm	3000 K	Warm white
911401780232	BCP386 30LED 27K 24V 60 L50	495 lm	2700 K	Warm white
911401780292	BCP386 30LED 27K 24V A11 L50	485 lm	2700 K	Warm white
911401780312	BCP386 30LED 30K 24V A11 L50	485 lm	3000 K	Warm white
911401780332	BCP386 30LED 40K 24V A11 L50	515 lm	4000 K	Neutral white
911401780442	BCP386 60LED 30K 24V 45 L100	975 lm	3000 K	Warm white
911401780482	BCP386 60LED 27K 24V 60 L100	985 lm	2700 K	Warm white
911401780502	BCP386 60LED 30K 24V 60 L100	985 lm	3000 K	Warm white
911401780522	BCP386 60LED 40K 24V 60 L100	1,045 lm	4000 K	Neutral white
911401780562	BCP386 60LED 30K 24V A11 L100	960 lm	3000 K	Warm white
911401780582	BCP386 60LED 40K 24V A11 L100	1,020 lm	4000 K	Neutral white

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401779982	BCP386 12LED 27K 24V 60 L30	3 W
911401780062	BCP386 12LED 30K 24V A11 L30	3 W
911401780082	BCP386 12LED 40K 24V A11 L30	3 W
911401780192	BCP386 30LED 30K 24V 45 L50	7.5 W
911401780232	BCP386 30LED 27K 24V 60 L50	7.5 W
911401780292	BCP386 30LED 27K 24V A11 L50	7.5 W
911401780312	BCP386 30LED 30K 24V A11 L50	7.5 W
911401780332	BCP386 30LED 40K 24V A11 L50	7.5 W
911401780442	BCP386 60LED 30K 24V 45 L100	15 W
911401780482	BCP386 60LED 27K 24V 60 L100	15 W
911401780502	BCP386 60LED 30K 24V 60 L100	15 W
911401780522	BCP386 60LED 40K 24V 60 L100	15 W
911401780562	BCP386 60LED 30K 24V A11 L100	15 W
911401780582	BCP386 60LED 40K 24V A11 L100	15 W