# UniEdge – Make Your Boundaries Stand Out

## UniEdge

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Light Weight and Tiltable Brackets.
- Through Wiring for power and DMX512 Signal.

### Features

- Robust design & IP66 for outdoor applications
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors

### Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

### Warnings and Safety

- For outdoor use only

# UniEdge

## Dimensional drawing



| General Information | |
|---|---|
| **Driver included** | No |

| Light Technical | |
|---|---|
| **Correlated Color Temperature (Nom)** | - |
| **Color rendering index (CRI)** | 80 |

| Operating and Electrical | |
|---|---|
| **Power Consumption** | 10 W |

| Controls and Dimming | |
|---|---|
| **Dimmable** | No |

| Mechanical and Housing | |
|---|---|
| **Optical cover type** | Tempered glass |
| **Housing Color** | Dark gray |
| **Mech. impact protection code** | IK06 |
| **Ingress protection code** | IP66 |

| Approval and Application | |
|---|---|
| **CE mark** | No |
| **Flammability mark** | For mounting on normally flammable surfaces |

## Light Technical

| Order Code | Full Product Name | Light source color | Luminous Flux |
|---|---|---|---|
| 911401737283 | BCP390 4LED 27K 24V 3x90 D3 | Warm white | 118 lm |
| 911401737303 | BCP390 4LED 30K 24V 3x90 D3 | Warm white | 127 lm |
| 911401737323 | BCP390 4LED 40K 24V 3x90 D3 | Neutral white | 144 lm |

© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.