




Direct View Linear Luminaires for Creative Architectural and Media Façade Applications

UniBar is a surface mounted, exterior-rated and slim sized linear LED direct view luminaire that is designed for façade and outdoor architectural lighting applications. The robust mechanical and unique optical design make it ideal for buildings facades, media facades, bridges, overpasses and any application that requires a slim linear direct view lighting solution. Direct view spread lens, through wiring for end-to-end connection and DMX control option available with up to 10 pixels (10IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations. Available in white, monochromatic colors, RGB, RGBW and tunable white.

Benefits

- Low power LEDs deliver a smooth and soft lighting distribution
- Up to 10 pixels (10IDs) for easy and flexible control
- Wide beam angle for direct view application
- Robust Design & IP66 rating for outdoor use
- Two types of mounting brackets to fit different applications

Applications

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape


Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, Monochromatic Colors and Tunable White
- Standard 300, 500 and 1000mm product lengths
- Available in DMX control option

Versions



Dimensional drawing



BCS340 Dimension Drawing (without table)

General Information	
Driver included	No
Light Technical	
Luminous Flux	600 lm
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Light source color	Neutral white
Operating and Electrical	
Power Consumption	12 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Silver
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Opal

Approval and Application

CE mark

Yes