



TownGuide Performer – Designed around your needs

TownGuide Performer

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project's specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

Benefits

- Six recognizable yet modern designs that blend in with, and enhance, their surroundings
- LED light sources, in combination with a wide choice of optics, ensure that the optimal configuration can be obtained for your application. The state-of-the-art LEDs increase visual comfort for motorists, cyclists and pedestrians.
- Considerable reduction in energy usage and carbon footprint compared to HPL mercury, SON-T and PL-L compact fluorescent lamps; further energy savings achievable when using CLO or dimming options (can amount to as much as 80% compared to HPL mercury)

Features

- Dedicated LED luminaire, optimized for minimum Total Cost of Ownership
- Wide choice of lumen packages, ranging from 1,200 to 7,000 lumens (GRN) or 4,000 to 12,000 lumens (ECO)
- Choice of light colors 3000 K (warm white) and 4000 K (neutral white)
- Long lifetime of 100,000 hours (GRN) or 80,000 hours (ECO) at L80B10
- Bayonet whistle connector for easy installation without opening the luminaire
- Suitable for new installations or one-to-one replacement in existing installations
- Vandal-resistant (IK10), ingress protection (IP66)
- TailorFit PCB technology
- Standard 3-year warranty program; as a service, we offer extended warranties or lifecycle services


Application

- Residential areas: residential streets, cycle paths & footpaths, roundabouts, squares, parks & playgrounds, parking areas
- City centers: side streets, squares, parks & playgrounds, cycle paths & footpaths, parking areas, roundabouts, shopping & pedestrian areas
- Area and Transportation: industrial areas, parking areas, petrol stations, airports, harbors, public transport areas
- Sports: parking areas







Versions



Dimensional drawing



Dimensional drawing



Product details

OPDP_BDP100i_0011-Detail
photo




OPDP_BDP100i_0001-Detail
photo

OPDP_BDP100i_0003-Detail
photo



OPDP_BDP100i_0007-Detail
photo



TownGuide Performer

Product details



OPDP_BDP100i_0009-Detail
photo



TownGuide_Performe-
BDP100_105-DPP.TIF

General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Mechanical and Housing	
Mech. impact protection code	IK10
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.5 %

General Information

Order Code	Full Product Name	Lamp family code
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	LED30
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	LED40
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	LED50
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	LED50
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	LED20
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	LED50
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	LED100
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	LED60
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	LED30
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	LED35
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	LED100
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	LED60
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	LED40
31987100	BDP102 LED50/740 DM PCC GR MSP 62P	LED50
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	LED50
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	LED20
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	LED30
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	LED35
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	LED50
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	LED70
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	LED20
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	LED35
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	LED50
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	LED120
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	LED30
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	LED40
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	LED50
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	LED100

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
90608700	BDP100 LED30/740 DN PCC SI CLO- LS-6 76P	32° x 29°	740 neutral white	4000 K	70
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	53° x 71°	830 warm white	3000 K	80
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	75°	830 warm white	3000 K	80
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
90614800	BDP101 LED60/830 II DS PCF SI CLO- DDF2 6	75°	830 warm white	3000 K	80
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
90613100	BDP101 LED60/830 II DM PCC SI CLO- DDF2 6	53° x 71°	830 warm white	3000 K	80
90620900	BDP102 LED40/830 II DW PCC SI CLO- DDF1 6	50° x 70°	830 warm white	3000 K	80
31987100	BDP102 LED50/740 DM PCC GR MSP 62P	53° x 71°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
90622300	BDP102 LED50/830 II DS PCF SI CLO- DDF1 6	75°	830 warm white	3000 K	80
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
90623000	BDP104 LED30/740 II DM PCC SI CLO- LS-8 6	53° x 71°	740 neutral white	4000 K	70
90624700	BDP104 LED40/830 II DS PCF SI CLO- LS-8 6	75°	830 warm white	3000 K	80
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	2,291 lm	4	Distribution narrow	3
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	2,888 lm	4	Distribution medium	3
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	3,700 lm	4	Distribution wide	3
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	1,862 lm	6	Distribution symmetrical	3
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	1,160 lm	4	Distribution wide	3
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	2,576 lm	6	Distribution wide	3
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	4,240 lm	6	Distribution wide	3
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	2,300 lm	8	Distribution symmetrical	15
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	1,798 lm	4	Distribution wide	15
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	2,013 lm	4	Distribution wide	15
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	4,560 lm	6	Distribution wide	15
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	4,424 lm	8	Distribution medium	3
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	3,116 lm	4	Distribution wide	3
31987100	BDP102 LED50/740 DM PCC GR MSP 62P	4,891 lm	4	Distribution medium	3

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	1,900 lm	4	Distribution symmetrical	10
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	1,200 lm	4	Distribution wide	10
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	1,740 lm	4	Distribution wide	10
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	1,947 lm	4	Distribution wide	10
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	2,714 lm	6	Distribution wide	10
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	3,584 lm	8	Distribution wide	10
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	1,060 lm	4	Distribution wide	4
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	1,716 lm	4	Distribution wide	4
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	2,346 lm	6	Distribution wide	4
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	4,800 lm	8	Distribution wide	4
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	2,204 lm	4	Distribution medium	3
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	1,386 lm	3	Distribution symmetrical	3
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	2,208 lm	6	Distribution wide	3
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	3,680 lm	6	Distribution wide	3

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 4 kV differential mode and 4 kV common mode
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	46.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
31987100	BDP102 LED50/740 DM PCC GR MSP 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	54 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	92 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Yes	50%
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Yes	50%
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	Yes	50%
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Yes	50%
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	No	Not applicable
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	No	Not applicable
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	No	Not applicable
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Yes	50%
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	No	Not applicable
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	No	Not applicable
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	Yes	50%
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	Yes	50%
31987100	BDP102 LED50/740 DM PCC GR MSP 62P	No	Not applicable
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	Yes	50%
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	No	Not applicable
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	No	Not applicable
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	No	Not applicable
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	No	Not applicable
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	No	Not applicable
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	No	Not applicable
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	No	Not applicable
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	No	Not applicable
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Yes	50%

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing
			Color
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Polycarbonate bowl/cover clear	Silver
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Polycarbonate bowl/cover clear	Silver
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/cover clear	Silver
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Polycarbonate bowl/cover frosted	Silver
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Polycarbonate bowl/cover frosted	Silver
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	Polycarbonate bowl/cover clear	Silver
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	Polycarbonate bowl/cover clear	Silver
31987100	BDP102 LED50/740 DM PCC GR MSP 62P	Polycarbonate bowl/cover clear	Gray

Product Data

Order Code	Full Product Name	Product family code
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	BDP100
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	BDP100
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	BDP100
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	BDP100
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	BDP100
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	BDP100

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Yes	50%
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	No	Not applicable
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	No	Not applicable


Order Code	Full Product Name	Optical cover type	Housing
			Color
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	Polycarbonate bowl/cover frosted	Silver
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Polycarbonate bowl/cover clear	Silver
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Polycarbonate bowl/cover frosted	Silver
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/cover frosted	Silver

Order Code	Full Product Name	Product family code
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	BDP100
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	BDP101
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	BDP101
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	BDP101
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	BDP101
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	BDP101


Order Code	Full Product Name	Product family code
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	BDP102
31987100	BDP102 LED50/740 DM PCC GR MSP 62P	BDP102
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	BDP102
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	BDP102
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	BDP102
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	BDP102
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	BDP102
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	BDP102

Order Code	Full Product Name	Product family code
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	BDP103
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	BDP103
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	BDP103
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	BDP103
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	BDP104
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	BDP104
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	BDP104
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	BDP104


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991010




Polar Normal (separate) - BDP100I - 910500991136




Polar Normal (separate) - BDP100I - 910500991021




Polar Normal (separate) - BDP100I - 910500991014




Polar Normal (separate) - BDP100I - 910500991112




Polar Normal (separate) - BDP100I - 910500991024



Polar Normal (separate) - BDP100I - 910500991223




Polar Normal (separate) - BDP100I - 910500991103




Polar Normal (separate) - BDP100I - 910500991149


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991069




Polar Normal (separate) - BDP100I - 910500991078




Polar Normal (separate) - BDP100I - 910500991096




Polar Normal (separate) - BDP100I - 910500991139




Polar Normal (separate) - BDP100I - 910500991015




Polar Normal (separate) - BDP100I - 910500991025



Polar Normal (separate) - BDP100I - 910500991009




Polar Normal (separate) - BDP100I - 910500991132




Polar Normal (separate) - BDP100I - 910500991128


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991072




Polar Normal (separate) - BDP100I - 910500991122




Polar Normal (separate) - BDP100I - 910500991125




Polar Normal (separate) - BDP100I - 910500991129




Polar Normal (separate) - BDP100I - 910500991121




Polar Normal (separate) - BDP100I - 910500991147



Polar Normal (separate) - BDP100I - 910500991117




Polar Normal (separate) - BDP100I - 910500991213



Polar Normal (separate) - BDP100I - 910500991142

Polar Wide Diagrams



Polar Normal (separate) - BDP100I - 910500991138

