



TownGuide Performer – Designed around your needs

TownGuide Performer

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project's specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

Benefits

- Six recognizable yet modern designs that blend in with, and enhance, their surroundings
- LED light sources, in combination with a wide choice of optics, ensure that the optimal configuration can be obtained for your application. The state-of-the-art LEDs increase visual comfort for motorists, cyclists and pedestrians.
- Considerable reduction in energy usage and carbon footprint compared to HPL mercury, SON-T and PL-L compact fluorescent lamps; further energy savings achievable when using CLO or dimming options (can amount to as much as 80% compared to HPL mercury)

Features

- Dedicated LED luminaire, optimized for minimum Total Cost of Ownership
- Wide choice of lumen packages, ranging from 1,200 to 7,000 lumens (GRN) or 4,000 to 12,000 lumens (ECO)
- Choice of light colors 3000 K (warm white) and 4000 K (neutral white)
- Long lifetime of 100,000 hours (GRN) or 80,000 hours (ECO) at L80B10
- Bayonet whistle connector for easy installation without opening the luminaire
- Suitable for new installations or one-to-one replacement in existing installations
- Vandal-resistant (IK10), ingress protection (IP66)
- TailorFit PCB technology
- Standard 3-year warranty program; as a service, we offer extended warranties or lifecycle services

Application

- Residential areas: residential streets, cycle paths & footpaths, roundabouts, squares, parks & playgrounds, parking areas
- City centers: side streets, squares, parks & playgrounds, cycle paths & footpaths, parking areas, roundabouts, shopping & pedestrian areas
- Area and Transportation: industrial areas, parking areas, petrol stations, airports, harbors, public transport areas
- Sports: parking areas

Versions

OPPR BDP100i 0021



OPPR BDP100i 0005




BDP102 TownGuide Performer
Classic cone, clear




BDP104 TownGuide Performer T,
clear



Dimensional drawing



Product details



TownGuide Performer

Product details

OPDP_BDP100i_0003-Detail
photo



OPDP_BDP100i_0007-Detail
photo



OPDP_BDP100i_0009-Detail
photo



TownGuide_Performe-
BDP100_105-DPP.TIF



General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Mechanical and Housing	
Mech. impact protection code	IK10
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.5 %

General Information

Order Code	Full Product Name	Lamp family code
34715700	BDP105 LED70/740 DS PCC GR D9 62P	LED70
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	LED30
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	LED40
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	LED40
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	LED50
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	LED60
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	LED40
91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	LED50
91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	LED60
91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	LED40
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	LED50
91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	LED60
91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	LED40
91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	LED50
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	LED60
30244600	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	LED30
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	LED40
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	LED80
90973600	BDP100 LED50/740 II DW PCC GR 62P	LED50
90974300	BDP100 LED70/740 II DW PCC GR 62P	LED70
90979800	BDP100 LED50/740 II DS PCC GR 62P	LED50
90980400	BDP100 LED70/740 II DS PCC GR 62P	LED70
90986600	BDP100 LED70/830 II DW PCC GR 62P	LED70
90991000	BDP100 LED50/830 II DS PCC GR 62P	LED50
90992700	BDP100 LED70/830 II DS PCC GR 62P	LED70

Order Code	Full Product Name	Lamp family code
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	LED120
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	LED50
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	LED50
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	LED60
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	LED40
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	LED50
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	LED60
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	LED40
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	LED50
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	LED60
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	LED40
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	LED50
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	LED60
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	LED20
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	LED50
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	LED100
91958200	BDP100 LED50/740 DW PCF SI 62P	LED50
32961000	BDP100 LED60/740 II DS PCF SI 62P	LED60
90603200	BDP100 LED50/830 II DS PCF GR 62P	LED50
90981100	BDP100 LED30/740 II DS PCF GR 62P	LED30
90982800	BDP100 LED50/740 II DS PCF GR 62P	LED50
90983500	BDP100 LED70/740 II DS PCF GR 62P	LED70
90995800	BDP100 LED70/830 II DS PCF GR 62P	LED70
91044200	BDP100 LED20/830 DS PCF GR 62P	LED20
91045900	BDP100 LED30/830 DS PCF GR 62P	LED30
91046600	BDP100 LED40/830 DS PCF GR 62P	LED40
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	LED60
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	LED30
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	LED35
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	LED100
90606300	BDP101 LED50/830 II DS PCF GR 62P	LED50
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	LED60
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	LED40
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	LED40
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	LED40
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	LED50
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	LED60
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	LED40
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	LED50
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	LED60
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	LED40
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	LED50
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	LED60
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	LED40
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	LED50
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	LED60
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	LED50
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	LED40
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	LED50
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	LED60
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	LED40
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	LED50

Order Code	Full Product Name	Lamp family code
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	LED60
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	LED40
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	LED50
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	LED60
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	LED40
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	LED50
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	LED60
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	LED20
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	LED30
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	LED35
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	LED50
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	LED70
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	LED20
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	LED35
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	LED50
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	LED120
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	LED30
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	LED70
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	LED40
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	LED40
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	LED50
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	LED100

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
34715700	BDP105 LED70/740 DS PCC GR D9 62P	75°	740 neutral white	4000 K	70	91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	32° x 29°	740 neutral white	4000 K	70	91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	53° x 71°	830 warm white	3000 K	80	91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70	91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70	91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70	91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70	91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
30244600	BDP100 LED30/740 DM PCC SI CLO- DDF1 76P	53° x 71°	740 neutral white	4000 K	70
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	75°	740 neutral white	4000 K	70
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	75°	740 neutral white	4000 K	70
90973600	BDP100 LED50/740 II DW PCC GR 62P	50° x 70°	740 neutral white	4000 K	70
90974300	BDP100 LED70/740 II DW PCC GR 62P	50° x 70°	740 neutral white	4000 K	70
90979800	BDP100 LED50/740 II DS PCC GR 62P	75°	740 neutral white	4000 K	70
90980400	BDP100 LED70/740 II DS PCC GR 62P	75°	740 neutral white	4000 K	70
90986600	BDP100 LED70/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
90991000	BDP100 LED50/830 II DS PCC GR 62P	75°	830 warm white	3000 K	80
90992700	BDP100 LED70/830 II DS PCC GR 62P	75°	830 warm white	3000 K	80
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	39° x 96°	740 neutral white	4000 K	70
90610000	BDP100 LED50/830 II DS PCF SI CLO- LS-6 6	75°	830 warm white	3000 K	80
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	75°	840 neutral white	4000 K	70
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91958200	BDP100 LED50/740 DW PCF SI 62P	50° x 70°	740 neutral white	4000 K	70
32961000	BDP100 LED60/740 II DS PCF SI 62P	75°	740 neutral white	4000 K	70
90603200	BDP100 LED50/830 II DS PCF GR 62P	75°	830 warm white	3000 K	80
90981100	BDP100 LED30/740 II DS PCF GR 62P	75°	740 neutral white	4000 K	70
90982800	BDP100 LED50/740 II DS PCF GR 62P	75°	740 neutral white	4000 K	70
90983500	BDP100 LED70/740 II DS PCF GR 62P	75°	740 neutral white	4000 K	70
90995800	BDP100 LED70/830 II DS PCF GR 62P	75°	830 warm white	3000 K	80
91044200	BDP100 LED20/830 DS PCF GR 62P	75°	830 warm white	3000 K	80

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
91045900	BDP100 LED30/830 DS PCF GR 62P	75°	830 warm white	3000 K	80
91046600	BDP100 LED40/830 DS PCF GR 62P	75°	830 warm white	3000 K	80
90614800	BDP101 LED60/830 II DS PCF SI CLO- DDF2 6	75°	830 warm white	3000 K	80
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
90606300	BDP101 LED50/830 II DS PCF GR 62P	75°	830 warm white	3000 K	80
90613100	BDP101 LED60/830 II DM PCC SI CLO- DDF2 6	53° x 71°	830 warm white	3000 K	80
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	75°	740 neutral white	4000 K	70
90620900	BDP102 LED40/830 II DW PCC SI CLO- DDF1 6	50° x 70°	830 warm white	3000 K	80
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
90622300	BDP102 LED50/830 II DS PCF SI CLO- DDF1 6	75°	830 warm white	3000 K	80
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
34715700	BDP105 LED70/740 DS PCC GR D9 62P	4,830 lm	8	Distribution symmetrical	0
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	2,291 lm	4	Distribution narrow	3
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	2,888 lm	4	Distribution medium	3
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	3,040 lm	3	Distribution wide	3
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	3,750 lm	4	Distribution wide	3
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	4,500 lm	4	Distribution wide	3
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	3,080 lm	3	Distribution symmetrical	3
91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	3,800 lm	4	Distribution symmetrical	3
91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	4,500 lm	4	Distribution symmetrical	3

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	53° x 71°	740 neutral white	4000 K	70
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	39° x 96°	740 neutral white	4000 K	70
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	75°	830 warm white	3000 K	80
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	3,040 lm	3	Distribution wide	3
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	3,700 lm	4	Distribution wide	3
91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	4,500 lm	4	Distribution wide	3
91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	3,080 lm	3	Distribution symmetrical	3
91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	3,800 lm	4	Distribution symmetrical	3
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	4,500 lm	4	Distribution symmetrical	3
30244600	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	2,204 lm	4	Distribution medium	3
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	3,080 lm	-	Distribution symmetrical	3
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	7,835 lm	-	Distribution symmetrical	3

TownGuide Performer

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
90973600	BDP100 LED50/740 II DW PCC GR 62P	3,750 lm	-	Distribution wide	3
90974300	BDP100 LED70/740 II DW PCC GR 62P	5,250 lm	-	Distribution wide	3
90979800	BDP100 LED50/740 II DS PCC GR 62P	3,800 lm	-	Distribution symmetrical	3
90980400	BDP100 LED70/740 II DS PCC GR 62P	5,250 lm	-	Distribution symmetrical	3
90986600	BDP100 LED70/830 II DW PCC GR 62P	5,250 lm	-	Distribution wide	3
90991000	BDP100 LED50/830 II DS PCC GR 62P	3,800 lm	-	Distribution symmetrical	3
90992700	BDP100 LED70/830 II DS PCC GR 62P	5,250 lm	-	Distribution symmetrical	3
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	8,400 lm	-	Distribution residential wide	0
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	1,862 lm	6	Distribution symmetrical	3
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	2,700 lm	4	Distribution wide	3
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	3,240 lm	4	Distribution wide	3
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	2,280 lm	3	Distribution symmetrical	3
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	2,800 lm	4	Distribution symmetrical	3
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	3,240 lm	4	Distribution symmetrical	3
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	2,160 lm	3	Distribution wide	3
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	2,650 lm	4	Distribution wide	3
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	3,240 lm	4	Distribution wide	3
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	2,280 lm	3	Distribution symmetrical	3
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	2,800 lm	4	Distribution symmetrical	3
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	3,240 lm	4	Distribution symmetrical	3
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	1,160 lm	4	Distribution wide	3
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	2,576 lm	6	Distribution wide	3
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	4,240 lm	6	Distribution wide	3
91958200	BDP100 LED50/740 DW PCF SI 62P	2,700 lm	6	Distribution wide	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
32961000	BDP100 LED60/740 II DS PCF SI 62P	3,240 lm	4	Distribution symmetrical	3
90603200	BDP100 LED50/830 II DS PCF GR 62P	2,800 lm	-	Distribution symmetrical	3
90981100	BDP100 LED30/740 II DS PCF GR 62P	1,710 lm	-	Distribution symmetrical	3
90982800	BDP100 LED50/740 II DS PCF GR 62P	2,800 lm	-	Distribution symmetrical	3
90983500	BDP100 LED70/740 II DS PCF GR 62P	3,780 lm	-	Distribution symmetrical	3
90995800	BDP100 LED70/830 II DS PCF GR 62P	3,780 lm	-	Distribution symmetrical	3
91044200	BDP100 LED20/830 DS PCF GR 62P	1,160 lm	-	Distribution symmetrical	3
91045900	BDP100 LED30/830 DS PCF GR 62P	1,710 lm	-	Distribution symmetrical	3
91046600	BDP100 LED40/830 DS PCF GR 62P	2,280 lm	-	Distribution symmetrical	3
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	2,300 lm	8	Distribution symmetrical	15
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	1,798 lm	4	Distribution wide	15
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	2,013 lm	4	Distribution wide	15
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	4,560 lm	6	Distribution wide	15
90606300	BDP101 LED50/830 II DS PCF GR 62P	3,000 lm	-	Distribution symmetrical	15
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	4,424 lm	8	Distribution medium	3
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	3,320 lm	-	Distribution symmetrical	3
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	3,116 lm	4	Distribution wide	3
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	3,160 lm	3	Distribution wide	3
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	4,891 lm	4	Distribution wide	3
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	4,680 lm	4	Distribution wide	3
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	3,280 lm	3	Distribution symmetrical	3
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	4,891 lm	4	Distribution symmetrical	3
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	4,740 lm	4	Distribution symmetrical	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	3,160 lm	3	Distribution wide	3
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	3,850 lm	4	Distribution wide	3
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	4,680 lm	4	Distribution wide	3
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	3,280 lm	3	Distribution symmetrical	3
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	4,000 lm	4	Distribution symmetrical	3
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	4,740 lm	4	Distribution symmetrical	3
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	1,900 lm	4	Distribution symmetrical	10
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	2,280 lm	3	Distribution wide	10
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	4,891 lm	4	Distribution wide	10
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	3,300 lm	4	Distribution wide	10
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	2,360 lm	3	Distribution symmetrical	10
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	4,891 lm	4	Distribution symmetrical	10
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	3,360 lm	4	Distribution symmetrical	10
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	2,280 lm	3	Distribution wide	10
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	2,800 lm	4	Distribution wide	10
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	3,300 lm	4	Distribution wide	10
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	2,360 lm	3	Distribution symmetrical	10
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	2,900 lm	4	Distribution symmetrical	10

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
34715700	BDP105 LED70/740 DS PCC GR D9 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	3,360 lm	4	Distribution symmetrical	10
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	1,200 lm	4	Distribution wide	10
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	1,740 lm	4	Distribution wide	10
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	1,947 lm	4	Distribution wide	10
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	2,714 lm	6	Distribution wide	10
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	3,584 lm	8	Distribution wide	10
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	1,060 lm	4	Distribution wide	4
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	1,716 lm	4	Distribution wide	4
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	2,346 lm	6	Distribution wide	4
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	4,800 lm	8	Distribution wide	4
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	2,204 lm	4	Distribution medium	3
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	4,620 lm	8	Distribution residential wide	3
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	1,386 lm	3	Distribution symmetrical	3
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	2,160 lm	3	Distribution wide	3
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	2,208 lm	6	Distribution wide	3
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	3,680 lm	6	Distribution wide	3

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

TownGuide Performer

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
30244600	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	53 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90973600	BDP100 LED50/740 II DW PCC GR 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90974300	BDP100 LED70/740 II DW PCC GR 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90979800	BDP100 LED50/740 II DS PCC GR 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
90980400	BDP100 LED70/740 II DS PCC GR 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90986600	BDP100 LED70/830 II DW PCC GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90991000	BDP100 LED50/830 II DS PCC GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90992700	BDP100 LED70/830 II DS PCC GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	79 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode

TownGuide Performer

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 4 kV differential mode and 4 kV common mode
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91958200	BDP100 LED50/740 DW PCF SI 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
32961000	BDP100 LED60/740 II DS PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90603200	BDP100 LED50/830 II DS PCF GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90981100	BDP100 LED30/740 II DS PCF GR 62P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90982800	BDP100 LED50/740 II DS PCF GR 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90983500	BDP100 LED70/740 II DS PCF GR 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90995800	BDP100 LED70/830 II DS PCF GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91044200	BDP100 LED20/830 DS PCF GR 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91045900	BDP100 LED30/830 DS PCF GR 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91046600	BDP100 LED40/830 DS PCF GR 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
90606300	BDP101 LED50/830 II DS PCF GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	46.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
34715700	BDP105 LED70/740 DS PCC GR D9 62P	Yes	0% (digital)
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Yes	50%

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	54 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	92 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Dimmable	Maximum dim level
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Yes	50%
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	Yes	50%
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	Yes	50%

TownGuide Performer

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	Yes	50%
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	Yes	50%
91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	Yes	50%
91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	Yes	50%
91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	Yes	50%
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	Yes	50%
91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	Yes	50%
91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	Yes	50%
91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	Yes	50%
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	Yes	50%
30244600	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	Yes	50%
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	Yes	50%
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	Yes	50%
90973600	BDP100 LED50/740 II DW PCC GR 62P	No	Not applicable
90974300	BDP100 LED70/740 II DW PCC GR 62P	No	Not applicable
90979800	BDP100 LED50/740 II DS PCC GR 62P	No	Not applicable
90980400	BDP100 LED70/740 II DS PCC GR 62P	No	Not applicable
90986600	BDP100 LED70/830 II DW PCC GR 62P	No	Not applicable
90991000	BDP100 LED50/830 II DS PCC GR 62P	No	Not applicable
90992700	BDP100 LED70/830 II DS PCC GR 62P	No	Not applicable
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	Yes	50%
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Yes	50%
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	Yes	50%
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	Yes	50%
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	Yes	50%
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	Yes	50%
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	Yes	50%
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	Yes	50%
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	Yes	50%
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	Yes	50%
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	Yes	50%
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	Yes	50%
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	Yes	50%
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	No	Not applicable
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	No	Not applicable
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	No	Not applicable
91958200	BDP100 LED50/740 DW PCF SI 62P	No	Not applicable
32961000	BDP100 LED60/740 II DS PCF SI 62P	No	Not applicable
90603200	BDP100 LED50/830 II DS PCF GR 62P	No	Not applicable
90981100	BDP100 LED30/740 II DS PCF GR 62P	No	Not applicable
90982800	BDP100 LED50/740 II DS PCF GR 62P	No	Not applicable
90983500	BDP100 LED70/740 II DS PCF GR 62P	No	Not applicable
90995800	BDP100 LED70/830 II DS PCF GR 62P	No	Not applicable
91044200	BDP100 LED20/830 DS PCF GR 62P	No	Not applicable
91045900	BDP100 LED30/830 DS PCF GR 62P	No	Not applicable
91046600	BDP100 LED40/830 DS PCF GR 62P	No	Not applicable
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Yes	50%
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	No	Not applicable
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	No	Not applicable
90606300	BDP101 LED50/830 II DS PCF GR 62P	No	Not applicable
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	Yes	50%
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	No	Not applicable
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	Yes	50%
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	Yes	50%
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	Yes	50%
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	Yes	50%
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	Yes	50%
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	Yes	50%
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	Yes	50%
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	Yes	50%
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	Yes	50%
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	Yes	50%
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	Yes	50%
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	Yes	50%
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	Yes	50%
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	Yes	50%
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	Yes	50%
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	Yes	50%
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	Yes	50%
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	Yes	50%
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	Yes	50%
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	Yes	50%
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	Yes	50%
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	Yes	50%
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	Yes	50%
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	Yes	50%
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	Yes	50%
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	Yes	50%
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	No	Not applicable
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	No	Not applicable
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	No	Not applicable
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	No	Not applicable
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	No	Not applicable
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	No	Not applicable
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	No	Not applicable
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	No	Not applicable
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	No	Not applicable
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Yes	50%
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	Yes	0% (digital)
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Yes	50%
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	Yes	50%
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	No	Not applicable
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	No	Not applicable

Mechanical and Housing

TownGuide Performer

Order Code	Full Product Name	Optical cover type	Housing Color
34715700	BDP105 LED70/740 DS PCC GR D9 62P	Polycarbonate bowl/ cover clear	Gray
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Polycarbonate bowl/ cover clear	Silver
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Polycarbonate bowl/ cover clear	Silver
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
30244600	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	Polycarbonate bowl/ cover clear	Silver
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	Polycarbonate bowl/ cover clear	Gray
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	Polycarbonate bowl/ cover clear	Gray
90973600	BDP100 LED50/740 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
90974300	BDP100 LED70/740 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
90979800	BDP100 LED50/740 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
90980400	BDP100 LED70/740 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
90986600	BDP100 LED70/830 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
90991000	BDP100 LED50/830 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
90992700	BDP100 LED70/830 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray

Order Code	Full Product Name	Optical cover type	Housing Color
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	Polycarbonate bowl/ cover clear	Gray
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Polycarbonate bowl/ cover frosted	Silver
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91958200	BDP100 LED50/740 DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
32961000	BDP100 LED60/740 II DS PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
90603200	BDP100 LED50/830 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
90981100	BDP100 LED30/740 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
90982800	BDP100 LED50/740 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
90983500	BDP100 LED70/740 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
90995800	BDP100 LED70/830 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
91044200	BDP100 LED20/830 DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
91045900	BDP100 LED30/830 DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray

TownGuide Performer

Order Code	Full Product Name	Optical cover type	Housing Color
91046600	BDP100 LED40/830 DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Polycarbonate bowl/ cover frosted	Silver
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
90606300	BDP101 LED50/830 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	Polycarbonate bowl/ cover clear	Silver
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	Polycarbonate bowl/ cover clear	Silver
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	Polycarbonate bowl/ cover frosted	Silver
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver

Order Code	Full Product Name	Optical cover type	Housing Color
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Polycarbonate bowl/ cover clear	Silver
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	Polycarbonate bowl/ cover clear	Gray
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Polycarbonate bowl/ cover frosted	Silver
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver

Approval and Application

TownGuide Performer

Order Code	Full Product Name	Glow-wire test
34715700	BDP105 LED70/740 DS PCC GR D9 62P	Temperature 650 °C, duration 5 s
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Temperature 650 °C, duration 5 s
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Temperature 650 °C, duration 5 s
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
30244600	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	Temperature 650 °C, duration 5 s
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	-
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	-
90973600	BDP100 LED50/740 II DW PCC GR 62P	-
90974300	BDP100 LED70/740 II DW PCC GR 62P	-
90979800	BDP100 LED50/740 II DS PCC GR 62P	-
90980400	BDP100 LED70/740 II DS PCC GR 62P	-
90986600	BDP100 LED70/830 II DW PCC GR 62P	-
90991000	BDP100 LED50/830 II DS PCC GR 62P	-
90992700	BDP100 LED70/830 II DS PCC GR 62P	-
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	-
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Temperature 650 °C, duration 5 s
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Glow-wire test
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91958200	BDP100 LED50/740 DW PCF SI 62P	Temperature 650 °C, duration 5 s
32961000	BDP100 LED60/740 II DS PCF SI 62P	Temperature 650 °C, duration 5 s
90603200	BDP100 LED50/830 II DS PCF GR 62P	-
90981100	BDP100 LED30/740 II DS PCF GR 62P	-
90982800	BDP100 LED50/740 II DS PCF GR 62P	-
90983500	BDP100 LED70/740 II DS PCF GR 62P	-
90995800	BDP100 LED70/830 II DS PCF GR 62P	-
91044200	BDP100 LED20/830 DS PCF GR 62P	-
91045900	BDP100 LED30/830 DS PCF GR 62P	-
91046600	BDP100 LED40/830 DS PCF GR 62P	-
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Temperature 650 °C, duration 5 s
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
90606300	BDP101 LED50/830 II DS PCF GR 62P	-
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	Temperature 650 °C, duration 5 s
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	-
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Glow-wire test
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	Temperature 650 °C, duration 5 s
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s

Product Data

Order Code	Full Product Name	Product family code
34715700	BDP105 LED70/740 DS PCC GR D9 62P	BDP105
90608700	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	BDP100
90609400	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	BDP100
90996500	BDP100 LED40/740 II DW PCC SI LS-6 62P	BDP100
90997200	BDP100 LED50/740 II DW PCC SI LS-6 62P	BDP100
90998900	BDP100 LED60/740 II DW PCC SI LS-6 62P	BDP100
91002200	BDP100 LED40/740 II DS PCC SI LS-6 62P	BDP100
91003900	BDP100 LED50/740 II DS PCC SI LS-6 62P	BDP100

Order Code	Full Product Name	Glow-wire test
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Temperature 650 °C, duration 5 s
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	Temperature 650 °C, duration 5 s
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Temperature 650 °C, duration 5 s
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s


Order Code	Full Product Name	Product family code
91004600	BDP100 LED60/740 II DS PCC SI LS-6 62P	BDP100
91008400	BDP100 LED40/830 II DW PCC SI LS-6 62P	BDP100
91009100	BDP100 LED50/830 II DW PCC SI LS-6 62P	BDP100
91010700	BDP100 LED60/830 II DW PCC SI LS-6 62P	BDP100
91014500	BDP100 LED40/830 II DS PCC SI LS-6 62P	BDP100
91015200	BDP100 LED50/830 II DS PCC SI LS-6 62P	BDP100
91016900	BDP100 LED60/830 II DS PCC SI LS-6 62P	BDP100
30244600	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	BDP100

TownGuide Performer


Order Code	Full Product Name	Product family code
37308800	BDP100 LED40/740 DS PCC GR DDF27 62P	BDP100
37309500	BDP100 LED80/740 DS PCC GR DDF27 62P	BDP100
90973600	BDP100 LED50/740 II DW PCC GR 62P	BDP100
90974300	BDP100 LED70/740 II DW PCC GR 62P	BDP100
90979800	BDP100 LED50/740 II DS PCC GR 62P	BDP100
90980400	BDP100 LED70/740 II DS PCC GR 62P	BDP100
90986600	BDP100 LED70/830 II DW PCC GR 62P	BDP100
90991000	BDP100 LED50/830 II DS PCC GR 62P	BDP100
90992700	BDP100 LED70/830 II DS PCC GR 62P	BDP100
12880400	BDP100 LED120/740 II DRW PCC GR-900 D11	BDP100
90610000	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	BDP100
91000800	BDP100 LED50/740 II DW PCF SI LS-6 62P	BDP100
91001500	BDP100 LED60/740 II DW PCF SI LS-6 62P	BDP100
91005300	BDP100 LED40/740 II DS PCF SI LS-6 62P	BDP100
91006000	BDP100 LED50/740 II DS PCF SI LS-6 62P	BDP100
91007700	BDP100 LED60/740 II DS PCF SI LS-6 62P	BDP100
91011400	BDP100 LED40/830 II DW PCF SI LS-6 62P	BDP100
91012100	BDP100 LED50/830 II DW PCF SI LS-6 62P	BDP100
91013800	BDP100 LED60/830 II DW PCF SI LS-6 62P	BDP100
91017600	BDP100 LED40/830 II DS PCF SI LS-6 62P	BDP100
91018300	BDP100 LED50/830 II DS PCF SI LS-6 62P	BDP100
91019000	BDP100 LED60/830 II DS PCF SI LS-6 62P	BDP100
91051000	BDP100 LED20/830 DW PCF SI CLO 62P	BDP100
91054100	BDP100 LED50/830 DW PCF SI CLO 62P	BDP100
91056500	BDP100 LED100/830 DW PCF SI CLO 62P	BDP100
91958200	BDP100 LED50/740 DW PCF SI 62P	BDP100
32961000	BDP100 LED60/740 II DS PCF SI 62P	BDP100
90603200	BDP100 LED50/830 II DS PCF GR 62P	BDP100
90981100	BDP100 LED30/740 II DS PCF GR 62P	BDP100
90982800	BDP100 LED50/740 II DS PCF GR 62P	BDP100
90983500	BDP100 LED70/740 II DS PCF GR 62P	BDP100
90995800	BDP100 LED70/830 II DS PCF GR 62P	BDP100
91044200	BDP100 LED20/830 DS PCF GR 62P	BDP100
91045900	BDP100 LED30/830 DS PCF GR 62P	BDP100
91046600	BDP100 LED40/830 DS PCF GR 62P	BDP100
90614800	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	BDP101
91060200	BDP101 LED30/830 DW PCF SI CLO 62P	BDP101
91061900	BDP101 LED35/830 DW PCF SI CLO 62P	BDP101
91064000	BDP101 LED100/830 DW PCF SI CLO 62P	BDP101
90606300	BDP101 LED50/830 II DS PCF GR 62P	BDP101
90613100	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	BDP101
34534100	BDP101 LED40/740 II DS PCC GR MSP 62P	BDP101

Order Code	Full Product Name	Product family code
90620900	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	BDP102
91020600	BDP102 LED40/740 II DW PCC SI LS-6 62P	BDP102
91021300	BDP102 LED50/740 II DW PCC SI LS-6 62P	BDP102
91022000	BDP102 LED60/740 II DW PCC SI LS-6 62P	BDP102
91026800	BDP102 LED40/740 II DS PCC SI LS-6 62P	BDP102
91027500	BDP102 LED50/740 II DS PCC SI LS-6 62P	BDP102
91028200	BDP102 LED60/740 II DS PCC SI LS-6 62P	BDP102
91032900	BDP102 LED40/830 II DW PCC SI LS-6 62P	BDP102
91033600	BDP102 LED50/830 II DW PCC SI LS-6 62P	BDP102
91034300	BDP102 LED60/830 II DW PCC SI LS-6 62P	BDP102
91038100	BDP102 LED40/830 II DS PCC SI LS-6 62P	BDP102
91039800	BDP102 LED50/830 II DS PCC SI LS-6 62P	BDP102
91040400	BDP102 LED60/830 II DS PCC SI LS-6 62P	BDP102
90622300	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	BDP102
91023700	BDP102 LED40/740 II DW PCF SI LS-6 62P	BDP102
91024400	BDP102 LED50/740 II DW PCF SI LS-6 62P	BDP102
91025100	BDP102 LED60/740 II DW PCF SI LS-6 62P	BDP102
91029900	BDP102 LED40/740 II DS PCF SI LS-6 62P	BDP102
91030500	BDP102 LED50/740 II DS PCF SI LS-6 62P	BDP102
91031200	BDP102 LED60/740 II DS PCF SI LS-6 62P	BDP102
91035000	BDP102 LED40/830 II DW PCF SI LS-6 62P	BDP102
91036700	BDP102 LED50/830 II DW PCF SI LS-6 62P	BDP102
91037400	BDP102 LED60/830 II DW PCF SI LS-6 62P	BDP102
91041100	BDP102 LED40/830 II DS PCF SI LS-6 62P	BDP102
91042800	BDP102 LED50/830 II DS PCF SI LS-6 62P	BDP102
91043500	BDP102 LED60/830 II DS PCF SI LS-6 62P	BDP102
91067100	BDP102 LED20/830 DW PCF SI CLO 62P	BDP102
91068800	BDP102 LED30/830 DW PCF SI CLO 62P	BDP102
91069500	BDP102 LED35/830 DW PCF SI CLO 62P	BDP102
91070100	BDP102 LED50/830 DW PCF SI CLO 62P	BDP102
91071800	BDP102 LED70/830 DW PCF SI CLO 62P	BDP102
91075600	BDP103 LED20/830 DW PCF SI CLO 62P	BDP103
91077000	BDP103 LED35/830 DW PCF SI CLO 62P	BDP103
91078700	BDP103 LED50/830 DW PCF SI CLO 62P	BDP103
91081700	BDP103 LED120/830 DW PCF SI CLO 62P	BDP103
90623000	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	BDP104
34713300	BDP104 LED70/740 DRW PCC GR D9 62P	BDP104
90624700	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	BDP104
90999600	BDP100 LED40/740 II DW PCF SI LS-6 62P	BDP100
91086200	BDP104 LED50/830 DW PCF SI CLO 62P	BDP104
91088600	BDP104 LED100/830 DW PCF SI CLO 62P	BDP104


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991089




Polar Normal (separate) - BDP100I - 910500991064




Polar Normal (separate) - BDP100I - 910500991080




Polar Normal (separate) - BDP100I - 910500991074




Polar Normal (separate) - BDP100I - 910500991010




Polar Normal (separate) - BDP100I - 910500991104



Polar Normal (separate) - BDP100I - 910500991136




Polar Normal (separate) - BDP100I - 910500991021




Polar Normal (separate) - BDP100I - 910500991062


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991085




Polar Normal (separate) - BDP100I - 910500991093




Polar Normal (separate) - BDP100I - 910500991066




Polar Normal (separate) - BDP100I - 910500991073




Polar Normal (separate) - BDP100I - 910500991082




Polar Normal (separate) - BDP100I - 910500991014



Polar Normal (separate) - BDP100I - 910500991090




Polar Normal (separate) - BDP100I - 910500991112




Polar Normal (separate) - BDP100I - 910500991077


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991024




Polar Normal (separate) - BDP100I - 910500991079




Polar Normal (separate) - BDP100I - 910500991223




Polar Normal (separate) - BDP100I - 910500991103




Polar Normal (separate) - BDP100I - 910500991149




Polar Normal (separate) - BDP100I - 910500991069



Polar Normal (separate) - BDP100I - 910500991084




Polar Normal (separate) - BDP100I - 910500991071




Polar Normal (separate) - BDP100I - 910500991078


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991081




Polar Normal (separate) - BDP100I - 910500991086




Polar Normal (separate) - BDP100I - 910500991083




Polar Normal (separate) - BDP100I - 910500991096




Polar Normal (separate) - BDP100I - 910500991094




Polar Normal (separate) - BDP100I - 910500991058



Polar Normal (separate) - BDP100I - 910500991139




Polar Normal (separate) - BDP100I - 910500991015




Polar Normal (separate) - BDP100I - 910500991097


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991025




Polar Normal (separate) - BDP100I - 910500991009




Polar Normal (separate) - BDP100I - 910500991076




Polar Normal (separate) - BDP100I - 910500991057




Polar Normal (separate) - BDP100I - 910500991060




Polar Normal (separate) - BDP100I - 910500991098



Polar Normal (separate) - BDP100I - 910500991087




Polar Normal (separate) - BDP100I - 910500991132




Polar Normal (separate) - BDP100I - 910500991190


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991063




Polar Normal (separate) - BDP100I - 910500991068




Polar Normal (separate) - BDP100I - 910500991059




Polar Normal (separate) - BDP100I - 910500991128




Polar Normal (separate) - BDP100I - 910500991065




Polar Normal (separate) - BDP100I - 910500991072



Polar Normal (separate) - BDP100I - 910500991101




Polar Normal (separate) - BDP100I - 910500991088




Polar Normal (separate) - BDP100I - 910500991164


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991061




Polar Normal (separate) - BDP100I - 910500991056




Polar Normal (separate) - BDP100I - 910500991122




Polar Normal (separate) - BDP100I - 910500991091




Polar Normal (separate) - BDP100I - 910500991125




Polar Normal (separate) - BDP100I - 910500991095



Polar Normal (separate) - BDP100I - 910500991129




Polar Normal (separate) - BDP100I - 910500991210




Polar Normal (separate) - BDP100I - 910500991067


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991121




Polar Normal (separate) - BDP100I - 910500991147




Polar Normal (separate) - BDP100I - 910500991070




Polar Normal (separate) - BDP100I - 910500991102




Polar Normal (separate) - BDP100I - 910500991117




Polar Normal (separate) - BDP100I - 910500991075



Polar Normal (separate) - BDP100I - 910500991142




Polar Normal (separate) - BDP100I - 910500991138




Polar Normal (separate) - BDP100I - 910925866295


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910925866299




Polar Normal (separate) - BDP100I - 910925866304




Polar Normal (separate) - BDP100I - 910925863295




Polar Normal (separate) - BDP100I - 910925866289




Polar Normal (separate) - BDP100I - 910925866287




Polar Normal (separate) - BDP100I - 910925866298



Polar Normal (separate) - BDP100I - 910925866297




Polar Normal (separate) - BDP100I - 910925866275




Polar Normal (separate) - BDP100I - 910925866278


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910925867796



Polar Normal (separate) - BDP100I - 910925452182



Polar Normal (separate) - BDP100I - 910925863304



Polar Normal (separate) - BDP100I - 910925863302

