

TownTune Asymmetric - Extending the home feel onto the street

Designed to enhance existing and scalable urban spaces, the TownTune family offers all the latest lighting innovations in terms of performance, quality of light and connectivity. The family consists of four solutions: a Central Post Top (CPT), an Asymmetric Spigot Post Top / Side Entry version (ASY), a version with an extending Lyre post top bracket (Lyre), and a Central Post Top with a Conical Comfort Bowl (CCB). Each TownTune luminaire can be customized with a choice of different shapes on top of the housing, plus there's the option to add a decorative ring, which comes in two colors (excluding CCB). Design options that enable you to create your very own lighting signature and bring a distinctive identity to districts and cities. In addition, every luminaire in the TownTune family is uniquely identifiable, thanks to the Signify Service tag app. By simply scanning a QR code, placed inside the door of the mast or directly on the luminaire, you can instantly access the configuration of the luminaire.

This makes maintenance and programming operations faster and easier and enables you to create your digital library of lighting assets and spare parts. TownTune also uses the LEDGINE-O lighting platform, ensuring you always have the right amount and direction of light on your street. Furthermore, thanks to being system ready (SR), TownTune is also future proof. A solution that's ready to be paired with both standalone and advanced control and lighting software applications such as Interact City.

Benefits

- LEDGINE-O platform for great performance, choice color temperatures and light distributions
- Optimized Total Cost of Ownership (L-Tune for flux tuning, standalone controls e.g., LumiStep, Dynadimmer, CLO (Constant Light output), LineSwitch)
- Ready to pair with advanced systems and software applications e.g., Interact City
- Long lifetime: 100,000 hours @L85 and higher
- Easy access to gear, vandal resistant (IK10), high ingress protection (IP66)

Applications

- Urban and residential areas
- Cycle paths, footpaths and pedestrian crossings

Versions




TownTune ASY DTD
BDP268

- City centers and squares
- Car parks

Features

- Simple design for easy integration into urban spaces, wide range of accessories for customization
- Suitable for new and retrofit installations
- Range of lumen packages (1200 to 12000 lm) and CCTs (2200K, 2700K, 3000K, 4000K) DarkSky Approved with 3000K CCT or warmer
- Dedicated bowl for visual comfort and comfortable lighting experiences
- Service tag for easy installation and maintenance.

Dimensional drawing



BDP268, TownTune asymmetric with decorative top dome

Product details



TownTune ASY BDP265




TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY DR BDP266



TownTune ASY BDP265

General Information

Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Upward light output ratio 0

Operating and Electrical

Surge Protection (Common/Differential) Standard surge protection level

Controls and Dimming

Maximum dim level 10%

Mechanical and Housing

Housing Color Gray
Ingress protection code IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code IK09 [10 J]
Standard tilt angle posttop -
Standard tilt angle side entry 0°
Optical cover type Polycarbonate bowl/cover UV-resistant

Approval and Application

Flammability mark For mounting on normally flammable surfaces
CE mark Yes

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h 0.5 %

Product Data

Product family code BDP268 [TOWNTUNE ASYMMETRIC DTD]

General Information

Order Code	Full Product Name	Lamp family code
912300024201	BDP268 LED30-4S/740 DW50 DR-GO CLO DDF1	LED30
912300024205	BDP268 LED74-4S/830 DW10 CLO SRT SRB 76A	LED74
912300024460	BDP268 LED84-4S/830 II DM10 48/60A	LED84
912300024461	BDP268 LED94-4S/830 II DM10 48/60A	LED94

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type out-door
912300024201	BDP268 LED30-4S/740 DW50 DR-GO CLO DDF1	2,378 lm	4000 K	70	740 neutral white	6° - 18° x 133°	Distribution wide 50
912300024205	BDP268 LED74-4S/830 DW10 CLO SRT SRB 76A	5,880 lm	3000 K	80	830 warm white	7° - 52° x 150°	Distribution wide 10
912300024460	BDP268 LED84-4S/830 II DM10 48/60A	6,888 lm	3000 K	80	830 warm white	77° - 11° x 156°	Distribution medium 10
912300024461	BDP268 LED94-4S/830 II DM10 48/60A	7,614 lm	3000 K	80	830 warm white	77° - 11° x 156°	Distribution medium 10


Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300024201	BDP268 LED30-4S/740 DW50 DR-GO CLO DDF1	18.8 W
912300024205	BDP268 LED74-4S/830 DW10 CLO SRT SRB 76A	55 W
912300024460	BDP268 LED84-4S/830 II DM10 48/60A	64 W
912300024461	BDP268 LED94-4S/830 II DM10 48/60A	72 W


Controls and Dimming

Order Code	Full Product Name	Dimmable
912300024201	BDP268 LED30-4S/740 DW50 DR-GO CLO DDF1	Yes
912300024205	BDP268 LED74-4S/830 DW10 CLO SRT SRB 76A	Yes
912300024460	BDP268 LED84-4S/830 II DM10 48/60A	No
912300024461	BDP268 LED94-4S/830 II DM10 48/60A	No

Polar normal diagrams



BDP268I - 912300024460



BDP268I - 912300024461

