



# Exquisite, stylish yet classic and versatile urban lighting

## UNIUrban

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

### Benefits

- Exquisite, stylish yet classic design to beautify your space
- State-of-the-art LEDs and drivers ensure better lighting performance and reliability
- Comfort and safety for urban
- Future-oriented


### Features

- 5 even more look-and-feels
- 3 options of wattage packages– 33W/ 65W / 100W
- 3000K/4000K CCT , 100+lm/w for energy-saving
- 3 options for installation - Side-entry, Post-top and Suspension
- 3 options for lighting distribution - Symmetrical / Asymmetrical / Omni
- IP65 / IK08 , professional design to ensure reliability
- 50K hrs. lifetime with 3 yrs. warranty
- Various mounting installation

### Application

- Sidewalks
- Parks, gardens
- Residential areas
- Shopping center plazas

Dimensional drawing



General Information	
Driver included	Yes
Lamp family code	-
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	≥70
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate micro lens optic
Housing Color	Grey
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
Flammability mark	-

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401727442	BDP461 LED33 WW 110-277V TS	Warm white	3000 K	3,300 lm
911401727452	BDP461 LED33 NW 110-277V TS	Neutral white	4000 K	3,300 lm
911401727462	BDP461 LED65 WW 110-277V TS	Warm white	3000 K	6,500 lm
911401727472	BDP461 LED65 NW 110-277V TS	Neutral white	4000 K	6,500 lm
911401727482	BDP461 LED100 WW 110-277V TS	Warm white	3000 K	10,000 lm
911401727492	BDP461 LED100 NW 110-277V TS	Neutral white	4000 K	10,000 lm
911401727622	BSP461 LED40 WW 110-277V TS	Warm white	3000 K	4,000 lm
911401727632	BSP461 LED40 NW 110-277V TS	Neutral white	4000 K	4,000 lm
911401727642	BSP461 LED40 WW 110-277V TA	Warm white	3000 K	4,000 lm
911401727652	BSP461 LED40 NW 110-277V TA	Neutral white	4000 K	4,000 lm
911401727662	BSP461 LED78 WW 110-277V TS	Warm white	3000 K	7,800 lm
911401727672	BSP461 LED78 NW 110-277V TS	Neutral white	4000 K	7,800 lm
911401727682	BSP461 LED78 WW 110-277V TA	Warm white	3000 K	7,800 lm
911401727692	BSP461 LED78 NW 110-277V TA	Neutral white	4000 K	7,800 lm
911401727702	BSP461 LED120 WW 110-277V TS	Warm white	3000 K	12,000 lm
911401727712	BSP461 LED120 NW 110-277V TS	Neutral white	4000 K	12,000 lm
911401727722	BSP461 LED120 WW 110-277V TA	Warm white	3000 K	12,000 lm
911401727732	BSP461 LED120 NW 110-277V TA	Neutral white	4000 K	12,000 lm
911401727742	BSS461 LED40 WW 110-277V CLASSIC	Warm white	3000 K	4,000 lm
911401727752	BSS461 LED40 NW 110-277V CLASSIC	Neutral white	4000 K	4,000 lm
911401727762	BSS461 LED78 WW 110-277V CLASSIC	Warm white	3000 K	7,800 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401727772	BSS461 LED78 NW 110-277V CLASSIC	Neutral white	4000 K	7,800 lm
911401727782	BSS461 LED120 WW 110-277V CLASSIC	Warm white	3000 K	7,800 lm
911401727792	BSS461 LED120 NW 110-277V CLASSIC	Neutral white	4000 K	12,000 lm
911401727502	BGP461 LED40 WW 110-277V TS	Warm white	3000 K	4,000 lm
911401727512	BGP461 LED40 NW 110-277V TS	Neutral white	4000 K	4,000 lm
911401727522	BGP461 LED40 WW 110-277V TA	Warm white	3000 K	4,000 lm
911401727532	BGP461 LED40 NW 110-277V TA	Neutral white	4000 K	4,000 lm
911401727542	BGP461 LED78 WW 110-277V TS	Warm white	3000 K	7,800 lm
911401727552	BGP461 LED78 NW 110-277V TS	Neutral white	4000 K	7,800 lm
911401727562	BGP461 LED78 WW 110-277V TA	Warm white	3000 K	7,800 lm
911401727572	BGP461 LED78 NW 110-277V TA	Neutral white	4000 K	7,800 lm
911401727582	BGP461 LED120 WW 110-277V TS	Tunable white	3000 K	12,000 lm
911401727592	BGP461 LED120 NW 110-277V TS	Neutral white	4000 K	12,000 lm
911401727602	BGP461 LED120 WW 110-277V TA	Warm white	3000 K	12,000 lm
911401727612	BGP461 LED120 NW 110-277V TA	Neutral white	4000 K	120,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401727442	BDP461 LED33 WW 110-277V TS	33 W
911401727452	BDP461 LED33 NW 110-277V TS	33 W
911401727462	BDP461 LED65 WW 110-277V TS	65 W
911401727472	BDP461 LED65 NW 110-277V TS	65 W
911401727482	BDP461 LED100 WW 110-277V TS	100 W
911401727492	BDP461 LED100 NW 110-277V TS	100 W
911401727622	BSP461 LED40 WW 110-277V TS	33 W
911401727632	BSP461 LED40 NW 110-277V TS	33 W
911401727642	BSP461 LED40 WW 110-277V TA	33 W
911401727652	BSP461 LED40 NW 110-277V TA	33 W
911401727662	BSP461 LED78 WW 110-277V TS	65 W
911401727672	BSP461 LED78 NW 110-277V TS	65 W
911401727682	BSP461 LED78 WW 110-277V TA	65 W
911401727692	BSP461 LED78 NW 110-277V TA	65 W
911401727702	BSP461 LED120 WW 110-277V TS	100 W
911401727712	BSP461 LED120 NW 110-277V TS	100 W
911401727722	BSP461 LED120 WW 110-277V TA	100 W
911401727732	BSP461 LED120 NW 110-277V TA	100 W

Order Code	Full Product Name	Power Consumption
911401727742	BSS461 LED40 WW 110-277V CLASSIC	33 W
911401727752	BSS461 LED40 NW 110-277V CLASSIC	33 W
911401727762	BSS461 LED78 WW 110-277V CLASSIC	65 W
911401727772	BSS461 LED78 NW 110-277V CLASSIC	65 W
911401727782	BSS461 LED120 WW 110-277V CLASSIC	100 W
911401727792	BSS461 LED120 NW 110-277V CLASSIC	100 W
911401727502	BGP461 LED40 WW 110-277V TS	33 W
911401727512	BGP461 LED40 NW 110-277V TS	33 W
911401727522	BGP461 LED40 WW 110-277V TA	33 W
911401727532	BGP461 LED40 NW 110-277V TA	33 W
911401727542	BGP461 LED78 WW 110-277V TS	65 W
911401727552	BGP461 LED78 NW 110-277V TS	65 W
911401727562	BGP461 LED78 WW 110-277V TA	65 W
911401727572	BGP461 LED78 NW 110-277V TA	65 W
911401727582	BGP461 LED120 WW 110-277V TS	100 W
911401727592	BGP461 LED120 NW 110-277V TS	100 W
911401727602	BGP461 LED120 WW 110-277V TA	100 W
911401727612	BGP461 LED120 NW 110-277V TA	100 W

Mechanical and Housing

Order Code	Full Product Name	Standard tilt angle posttop
911401727442	BDP461 LED33 WW 110-277V TS	-
911401727452	BDP461 LED33 NW 110-277V TS	-
911401727462	BDP461 LED65 WW 110-277V TS	-
911401727472	BDP461 LED65 NW 110-277V TS	-
911401727482	BDP461 LED100 WW 110-277V TS	-
911401727492	BDP461 LED100 NW 110-277V TS	-

Order Code	Full Product Name	Standard tilt angle posttop
911401727622	BSP461 LED40 WW 110-277V TS	-
911401727632	BSP461 LED40 NW 110-277V TS	-
911401727642	BSP461 LED40 WW 110-277V TA	-
911401727652	BSP461 LED40 NW 110-277V TA	-
911401727662	BSP461 LED78 WW 110-277V TS	-
911401727672	BSP461 LED78 NW 110-277V TS	-

Order Code	Full Product Name	Standard tilt angle posttop
911401727682	BSP461 LED78 WW 110-277V TA	-
911401727692	BSP461 LED78 NW 110-277V TA	-
911401727702	BSP461 LED120 WW 110-277V TS	-
911401727712	BSP461 LED120 NW 110-277V TS	-
911401727722	BSP461 LED120 WW 110-277V TA	-
911401727732	BSP461 LED120 NW 110-277V TA	-
911401727742	BSS461 LED40 WW 110-277V CLASSIC	-
911401727752	BSS461 LED40 NW 110-277V CLASSIC	-
911401727762	BSS461 LED78 WW 110-277V CLASSIC	-
911401727772	BSS461 LED78 NW 110-277V CLASSIC	-
911401727782	BSS461 LED120 WW 110-277V CLASSIC	-
911401727792	BSS461 LED120 NW 110-277V CLASSIC	-

Order Code	Full Product Name	Standard tilt angle posttop
911401727502	BGP461 LED40 WW 110-277V TS	15°
911401727512	BGP461 LED40 NW 110-277V TS	15°
911401727522	BGP461 LED40 WW 110-277V TA	15°
911401727532	BGP461 LED40 NW 110-277V TA	15°
911401727542	BGP461 LED78 WW 110-277V TS	15°
911401727552	BGP461 LED78 NW 110-277V TS	15°
911401727562	BGP461 LED78 WW 110-277V TA	15°
911401727572	BGP461 LED78 NW 110-277V TA	15°
911401727582	BGP461 LED120 WW 110-277V TS	15°
911401727592	BGP461 LED120 NW 110-277V TS	15°
911401727602	BGP461 LED120 WW 110-277V TA	15°
911401727612	BGP461 LED120 NW 110-277V TA	15°

