

## Metronomis LED Fluid

BDS670



## Metronomis LED: a play of light and shadow

Metronomis LED is the first post-top luminaire range in the world to offer a palette of lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow that casts a pattern on the ground, or in the bowl, to create additional ambience. Four iconic designs are available: Metronomis LED Torch (BDS650), Metronomis LED Torch with hat (BDS651), Metronomis LED Sharp (BDS660), and Metronomis LED Fluid (BDS670). Each luminaire design has a visual and modular link to Metronomis I, reduced to its essential elements. During the day, the discreet, transparent design blends into its urban context, whether that be contemporary or classical architecture and surroundings, while its night-time appearance is both functional and decorative. Flexible and modular, the Metronomis LED family comes with a range of columns and a wide variety of effects. This enables architects and lighting designers to create a unified, consistent lighting design across any cityscape, while still reflecting the differences in urban culture and history.

Metronomis LED also offers all the benefits of LEDGINE. Energy saving, serviceable and upgradable, this luminaire range is designed to maintain excellent light quality over its lifetime.

## Benefits

- Create a unique city identity with a pure design and palette of lighting effects
- Complete and innovative solution with a shared design identity for mast and luminaires
- Exceptional visual comfort with multiple geometries to optimize safety
- Future-ready with a Zhaga-D4i system ready (SR) top socket to connect with Interact controls
- Service tag for easy installation and maintenance

## Applications

- City centers and squares
- Commercial and business centers
- Residential and architectural areas
- Cycle paths, footpaths

## Versions




OPPR BDS650i 0017



Metronomis LED Fluid featuring a signature washlight effect to create ambiance

## Dimensional drawing



Metronomis LED Cone Fluid dimensional drawing

## Product details




OPDP\_BDS650i\_0009-  
Detail photo




OPDP\_BDS650i\_0011-  
Detail photo

OPDP\_BDS650i\_0045-  
Detail photo


OPDP\_BDS650i\_0047-  
Detail photo




OPDP\_BDS650i\_0049-  
Detail photo




OPDP\_BDS650i\_0051-  
Detail photo



OPDP\_BDS650i\_0053-  
Detail photo



OPDP\_BDS650i\_0055-  
Detail photo



## General Information

Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

## Operating and Electrical

Surge Protection (Common/ Differential)	Surge protection level until 10 kV
--------------------------------------------	------------------------------------

## Controls and Dimming

Dimmable	Yes
Maximum dim level	Programmable

## Mechanical and Housing

Housing Color	Gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	Polycarbonate bowl/cover

## Approval and Application

Flammability mark	-
CE mark	Yes

## Product Data

Product family code	BDS670 [METRONOMIS LED CONE FLUID]
---------------------	------------------------------------

## General Information

Order Code	Full Product Name	Lamp family code
910925868187	BDS670 LED80-4S/740 I MDM D9 STD 60	LED80
910925868198	BDS670 LED80/722 I MDM SRT 60	LED80
910925869082	BDS670 LED40-4S/830 II MDS DF CLO STD 60	LED40


## Light Technical

Order Code	Full Product Name	Luminaire light beam spread	Upward light output ratio	Light source color	Luminous Flux	Color rendering index (CRI)	Optic type outdoor	Correlated Color Temperature (Nom)
910925868187	BDS670 LED80-4S/740 I MDM D9 STD 60	48° x 66°	4.92	740 neutral white	6,800 lm	70	Metronomis distribution medium	4000 K
910925868198	BDS670 LED80/722 I MDM SRT 60	48° x 66°	4.92	722 warm white	6,720 lm	70	Metronomis distribution medium	2200 K
910925869082	BDS670 LED40-4S/830 II MDS DF CLO STD 60	17°	5.37	830 warm white	3,306 lm	80	Metronomis distribution symmetrical	3000 K


## Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925868187	BDS670 LED80-4S/740 I MDM D9 STD 60	46.5 W
910925868198	BDS670 LED80/722 I MDM SRT 60	64 W
910925869082	BDS670 LED40-4S/830 II MDS DF CLO STD 60	32 W


## Polar normal diagrams



BDS650I - 910925869082



BDS650I - 910925868187



BDS650I - 910925868198