



# Metronomis LED: a play of light and shadow

## Metronomis LED Fluid

Metronomis LED is the first post-top luminaire range in the world to offer a palette of lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow that casts a pattern on the ground, or in the bowl, to create additional ambience. Four iconic designs are available: Metronomis LED Torch (BDS650), Metronomis LED Torch with hat (BDS651), Metronomis LED Sharp (BDS660), and Metronomis LED Fluid (BDS670). Each luminaire design has a visual and modular link to Metronomis I, reduced to its essential elements. During the day, the discreet, transparent design blends into its urban context, whether that be contemporary or classical architecture and surroundings, while its night-time appearance is both functional and decorative. Flexible and modular, the Metronomis LED family comes with a range of columns and a wide variety of effects. This enables architects and lighting designers to create a unified, consistent lighting design across any cityscape, while still reflecting the differences in urban culture and history. Metronomis LED also offers all the benefits of LEDGINE. Energy saving, serviceable and upgradable, this luminaire range is designed to maintain excellent light quality over its lifetime.

### Benefits

- Create a unique city identity with a pure design and palette of lighting effects
- Complete and innovative solution with a shared design identity for mast and luminaires
- Exceptional visual comfort with multiple geometries to optimize safety
- Future-ready with a Zhaga-D4i system ready (SR) top socket to connect with Interact controls
- Service tag for easy installation and maintenance

# Metronomis LED Fluid

## Features

- Large choice of light effects (on ground, inside/outside bowl)
- 2D engraving option to personalize luminaires further
- Choice of color temperatures and color rendering for different ambiances: 2200K, 2700K, 3000K and 4000K
- Efficacy up to 157 lm/W
- Torch version with ULR <1%
- Lifetime up to 100,000 hours @L96 B10
- Five dedicated aluminum and wooden masts (3.5 and 4 meters)
- 5-year standard warranty (option to extend up to 10 years)

## Application


- City centers and squares
- Commercial and business centers
- Residential and architectural areas
- Cycle paths, footpaths

## Versions



OPPR BDS650i 0017

## Dimensional drawing



# Metronomis LED Fluid

## Product details



OPDP\_BDS650i\_0009-Detail  
photo



OPDP\_BDS650i\_0011-Detail  
photo



OPDP\_BDS650i\_0023-Detail  
photo



OPDP\_BDS650i\_0025-Detail  
photo



OPDP\_BDS650i\_0027-Detail  
photo



OPDP\_BDS650i\_0029-Detail  
photo



OPDP\_BDS650i\_0031-Detail  
photo




OPDP\_BDS650i\_0045-Detail  
photo


## Metronomis LED Fluid

### Product details


OPDP\_BDS650i\_0047-Detail  
photo




OPDP\_BDS650i\_0049-Detail  
photo




OPDP\_BDS650i\_0051-Detail  
photo



OPDP\_BDS650i\_0053-Detail  
photo



OPDP\_BDS650i\_0055-Detail  
photo



# Metronomis LED Fluid

General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Operating and Electrical	
Surge Protection (Common/Differential)	Surge protection level until 10 kV
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Optical cover type	Polycarbonate bowl/cover
Housing Color	Gray
Mech. impact protection code	IK10
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Approval and Application	
CE mark	Yes
Flammability mark	-
Product Data	
Product family code	BDS670

## General Information

Order Code	Full Product Name	Lamp family code
910925868187	BDS670 LED80-4S/740 I MDM D9 STD 60	LED80
910925868198	BDS670 LED80/722 I MDM SRT 60	LED80
910925869082	BDS670 LED40-4S/830 II MDS DF CLO STD 60	LED40

## Light Technical (1/2)

Order Code	Name	Correlated				
		Full Product	Luminaire light beam	Light source	Color temperature	Color rendering
		spread	color	(Nom)	index (CRI)	
910925868187	BDS670	48° x 66°	740	4000 K	70	
	LED80-4S/740 I			neutral		
	MDM D9 STD 60			white		
910925868198	BDS670	48° x 66°	722 warm	2200 K	70	
	LED80/722 I			white		
	MDM SRT 60					

Order Code	Name	Correlated				
		Full Product	Luminaire light beam	Light source	Color temperature	Color rendering
		spread	color	(Nom)	index (CRI)	
910925869082	BDS670	17°	830	3000 K	80	
	LED40-4S/830			warm		
	II MDS DF CLO			white		
	STD 60					

## Light Technical (2/2)

Order Code	Full Product Name	Upward light output		
		Luminous Flux	Optic type	output ratio
		outdoor		
910925868187	BDS670 LED80-4S/740 I MDM D9 STD 60	6,800 lm	Metronomis distribution	4.92
			medium	
910925868198	BDS670 LED80/722 I MDM SRT 60	6,720 lm	Metronomis distribution	4.92
			medium	

Order Code	Full Product Name	Upward light output		
		Luminous Flux	Optic type	output ratio
		outdoor		
910925869082	BDS670 LED40-4S/830 II MDS DF CLO STD 60	3,306 lm	Metronomis distribution	5.37
			symmetrical	

# Metronomis LED Fluid

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925868187	BDS670 LED80-4S/740 I MDM D9 STD 60	46.5 W
910925868198	BDS670 LED80/722 I MDM SRT 60	64 W



Order Code	Full Product Name	Power Consumption
910925869082	BDS670 LED40-4S/830 II MDS DF CLO STD 60	32 W

## Controls and Dimming

Order Code	Full Product Name	Maximum dim level
910925868187	BDS670 LED80-4S/740 I MDM D9 STD 60	Programmable
910925868198	BDS670 LED80/722 I MDM SRT 60	Programmable

Order Code	Full Product Name	Maximum dim level
910925869082	BDS670 LED40-4S/830 II MDS DF CLO STD 60	-

## Polar Wide Diagrams



Polar Normal (separate) - BDS650I -  
910925869082

Polar Normal (separate) - BDS650I -  
910925868187

