



## FlowStar Gen2: keep traffic moving safely in critical tunnel lighting conditions

For the most demanding conditions, where corrosion is a real threat, tunnel owners want tunnel luminaires that deliver cost, safety and availability benefits over their entire lifetime. With a high-grade, corrosion-resistant, full stainless steel build and dedicated LED design, FlowStar Gen2 delivers all that – and more. FlowStar Gen2 is part of the TotalTunnel solution. Combined with lighting controls, cables and our lifecycle services, these tunnel luminaires offer the highest levels of performance with exactly the right balance of visibility, safety and economy. And thanks to a high lumen output, they can also reduce the number of project luminaires required without compromising safety. A long-lasting and highly-efficient solution for tunnel lighting or underpass lighting that will keep traffic safe and moving.

### Benefits

- Reliable and long-lasting for traffic tunnels in highly corrosive environments
- Undisputed corrosion resistance, full stainless steel build
- Highly efficient to reduce energy consumption

- High lumen output to reduce the number of project luminaires
- Easy to clean, with a self-drainable top

### Applications

- Tunnel
- Underpass

## Features

- High-grade stainless-steel housing with no external aluminium parts
- Flat top, no ribs or fins
- Wide choice of high-quality optics

- Flexible mounting with quick release for easy maintenance
- Compatible with tunnel controls from and third parties
- Service tag: QR-based identification for maintenance, installation and spare part information


## Versions



BGB308 FlowStar Gen2  
Large




BGB307 FlowStar Gen2  
Medium




BGB306 FlowStar Gen2  
Small


## Dimensional drawing



BGB308 LED720/740 DTX1-HT D9 STD MICIO F



BGB306 LED230/740 DSM11 D9 STD MICIO FU




BGB307 LED500/740 DSM11 D9 STD MICIO FU

## Product details

BGB307\_FlowStar Gen2  
LED unit  
Medium\_interfaces



BGB308\_FlowStar Gen2  
LED unit Large\_Interfaces



BGB306\_FlowStar Gen2  
Small\_Backside



BGB305\_FlowStar Gen2  
Mini\_Backside details



### General Information

Light source replaceable	Yes
Driver included	Yes
Service Tag	Yes

### Light Technical

Upwards light output ratio	0
Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	70
Light source colour	740 neutral white

### Operating and Electrical

Surge Protection (Common/Differential)	Standard surge protection level
--	---------------------------------

## Controls and Dimming

Dimmable	Yes
Maximum dim level	10%

## Mechanical and Housing

Housing Colour	Steel
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle post-top	-
Standard tilt angle side entry	0°
Optical cover type	Glass flat with frame

## Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

## General Information

Order Code	Full Product Name	Lamp family code	Number of gear units
912300060015	BGB308 LED720/740 DTX1-HT D9 STD MICIO F	LED720	3 units
912300060127	BGB307 LED500/740 DSM11 D9 STD MICIO FU	LED500	Unit
912300060014	BGB306 LED230/740 DSM11 D9 MICIO FU BA	LED230	Unit
912300060126	BGB306 LED230/740 DSM11 D9 STD MICIO FU	LED230	Unit

## Light Technical

Order Code	Full Product Name	Luminous Flux	Luminaire light beam spread	Optic type outdoor
912300060015	BGB308 LED720/740 DTX1-HT D9 STD MICIO F	57,600 lm	152° x 155°	Asymmetrical
912300060127	BGB307 LED500/740 DSM11 D9 STD MICIO FU	40,500 lm	101° x 158°	Distribution symmetrical medium 11
912300060014	BGB306 LED230/740 DSM11 D9 MICIO FU BA	20,010 lm	101° x 158°	Distribution symmetrical medium 11
912300060126	BGB306 LED230/740 DSM11 D9 STD MICIO FU	18,860 lm	101° x 158°	Distribution symmetrical medium 11

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300060015	BGB308 LED720/740 DTX1-HT D9 STD MICIO F	425 W
912300060127	BGB307 LED500/740 DSM11 D9 STD MICIO FU	300 W
912300060014	BGB306 LED230/740 DSM11 D9 MICIO FU BA	136 W
912300060126	BGB306 LED230/740 DSM11 D9 STD MICIO FU	136 W

## Product Data

Order Code	Full Product Name	Product family code
912300060015	BGB308 LED720/740 DTX1-HT D9 STD MICIO F	BGB308
912300060127	BGB307 LED500/740 DSM11 D9 STD MICIO FU	BGB307
912300060014	BGB306 LED230/740 DSM11 D9 MICIO FU BA	BGB306
912300060126	BGB306 LED230/740 DSM11 D9 STD MICIO FU	BGB306