



## Versatile and cost-efficient LED lighting

ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimize your Total Cost of Ownership. ClearWay Gen2 significantly improves the most important aspects of the street lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design, which makes it easier to install.

### Benefits

- A range of benefits packaged in one single luminaire architecture
- Easy to install
- Low initial cost
- Reasonable Total Cost of Ownership
- Signify Service tag (unique QR identification) for maintenance, installation and spare part information

### Applications

- Urban and residential roads
- Bicycle and pedestrian paths
- Minor roads
- Parking lots

## Features

- One flexible design that offers different options depending on application needs

- Includes a dedicated light recipe that preserves dark night skies
- Compact and efficient design
- Tilt regulation with no need to open the cover

## Versions

ClearWay gen2 Performer-  
BGP307




ClearWay gen2 Core-  
BGP307



Clearway gen2



## Dimensional drawing



ClearWay gen2 - LED module 8400 lm - 740 neutral white  
- Safety class II - Distribution extra wide 10 - Universal  
for diameter 48 to 76 mm

BGP307 LED30-4S/740 II DM50 48/60S

### General Information

Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

## Light Technical

Upward light output ratio	0
Color rendering index (CRI)	70

## Operating and Electrical

Surge Protection (Common/Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode
--	--

## Mechanical and Housing

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Flat glass

## Approval and Application

Flammability mark	-
CE mark	Yes

## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
-------------------------------	-------

## Product Data

Product family code	BGP307 [CLEARWAY GEN2]
---------------------	------------------------

## General Information

Order Code	Full Product Name	Lamp family code
98795700	BGP307 LED18-4S/740 I DM50 48/60S	LED18
98796400	BGP307 LED25-4S/740 I DM50 48/60S	LED25
98797100	BGP307 LED30-4S/740 I DM50 48/60S	LED30
98798800	BGP307 LED35-4S/740 I DM50 48/60S	LED35
98799500	BGP307 LED40-4S/740 I DM50 48/60S	LED40
98800800	BGP307 LED45-4S/740 I DM50 48/60S	LED45
98801500	BGP307 LED54-4S/740 I DM50 48/60S	LED54
98802200	BGP307 LED69-4S/740 I DM50 48/60S	LED69
98803900	BGP307 LED84-4S/740 I DM50 48/60S	LED84

Order Code	Full Product Name	Lamp family code
98804600	BGP307 LED99-4S/740 I DM50 48/60S	LED99
98805300	BGP307 LED109-4S/740 I DM50 48/60S	LED109
98806000	BGP307 LED120-4S/740 I DM50 48/60S	LED120
98697400	BGP307 LED18-4S/740 II DM50 48/60S	LED18
98698100	BGP307 LED25-4S/740 II DM50 48/60S	LED25
98699800	BGP307 LED30-4S/740 II DM50 48/60S	LED30
98700100	BGP307 LED35-4S/740 II DM50 48/60S	LED35
98701800	BGP307 LED40-4S/740 II DM50 48/60S	LED40
98702500	BGP307 LED45-4S/740 II DM50 48/60A	LED45
98703200	BGP307 LED54-4S/740 II DM50 48/60S	LED54
98704900	BGP307 LED69-4S/740 II DM50 48/60S	LED69
98705600	BGP307 LED84-4S/740 II DM50 48/60S	LED84
98706300	BGP307 LED99-4S/740 II DM50 48/60S	LED99
98707000	BGP307 LED109-4S/740 II DM50 48/60S	LED109
98708700	BGP307 LED120-4S/740 II DM50 48/60S	LED120
99630000	BGP307 LED35-4S/740 I DM11 48/76S	LED35
99632400	BGP307 LED120-4S/740 I DM11 48/76S	LED120
99705500	BGP307 LED35-4S/740 II DM11 CLO 48/60S	LED35
99720800	BGP307 LED99-4S/740 II DM11 CLO 48/60S	LED99
99724600	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	LED84
99728400	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	LED69
11999400	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	LED84
44818900	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	LED130
70792400	BGP307 LED120-4S/730 II DM32 7042 MSP CL	LED120

## Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color	Luminaire light beam spread	Optic type outdoor
98795700	BGP307 LED18-4S/740 I DM50 48/60S	1,584 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98796400	BGP307 LED25-4S/740 I DM50 48/60S	2,175 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98797100	BGP307 LED30-4S/740 I DM50 48/60S	2,610 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98798800	BGP307 LED35-4S/740 I DM50 48/60S	3,080 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98799500	BGP307 LED40-4S/740 I DM50 48/60S	3,520 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color	Luminaire light beam spread	Optic type outdoor
98800800	BGP307 LED45-4S/740 I DM50 48/60S	3,960 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98801500	BGP307 LED54-4S/740 I DM50 48/60S	4,698 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98802200	BGP307 LED69-4S/740 I DM50 48/60S	6,160 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98803900	BGP307 LED84-4S/740 I DM50 48/60S	7,308 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98804600	BGP307 LED99-4S/740 I DM50 48/60S	8,600 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98805300	BGP307 LED109-4S/740 I DM50 48/60S	9,460 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98806000	BGP307 LED120-4S/740 I DM50 48/60S	10,200 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98697400	BGP307 LED18-4S/740 II DM50 48/60S	1,584 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98698100	BGP307 LED25-4S/740 II DM50 48/60S	2,175 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98699800	BGP307 LED30-4S/740 II DM50 48/60S	2,610 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98700100	BGP307 LED35-4S/740 II DM50 48/60S	3,080 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98701800	BGP307 LED40-4S/740 II DM50 48/60S	3,520 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98702500	BGP307 LED45-4S/740 II DM50 48/60A	3,960 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98703200	BGP307 LED54-4S/740 II DM50 48/60S	4,698 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98704900	BGP307 LED69-4S/740 II DM50 48/60S	6,160 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98705600	BGP307 LED84-4S/740 II DM50 48/60S	7,308 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98706300	BGP307 LED99-4S/740 II DM50 48/60S	8,600 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98707000	BGP307 LED109-4S/740 II DM50 48/60S	9,460 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
98708700	BGP307 LED120-4S/740 II DM50 48/60S	10,200 lm	4000 K	740 neutral white	154° - 31° x 54°	Distribution medium 50
99630000	BGP307 LED35-4S/740 I DM11 48/76S	3,045 lm	4000 K	740 neutral white	160° - 42° x 54°	Distribution medium 11
99632400	BGP307 LED120-4S/740 I DM11 48/76S	10,200 lm	4000 K	740 neutral white	160° - 42° x 54°	Distribution medium 11
99705500	BGP307 LED35-4S/740 II DM11 CLO 48/60S	2,958 lm	4000 K	740 neutral white	160° - 42° x 54°	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color	Luminaire light beam spread	Optic type outdoor
99720800	BGP307 LED99-4S/740 II DM11 CLO 48/60S	8,256 lm	4000 K	740 neutral white	160° - 42° x 54°	Distribution medium 11
99724600	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	7,134 lm	4000 K	740 neutral white	160° - 42° x 54°	Distribution medium 11
99728400	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	5,916 lm	4000 K	740 neutral white	160° - 42° x 54°	Distribution medium 11
11999400	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	6,972 lm	4000 K	740 neutral white	152° - 25° x 66°	Distribution extra wide 10
44818900	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	10,920 lm	4000 K	740 neutral white	160° - 42° x 54°	Distribution medium 11
70792400	BGP307 LED120-4S/730 II DM32 7042 MSP CL	9,890 lm	3000 K	730 warm white	160° - 42° x 54°	Distribution medium 11

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
98795700	BGP307 LED18-4S/740 I DM50 48/60S	11.6 W
98796400	BGP307 LED25-4S/740 I DM50 48/60S	16.2 W
98797100	BGP307 LED30-4S/740 I DM50 48/60S	19.6 W
98798800	BGP307 LED35-4S/740 I DM50 48/60S	21.5 W
98799500	BGP307 LED40-4S/740 I DM50 48/60S	24.5 W
98800800	BGP307 LED45-4S/740 I DM50 48/60S	27.5 W
98801500	BGP307 LED54-4S/740 I DM50 48/60S	33.5 W
98802200	BGP307 LED69-4S/740 I DM50 48/60S	40.5 W
98803900	BGP307 LED84-4S/740 I DM50 48/60S	49.5 W
98804600	BGP307 LED99-4S/740 I DM50 48/60S	59 W
98805300	BGP307 LED109-4S/740 I DM50 48/60S	65 W
98806000	BGP307 LED120-4S/740 I DM50 48/60S	72 W
98697400	BGP307 LED18-4S/740 II DM50 48/60S	11.6 W
98698100	BGP307 LED25-4S/740 II DM50 48/60S	16.2 W
98699800	BGP307 LED30-4S/740 II DM50 48/60S	19.6 W
98700100	BGP307 LED35-4S/740 II DM50 48/60S	21.5 W
98701800	BGP307 LED40-4S/740 II DM50 48/60S	24.5 W
98702500	BGP307 LED45-4S/740 II DM50 48/60A	27.5 W
98703200	BGP307 LED54-4S/740 II DM50 48/60S	33.5 W
98704900	BGP307 LED69-4S/740 II DM50 48/60S	40.5 W
98705600	BGP307 LED84-4S/740 II DM50 48/60S	49.5 W
98706300	BGP307 LED99-4S/740 II DM50 48/60S	59 W
98707000	BGP307 LED109-4S/740 II DM50 48/60S	65 W

Order Code	Full Product Name	Power Consumption
98708700	BGP307 LED120-4S/740 II DM50 48/60S	72 W
99630000	BGP307 LED35-4S/740 I DM11 48/76S	21.5 W
99632400	BGP307 LED120-4S/740 I DM11 48/76S	72 W
99705500	BGP307 LED35-4S/740 II DM11 CLO 48/60S	21 W
99720800	BGP307 LED99-4S/740 II DM11 CLO 48/60S	56 W
99724600	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	48 W
99728400	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	39.5 W
11999400	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	49.5 W
44818900	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	79 W
70792400	BGP307 LED120-4S/730 II DM32 7042 MSP CL	73 W

## Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
98795700	BGP307 LED18-4S/740 I DM50 48/60S	No	Not applicable
98796400	BGP307 LED25-4S/740 I DM50 48/60S	No	Not applicable
98797100	BGP307 LED30-4S/740 I DM50 48/60S	No	Not applicable
98798800	BGP307 LED35-4S/740 I DM50 48/60S	No	Not applicable
98799500	BGP307 LED40-4S/740 I DM50 48/60S	No	Not applicable
98800800	BGP307 LED45-4S/740 I DM50 48/60S	No	Not applicable
98801500	BGP307 LED54-4S/740 I DM50 48/60S	No	Not applicable
98802200	BGP307 LED69-4S/740 I DM50 48/60S	No	Not applicable
98803900	BGP307 LED84-4S/740 I DM50 48/60S	No	Not applicable
98804600	BGP307 LED99-4S/740 I DM50 48/60S	No	Not applicable
98805300	BGP307 LED109-4S/740 I DM50 48/60S	No	Not applicable
98806000	BGP307 LED120-4S/740 I DM50 48/60S	No	Not applicable
98697400	BGP307 LED18-4S/740 II DM50 48/60S	No	Not applicable
98698100	BGP307 LED25-4S/740 II DM50 48/60S	No	Not applicable
98699800	BGP307 LED30-4S/740 II DM50 48/60S	No	Not applicable
98700100	BGP307 LED35-4S/740 II DM50 48/60S	No	Not applicable
98701800	BGP307 LED40-4S/740 II DM50 48/60S	No	Not applicable
98702500	BGP307 LED45-4S/740 II DM50 48/60A	No	Not applicable
98703200	BGP307 LED54-4S/740 II DM50 48/60S	No	Not applicable
98704900	BGP307 LED69-4S/740 II DM50 48/60S	No	Not applicable
98705600	BGP307 LED84-4S/740 II DM50 48/60S	No	Not applicable
98706300	BGP307 LED99-4S/740 II DM50 48/60S	No	Not applicable
98707000	BGP307 LED109-4S/740 II DM50 48/60S	No	Not applicable
98708700	BGP307 LED120-4S/740 II DM50 48/60S	No	Not applicable
99630000	BGP307 LED35-4S/740 I DM11 48/76S	No	Not applicable


Order Code	Full Product Name	Dimmable	Maximum dim level
99632400	BGP307 LED120-4S/740 I DM11 48/76S	No	Not applicable
99705500	BGP307 LED35-4S/740 II DM11 CLO 48/60S	No	0% (digital)
99720800	BGP307 LED99-4S/740 II DM11 CLO 48/60S	No	0% (digital)
99724600	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
99728400	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
11999400	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	No	Not applicable
44818900	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Yes	Not applicable
70792400	BGP307 LED120-4S/730 II DM32 7042 MSP CL	Yes	0% (digital)

## Mechanical and Housing


Order Code	Full Product Name	Housing Color
98795700	BGP307 LED18-4S/740 I DM50 48/60S	Gray
98796400	BGP307 LED25-4S/740 I DM50 48/60S	Gray
98797100	BGP307 LED30-4S/740 I DM50 48/60S	Gray
98798800	BGP307 LED35-4S/740 I DM50 48/60S	Gray
98799500	BGP307 LED40-4S/740 I DM50 48/60S	Gray
98800800	BGP307 LED45-4S/740 I DM50 48/60S	Gray
98801500	BGP307 LED54-4S/740 I DM50 48/60S	Gray
98802200	BGP307 LED69-4S/740 I DM50 48/60S	Gray
98803900	BGP307 LED84-4S/740 I DM50 48/60S	Gray
98804600	BGP307 LED99-4S/740 I DM50 48/60S	Gray
98805300	BGP307 LED109-4S/740 I DM50 48/60S	Gray
98806000	BGP307 LED120-4S/740 I DM50 48/60S	Gray
98697400	BGP307 LED18-4S/740 II DM50 48/60S	Gray
98698100	BGP307 LED25-4S/740 II DM50 48/60S	Gray
98699800	BGP307 LED30-4S/740 II DM50 48/60S	Gray
98700100	BGP307 LED35-4S/740 II DM50 48/60S	Gray
98701800	BGP307 LED40-4S/740 II DM50 48/60S	Gray
98702500	BGP307 LED45-4S/740 II DM50 48/60A	Gray
98703200	BGP307 LED54-4S/740 II DM50 48/60S	Gray
98704900	BGP307 LED69-4S/740 II DM50 48/60S	Gray
98705600	BGP307 LED84-4S/740 II DM50 48/60S	Gray
98706300	BGP307 LED99-4S/740 II DM50 48/60S	Gray
98707000	BGP307 LED109-4S/740 II DM50 48/60S	Gray
98708700	BGP307 LED120-4S/740 II DM50 48/60S	Gray
99630000	BGP307 LED35-4S/740 I DM11 48/76S	Gray
99632400	BGP307 LED120-4S/740 I DM11 48/76S	Gray
99705500	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Gray

Order Code	Full Product Name	Housing Color
99720800	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Gray
99724600	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Gray
99728400	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Gray
11999400	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	Gray
44818900	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Grey
70792400	BGP307 LED120-4S/730 II DM32 7042 MSP CL	Grey


## Polar normal diagrams




BGP307I - 910925864604




BGP307I - 910925864592




BGP307I - 910925864597




BGP307I - 910925864587




BGP307I - 910925864586




BGP307I - 910925864590




BGP307I - 910925865134




BGP307I - 910925865151




BGP307I - 910925865551




BGP307I - 910925864593




BGP307I - 910925864595




BGP307I - 910925864584




BGP307I - 910925864588




BGP307I - 910925864589




BGP307I - 910925865153




BGP307I - 910925865251




BGP307I - 910925865245



BGP307I - 910925865242



BGP307I - 910925867804



BGP307I - 910925868941