



The most cost-effective outdoor spot light with better efficient and performance

UniPoint

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturization. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

Benefits

- In stylish and very compact design
- Price point versus PHILIPS standards
- Effortless and flexible installation
- Customizing for you

Features

- High quality LED
- Different choice of light source and beam angles
- Die-cast aluminum housing + dark grey sand coating to ensure anticorrosion
- Structural waterproof technology
- IP66
- IK06
- Quality and reliability in line with all regulations

Application


- Buildings
- Statues
- Columns
- Pillars
- Eaves

Versions



UniPoint BGP312 3LED

Dimensional drawing



General Information	
Driver included	No
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	>75
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Glass bowl/cover
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Approval and Application	
CE mark	No

Light Technical (1/2)

Order Code	Full Product Name	Luminaire			
		light beam spread	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401710672	BGP312 1LED 3000K NB	10°	830 warm white	3000 K	120 lm
911401710682	BGP312 1LED 3000K MB	25°	830 warm white	3000 K	120 lm
911401710762	BGP312 3LED 3000K NB	10°	830 warm white	3000 K	330 lm
911401710862	BGP312 5LED 3000K MB	25°	830 warm white	3000 K	595 lm
911401710872	BGP312 5LED 3000K WB	40°	830 warm white	3000 K	595 lm
911401710882	BGP312 5LED 4000K NB	10°	840 neutral white	4000 K	595 lm
911401710902	BGP312 5LED 4000K WB	40°	840 neutral white	4000 K	595 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type outdoor
911401710672	BGP312 1LED 3000K NB	Narrow beam angle 10°
911401710682	BGP312 1LED 3000K MB	Medium beam angle 25°
911401710762	BGP312 3LED 3000K NB	Narrow beam angle 10°
911401710862	BGP312 5LED 3000K MB	Medium beam angle 25°

Order Code	Full Product Name	Optic type outdoor
911401710872	BGP312 5LED 3000K WB	Wide beam angle 42°
911401710882	BGP312 5LED 4000K NB	Narrow beam angle 10°
911401710902	BGP312 5LED 4000K WB	Wide beam angle 42°

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401710672	BGP312 1LED 3000K NB	3 W
911401710682	BGP312 1LED 3000K MB	3 W
911401710762	BGP312 3LED 3000K NB	6 W
911401710862	BGP312 5LED 3000K MB	10 W

Order Code	Full Product Name	Power Consumption
911401710872	BGP312 5LED 3000K WB	10 W
911401710882	BGP312 5LED 4000K NB	10 W
911401710902	BGP312 5LED 4000K WB	10 W

