



The most cost-effective outdoor spot light with better efficient and performance

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturization. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

Benefits

- In stylish and very compact design
- Price point versus PHILIPS standards
- Effortless and flexible installation
- Customizing for you

Applications

- Buildings
- Statues
- Columns
- Pillars
- Eaves

Features

- High quality LED
- Different choice of light source and beam angles
- Die-cast aluminum housing + dark grey sand coating to ensure anticorrosion


- Structural waterproof technology
- IP66
- IK06
- Quality and reliability in line with all regulations

Versions



UniPoint BGP312 5LED

Dimensional drawing



Unipoint BGP312 5LED

General Information

Light source replaceable	No
Driver included	No

Light Technical

Luminous Flux	595 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>75
Light source color	830 warm white
Luminaire light beam spread	25°
Optic type outdoor	Medium beam angle 25°

Operating and Electrical

Power Consumption	10 W
-------------------	------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	Glass bowl/cover

Approval and Application

CE mark	No
---------	----