



## TubeLine: linear tunnel lighting for optimized comfort and guidance

For customers who demand a high level of visual comfort from their tunnel luminaires, fluorescent linear lighting has traditionally been the preferred choice. With excellent light uniformity on the road and walls, perfect visual guidance and high color rendering, linear lighting offers drivers superior lighting quality and safety. It also promises high system redundancy compared to point source lighting solutions. With TubeLine tunnel luminaires, you can achieve the same lighting quality, but with all the added advantages of LED technology. TubeLine is a state-of-the-art tunnel luminaire that harnesses the latest LED technology with optimized dimensions and attractive pricing for a quick return on investment. Linear lighting has never been more achievable for tunnel lighting and underpass lighting on a limited budget.

### Benefits

- Optimal traffic flow due to increased visual comfort and safety compared to point-source lighting
- Economical alternative to fluorescent tunnel lighting
- High tunnel lighting availability: remote driver system
- Flexible, easy-to-install lighting system

### Applications

- Tunnel
- Underpass

## Features

- Linear luminaire in 1 or 2 meter lengths
- Driver not integrated: remote driver set-up
- Wide range of lumen packages: 3,000 to 30,000 lm

- Multiple mounting and connectivity options
- Compatible with tunnel controls from and third parties
- Service tag: QR-based identification for maintenance, installation and spare part information

## Versions



TubeLine BGP360

## Dimensional drawing

TubeLine 2M - LED module 6000 lm - Distribution tunnel  
symmetrical - Safety class I - Cord with plug Wieland/  
Adels compatible 3-pole

## Product details



TubeLine\_BGP360-  
DP01.tif



TubeLine\_BGP360-  
DP02.tif




TubeLine\_BGP360-  
DP03.tif



TubeLine\_BGP360-  
DP04.tif



TubeLine\_BGP360-  
DP05.tif



TubeLine\_BGP360-  
DP06.tif



TubeLine\_BGP360-  
DP07.tif



TubeLine\_BGP360-  
DP08.tif



TubeLine\_BGP360\_ZGP360-  
DP09.tif

## General Information

Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	No
Service tag	Yes

## Light Technical

Upward light output ratio	0
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	70
Light source color	740 neutral white
Luminaire light beam spread	150°
Optic type outdoor	Distribution tunnel symmetrical

## Operating and Electrical

Surge Protection (Common/ Differential)	-
--	---

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Housing Color	Aluminum
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	Flat glass

## Approval and Application

Flammability mark	-
CE mark	Yes

## Product Data

Product family code	BGP360 [TUBELINE]
---------------------	-------------------

## General Information

Order Code	Full Product Name	Lamp family code
09429400	BGP360 LED30/740 DTS CFW C250W GP	LED30
09430000	BGP360 LED60/740 DTS CFW C250W GP	LED60
09432400	BGP360 LED120/740 DTS CFW C250W GP	LED120

## Light Technical

Order Code	Full Product Name	Luminous Flux	Number of light sources
09429400	BGP360 LED30/740 DTS CFW C250W GP	2,700 lm	24
09430000	BGP360 LED60/740 DTS CFW C250W GP	5,400 lm	48
09432400	BGP360 LED120/740 DTS CFW C250W GP	10,800 lm	48

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
09429400	BGP360 LED30/740 DTS CFW C250W GP	18.8 W
09430000	BGP360 LED60/740 DTS CFW C250W GP	35.5 W
09432400	BGP360 LED120/740 DTS CFW C250W GP	72 W