

**PHILIPS**

**Lighting**



# **TubeLine: linear tunnel lighting for optimized comfort and guidance**

## **TubeLine**

For customers who demand a high level of visual comfort from their tunnel luminaires, fluorescent linear lighting has traditionally been the preferred choice. With excellent light uniformity on the road and walls, perfect visual guidance and high color rendering, linear lighting offers drivers superior lighting quality and safety. It also promises high system redundancy compared to point source lighting solutions. With TubeLine tunnel luminaires, you can achieve the same lighting quality, but with all the added advantages of LED technology. TubeLine is a state-of-the-art tunnel luminaire that harnesses the latest LED technology with optimized dimensions and attractive pricing for a quick return on investment. Linear lighting has never been more achievable for tunnel lighting and underpass lighting on a limited budget.

### **Benefits**

- Optimal traffic flow due to increased visual comfort and safety compared to point-source lighting
- Quick return on investment
- Flexible, easy-to-install solution

## Features

- Robust, corrosion-resistant aluminum build
- Standard length 2 m
- Smooth design, easy to clean
- Remote driver designed to prevent lane closures
- Lumen packages up to 14,400 lm
- Flexible mounting and connectivity
- Compatible with Philips controls

## Application


- Traffic tunnels
- Underpasses

## Versions



TubeLine BGP360

## Dimensional drawing



## Product details

TubeLine\_BGP360-DP01.tif



TubeLine\_BGP360-DP02.tif



TubeLine\_BGP360-DP03.tif



TubeLine\_BGP360-DP04.tif



TubeLine\_BGP360-DP05.tif



TubeLine\_BGP360-DP06.tif



TubeLine\_BGP360-DP07.tif



TubeLine\_BGP360-DP08.tif



## Product details

TubeLine\_BGP360\_ZGP360-  
DP09.tif



## General Information

Driver included	No
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

## Light Technical

Luminaire light beam spread	150°
Light source color	740 neutral white
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	70
Optic type outdoor	Distribution tunnel symmetrical
Upward light output ratio	0

## Operating and Electrical

Surge Protection (Common/	-
Differential)	

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Optical cover type	Flat glass
Housing Color	Aluminum
Mech. impact protection code	IK09
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	-

## Approval and Application

CE mark	Yes
Flammability mark	-

## Product Data

Product family code	BGP360
---------------------	--------

## General Information

Order Code	Full Product Name	Lamp family code
09429400	BGP360 LED30/740 DTS CFW C250W GP	LED30
09430000	BGP360 LED60/740 DTS CFW C250W GP	LED60
09432400	BGP360 LED120/740 DTS CFW C250W GP	LED120
09433100	BGP360 LED165/740 DTS CFW C250W GP	LED165

## Light Technical

Number of light			
Order Code	Full Product Name	Luminous Flux	sources
09429400	BGP360 LED30/740 DTS CFW C250W GP	2,700 lm	24
09430000	BGP360 LED60/740 DTS CFW C250W GP	5,400 lm	48

Number of light			
Order Code	Full Product Name	Luminous Flux	sources
09432400	BGP360 LED120/740 DTS CFW C250W GP	10,800 lm	48
09433100	BGP360 LED165/740 DTS CFW C250W GP	14,685 lm	48

#### Operating and Electrical

Order Code	Full Product Name	Power Consumption
09429400	BGP360 LED30/740 DTS CFW C250W GP	18.8 W
09430000	BGP360 LED60/740 DTS CFW C250W GP	35.5 W

Order Code	Full Product Name	Power Consumption
09432400	BGP360 LED120/740 DTS CFW C250W GP	72 W
09433100	BGP360 LED165/740 DTS CFW C250W GP	104 W

