Signify

TubeLine

BGP360

TubeLine: linear tunnel lighting for optimised comfort and guidance

For customers who demand a high level of visual comfort from their tunnel luminaires, fluorescent linear lighting has traditionally been the preferred choice. With excellent light uniformity on the road and walls, perfect visual guidance and high colour rendering, linear lighting offers drivers superior lighting quality and safety. It also promises high system redundancy compared to point source lighting solutions. With TubeLine tunnel luminaires, you can achieve the same lighting quality, but with all the added advantages of LED technology. TubeLine is a state-of-the-art tunnel luminaire that harnesses the latest LED technology with optimised dimensions and attractive pricing for a quick return on investment. Linear lighting has never been more achievable for tunnel lighting and underpass lighting on a limited budget.

Benefits

- Optimal traffic flow due to increased visual comfort and safety compared to point-source lighting
- Economical alternative to fluorescent tunnel lighting
- High tunnel lighting availability: remote driver system
- Flexible, easy-to-install lighting system

Applications

- Tunnel
- Underpass

Data subject to change

Features

- Linear luminaire in one- or two-metre lengths
- Driver not integrated: remote driver set-up
- Wide range of lumen packages: 3,000 to 30,000 lm
- Multiple mounting and connectivity options
- Compatible with tunnel controls from and third parties
- Service tag: QR-based identification for maintenance, installation and spare part information

Versions

TubeLine BGP360

Dimensional drawing

BGP360 LED30/740 DTS CFW C250W GP

Product details

TubeLine_BGP360-DP01.tif

TubeLine_BGP360-DP02.tif

TubeLine_BGP360-DP03.tif

TubeLine_BGP360-DP04.tif

TubeLine_BGP360-DP05.tif

TubeLine_BGP360-DP06.tif



TubeLine_BGP360-DP07.tif

TubeLine_BGP360-DP08.tif

TubeLine_BGP360_ZGP360-DP09.tif

General Information

Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	No
Service Tag	Yes

Light Technical

Upwards light output ratio	0
Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Luminaire light beam spread	150°
Optic type outdoor	Distribution tunnel symmetrical

Operating and Electrical

Surge Protection (Common/ Differential)	-

Controls and Dimming

Dimmable	No

Mechanical and Housing

Housing Colour	Aluminium
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Optical cover type	Flat glass

Approval and Application

Flammability mark	-
CE mark	Yes

Product Data

Product family code	BGP360 [TUBELINE]

General Information

Order Code	Full Product Name	Lamp family code
912300023650	BGP360 LED30/740 DTS CFW C250W GP	LED30
912300023653	BGP360 LED120/740 DTS CFW C250W GP	LED120

Light Technical

Order Code	Full Product Name	Luminous Flux	Number of light sources
912300023650	BGP360 LED30/740 DTS CFW C250W GP	2,700 lm	24
912300023653	BGP360 LED120/740 DTS CFW C250W GP	10,800 lm	48

Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300023650	BGP360 LED30/740 DTS CFW C250W GP	18.8 W
912300023653	BGP360 LED120/740 DTS CFW C250W GP	72 W

© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.