



Amazingly Linear,. Brighter, Comfortable and Safer. .

LineBase

LineBase is breakthrough lighting for the city tunnel, underpass. It's a really and amazingly linear lighting yet easy to install, and it's the ideal solution to replace fluorescent lighting. The customized lumen output of LineBase enables lighting designers to have freedom on lighting layout. Its continuous installation is to create a seamless, brighter, comfortable visual effect with less flicker. Its plug-and-play electrical connection and remote waterproof drivers save total cost of owner. The products pass kinds of safety and durability test to prove a long lifespan on its operation.

Benefits

- Continuous installation for visual comfort
- Flexible lumen package for more application
- Remote driver attached to housing for flexibility
- Compact end cap for amazing linear yet easy to install

Features

- Wattage ranges from 10-60W, lumen output customized
- Slim and linear housing, compact end cap with positioning-slot
- Typical 120-130lm/w system efficacy
- IP 67 connector for plug-and-play quick installation
- Loop in-and loop out wiring for easy installation

Application

- City tunnel
- Underpass
- Road lighting
- Industrial areas

Warnings and Safety

- Strongly recommended to use surge protection device in electricity cabinet to wire luminaires

Specifications

| | |
|---|---|
| Material | Housing: die-cast aluminium Optic cover: glass |
| Light Source | 2835/3030 LED |
| Installation | Fixed and adjustable bracket options Adjustable tilting angle +/- 60D |
| Luminous flux | up to 38400lm |
| Correlated color temperature - CCT | 5000K4000K3000K |
| Luminaire efficacy | 4000K: 115-125lm/W |
| Color Rendering index - 70 CRI | |

| | |
|------------------------------------|---------------------|
| Power | up to 320W |
| Mains Voltage | 220-240VAC, 50/60Hz |
| Control system input | 1-10V |
| Dimming | 1-10VStep dimming |
| Operating Temperature range | -40 to +50C Ta |
| Ingress protection | IP66 |
| Certification | CQC |

Versions



LineBase

Dimensional drawing



General Information

Driver included No

Light Technical

Light source color 840 neutral white

Correlated Color Temperature (Nom) 4000 K

Color rendering index (CRI) >70

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Optical cover type Polycarbonate
Diffuser

Housing Color Aluminum

Mech. impact protection code IK05

Ingress protection code IP66

Approval and Application

CE mark No

Flammability mark -

Light Technical

| Order Code | Full Product Name | Luminous Flux |
|--------------|--------------------------------|---------------|
| 911401698407 | BGP472 LED14/36 NW 12/30W G2 F | 3,780 lm |
| 911401699107 | BGP472 LED48/72 NW 40/60W G2 A | 7,640 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|--------------|--------------------------------|-------------------|
| 911401698407 | BGP472 LED14/36 NW 12/30W G2 F | 30 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|--------------------------------|-------------------|
| 911401699107 | BGP472 LED48/72 NW 40/60W G2 A | 60 W |

