



Get your city ready for the future with DigiStreet

Developed with the aim to become your long term partner, the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

Benefits

- Prepared for the future, it is easy to upgrade directly after installation or later with future CMS nodes and sensors to enable new functionalities
- Large availability of lense optics to match international road and street geometries
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Applications

- Traffic routes and main access road
- Urban and residential area
- City centers and main streets
- Cycle paths, footpaths and pedestrian crossings

Features

- Easy luminaire identification due to the Service tag
- High efficacy up to 161 lm/W
- Choice of 30+ different beams and different internal louvers


- Surge protection, 10 kV
- L-tune tool available
- Lifetime 100Khrs up to L96 at Tq +25 °C
- Internal louver (optional)

Versions

Digistreet-BGP762-DP03



Digistreet-BGP760




Digistreet-BGP763-DP04



Digistreet-BGP761-DP07




Dimensional drawing




BGP760

DigiStreet Mini - LED Module 4500 lm - 518 ClearStar WW - Safety class II - Distribution medium 11 - Dark gray - Luminaire surge protection level until 6 kV differential mode and 8 kV common mode - Spigot for diameter 62 mm



DigiStreet Medium - LED module 21000 lm - 740 neutral white - Safety class II - Distribution extra wide 70 - Dark gray - Luminaire surge protection level until 6 kV differential mode and 8 kV common mode - Spigot for diameter 76 mm



DigiStreet Large - LED module 26000 lm - 740 neutral white - Safety class I - Distribution extra wide 10 - Dark gray - Luminaire surge protection level until 6 kV differential mode and 8 kV common mode - Spigot for diameter 32 to 48 mm

Product details

Digistreet-BGP760-DP06.tif



Digistreet-BGP760-DP09.tif






Digistreet-BGP760-DP10.tif



Digistreet-BGP760-DP11.tif



Digistreet-BGP761-DP17.tif



Digistreet-BGP761-DP18.tif



Digistreet-BGP761-DP19.tif



Digistreet-BGP761-DP20.tif



Digistreet-BGP761-DP21.tif



Digistreet-BGP761-DP22.tif



Digistreet-BGP761-DP23.tif



Digistreet-BGP761-DP24.tif

Digistreet-BGP761-DP25.tif



Digistreet-BGP761-DP26.tif



General Information

Light source replaceable	Yes
Gear	EB [Electronic]
Driver included	Yes
Service tag	Yes

Light Technical

Upward light output ratio	0
Number of light sources	1

Mechanical and Housing

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Flat glass

Approval and Application

Glow-wire test	Temperature 650 °C, duration 5 s
Flammability mark	-
CE mark	Yes

General Information

Order Code	Full Product Name	Lamp family code	Number of gear units
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	LED95	1 unit
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	LED95	1 unit
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	LED120	1 unit
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	LED159	1 unit
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	LED129	1 unit

Order Code	Full Product Name	Lamp family code	Number of gear units
910925866223	BGP762 LED169-/740 I DS50 DGR 62	LED169	1 unit
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	LED110	1 unit
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	LED180	1 unit
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	LED139	1 unit
910925866229	BGP762 LED170-/830 II DW10 DGR 76	LED170	1 unit
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	LED95	1 unit
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	LED169	1 unit
910925866245	BGP762 LED200-/740 I DW50 DGR 62	LED200	1 unit
910925866246	BGP762 LED210-/740 II DX70 DGR 76	LED210	1 unit
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	LED190	1 unit
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	LED220	1 unit
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	LED159	1 unit
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	LED239	1 unit
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	LED239	1 unit
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	LED149	1 unit
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	LED239	1 unit
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	LED10	1 unit
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	LED12	1 unit
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	LED14	1 unit
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	LED16	1 unit
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	LED22	1 unit
910925863563	BGP760 LED30-/830 II DW10 DGR 62	LED30	1 unit
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	LED44	1 unit
910925863567	BGP760 LED49-/740 II DX70 DGR 62	LED49	1 unit
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	LED24	1 unit
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	LED44	1 unit
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	LED16	1 unit
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	LED16	1 unit
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	LED60	1 unit
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	LED60	1 unit
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	LED60	1 unit
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	LED49	1 unit
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	LED49	1 unit
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	LED280	2 units
910925866249	BGP763 LED300-/740 I DW50 DGR 62	LED300	2 units
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	LED260	2 units
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	LED340	2 units
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	LED260	2 units
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	LED360	2 units
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	LED360	2 units
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	LED360	2 units
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	LED45	1 unit

Order Code	Full Product Name	Lamp family code	Number of gear units
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	LED45	1 unit
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	LED45	1 unit
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	LED74	1 unit
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	LED94	1 unit
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	LED109	1 unit
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	LED55	1 unit
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	LED84	1 unit
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	LED50	1 unit
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	LED79	1 unit
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	LED59	1 unit
910925866241	BGP761 LED90-/740 II DW10 DGR 62	LED90	1 unit
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	LED74	1 unit
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	LED84	1 unit
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	LED119	1 unit
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	LED119	1 unit
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	LED84	1 unit

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	5,952 lm	1800 K	50	518 ClearStar WW	160° - 42° x 53°	Distribution medium 11
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	5,952 lm	2000 K	40	420 ClearStar NW	160° - 42° x 53°	Distribution medium 11
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	10,800 lm	3000 K	80	830 warm white	53° x 71°	Distribution narrow 11
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	13,920 lm	3000 K	80	830 warm white	-	Distribution medium 70
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	11,830 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925866223	BGP762 LED169-/740 I DS50 DGR 62	14,960 lm	4000 K	70	740 neutral white	32° x 29°	Distribution symmetrical 50
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	10,010 lm	4000 K	70	740 neutral white	68° x 158°	Distribution narrow 10
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	15,480 lm	4000 K	70	740 neutral white	150° - 43° x 67°	Distribution extra wide 10
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	12,740 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925866229	BGP762 LED170-/830 II DW10 DGR 76	15,300 lm	3000 K	80	830 warm white	61° x 150°	Distribution wide 10
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	8,640 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	14,960 lm	4000 K	70	740 neutral white	30°	Distribution symmetrical 50
910925866245	BGP762 LED200-/740 I DW50 DGR 62	17,200 lm	4000 K	70	740 neutral white	152° - 24° x 66°	Distribution wide 50

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925866246	BGP762 LED210-/740 II DX70 DGR 76	18,060 lm	4000 K	70	740 neutral white	106° x 86°	Distribution extra wide 70
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	17,100 lm	4000 K	70	740 neutral white	61° x 150°	Distribution wide 10
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	19,800 lm	4000 K	70	740 neutral white	61° x 150°	Distribution wide 10
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	14,240 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	20,700 lm	4000 K	70	740 neutral white	149° - 10° x 57°	Distribution medium 32
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	13,800 lm	4000 K	70	740 neutral white	152° - 25° x 66°	Distribution wide 50
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	13,195 lm	4000 K	70	740 neutral white	149° - 10° x 57°	Distribution medium 32
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	20,700 lm	4000 K	70	740 neutral white	149° - 10° x 57°	Distribution medium 32
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	900 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	1,092 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	1,274 lm	4000 K	70	740 neutral white	68° x 157°	Distribution narrow 10
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	1,456 lm	3000 K	80	830 warm white	53° x 71°	Distribution narrow 11
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	2,002 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925863563	BGP760 LED30-/830 II DW10 DGR 62	2,730 lm	3000 K	80	830 warm white	61° x 150°	Distribution wide 10
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	3,784 lm	4000 K	70	740 neutral white	152° - 24° x 66°	Distribution wide 50
910925863567	BGP760 LED49-/740 II DX70 DGR 62	4,263 lm	4000 K	70	740 neutral white	106° x 44°	Distribution extra wide 70
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	2,070 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	3,827 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	992 lm	1800 K	50	518 ClearStar WW	160° - 42° x 53°	Distribution medium 11
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	992 lm	2000 K	40	420 ClearStar NW	160° - 42° x 53°	Distribution medium 11
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	5,340 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	4,988 lm	4000 K	70	740 neutral white	151° - 43° x 67°	Distribution extra wide 10
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	4,988 lm	4000 K	70	740 neutral white	152° - 25° x 66°	Distribution wide 50
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	3,588 lm	4000 K	70	740 neutral white	149° - 10° x 57°	Distribution medium 32

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	4,900 lm	4000 K	70	740 neutral white	149° - 10° x 57°	Distribution medium 32
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	21,360 lm	3000 K	80	830 warm white	61° x 150°	Distribution wide 10
910925866249	BGP763 LED300-/740 I DW50 DGR 62	25,200 lm	4000 K	70	740 neutral white	152° - 24° x 66°	Distribution wide 50
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	22,100 lm	4000 K	70	740 neutral white	150° - 43° x 67°	Distribution extra wide 10
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	29,920 lm	4000 K	70	740 neutral white	61° x 150°	Distribution wide 10
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	23,140 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	31,320 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	28,560 lm	4000 K	70	740 neutral white	151° - 43° x 67°	Distribution extra wide 10
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	20,060 lm	4000 K	70	740 neutral white	152° - 25° x 66°	Distribution wide 50
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	2,790 lm	1800 K	50	518 ClearStar WW	160° - 42° x 53°	Distribution medium 11
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	2,790 lm	2000 K	40	420 ClearStar NW	160° - 42° x 53°	Distribution medium 11
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	4,050 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	6,660 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	8,084 lm	4000 K	70	740 neutral white	150° - 43° x 67°	Distribution extra wide 10
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	9,790 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	5,096 lm	4000 K	70	740 neutral white	68° x 157°	Distribution narrow 10
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	7,392 lm	4000 K	70	740 neutral white	32° x 29°	Distribution symmetrical 50
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	4,550 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	6,688 lm	3000 K	80	830 warm white	-	Distribution medium 70
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	5,400 lm	3000 K	80	830 warm white	53° x 71°	Distribution narrow 11
910925866241	BGP761 LED90-/740 II DW10 DGR 62	8,100 lm	4000 K	70	740 neutral white	61° x 150°	Distribution wide 10
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	6,660 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	7,476 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	10,680 lm	4000 K	70	740 neutral white	157° - 33° x 55°	Distribution medium 10
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	6,900 lm	4000 K	70	740 neutral white	152° - 25° x 66°	Distribution wide 50
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	7,462 lm	4000 K	70	740 neutral white	149° - 10° x 57°	Distribution medium 32

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	69 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	55 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	81 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	106 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	72 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866223	BGP762 LED169-/740 I DS50 DGR 62	98 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	100 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866229	BGP762 LED170-/830 II DW10 DGR 76	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	53 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	99 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866245	BGP762 LED200-/740 I DW50 DGR 62	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866246	BGP762 LED210-/740 II DX70 DGR 76	120 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	106 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	126 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	86 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	6.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	9 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	11.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	13.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863563	BGP760 LED30-/830 II DW10 DGR 62	21 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	26 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863567	BGP760 LED49-/740 II DX70 DGR 62	29.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	15 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	26 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	13.6 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	11.2 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	38 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	37 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	37 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	29.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	33.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	160 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866249	BGP763 LED300-/740 I DW50 DGR 62	176 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	150 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	196 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	154 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	215 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	198 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	198 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	34 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	27.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	27 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	43.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	63 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	31.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	34 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866241	BGP761 LED90-/740 II DW10 DGR 62	51 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	43.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	72 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	50 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	Yes	Not applicable
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	Yes	Not applicable
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Yes	Not applicable
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Yes	50%
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	No	Not applicable
910925866223	BGP762 LED169-/740 I DS50 DGR 62	No	Not applicable
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	No	Not applicable
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	No	Not applicable
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866229	BGP762 LED170-/830 II DW10 DGR 76	No	Not applicable
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	Yes	0% (digital)
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Yes	Not applicable
910925866245	BGP762 LED200-/740 I DW50 DGR 62	No	Not applicable
910925866246	BGP762 LED210-/740 II DX70 DGR 76	No	Not applicable
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	No	Not applicable
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Yes	0% (digital)
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	Yes	50%
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Yes	0% (digital)
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	No	Not applicable
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Yes	Not applicable
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	No	Not applicable
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Yes	Not applicable
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	No	Not applicable
910925863563	BGP760 LED30-/830 II DW10 DGR 62	No	Not applicable
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	No	Not applicable
910925863567	BGP760 LED49-/740 II DX70 DGR 62	No	Not applicable
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	Yes	50%
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	Yes	50%
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	Yes	Not applicable
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	Yes	Not applicable
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	Yes	Not applicable
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	Yes	0% (digital)
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	Yes	0% (digital)
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	Yes	50%
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	Yes	50%
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	No	Not applicable
910925866249	BGP763 LED300-/740 I DW50 DGR 62	No	Not applicable
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	No	Not applicable
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Yes	Not applicable
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Yes	Not applicable
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	No	0% (digital)
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	No	0% (digital)
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	Yes	Not applicable
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	Yes	Not applicable
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	No	Not applicable
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	No	Not applicable
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	No	Not applicable
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Yes	50%
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	No	Not applicable
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	No	Not applicable
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Yes	50%
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Yes	Not applicable
910925866241	BGP761 LED90-/740 II DW10 DGR 62	No	Not applicable
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Yes	Not applicable
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	No	Not applicable
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Yes	Not applicable
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	Yes	0% (digital)
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	Yes	50%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	Dark gray
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	Dark gray
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Dark gray
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Dark gray
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	Dark gray
910925866223	BGP762 LED169-/740 I DS50 DGR 62	Dark gray
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	Dark gray
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	Dark gray
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Dark gray
910925866229	BGP762 LED170-/830 II DW10 DGR 76	Dark gray
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	Dark gray
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Dark gray
910925866245	BGP762 LED200-/740 I DW50 DGR 62	Dark gray
910925866246	BGP762 LED210-/740 II DX70 DGR 76	Dark gray
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	Dark gray
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	Dark gray
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	Dark gray
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Gray
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	Dark gray
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	Gray
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Gray
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	Dark gray
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Dark gray
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	Dark gray
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Dark gray
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	Dark gray
910925863563	BGP760 LED30-/830 II DW10 DGR 62	Dark gray
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	Dark gray
910925863567	BGP760 LED49-/740 II DX70 DGR 62	Dark gray
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	Dark gray
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	Dark gray
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	Dark gray
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	Dark gray
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	Dark gray
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	Dark gray
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	Dark gray
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	Gray
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	Dark gray
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	Dark gray
910925866249	BGP763 LED300-/740 I DW50 DGR 62	Dark gray
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	Dark gray

Order Code	Full Product Name	Housing Color
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	Dark gray
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Dark gray
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Dark gray
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	Dark gray
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	Dark gray
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	Dark gray
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	Dark gray
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	Dark gray
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	Dark gray
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	Dark gray
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Dark gray
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	Dark gray
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	Dark gray
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Dark gray
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Dark gray
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Dark gray
910925866241	BGP761 LED90-/740 II DW10 DGR 62	Dark gray
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Dark gray
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	Dark gray
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Dark gray
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	Dark gray
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	Gray


Product Data

Order Code	Full Product Name	Product family code
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	BGP762
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	BGP762
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	BGP762
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	BGP762
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	BGP762
910925866223	BGP762 LED169-/740 I DS50 DGR 62	BGP762
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	BGP762
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	BGP762
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	BGP762
910925866229	BGP762 LED170-/830 II DW10 DGR 76	BGP762
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	BGP762
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	BGP762
910925866245	BGP762 LED200-/740 I DW50 DGR 62	BGP762
910925866246	BGP762 LED210-/740 II DX70 DGR 76	BGP762
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	BGP762
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	BGP762
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	BGP762

Order Code	Full Product Name	Product family code
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	BGP762
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	BGP762
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	BGP762
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	BGP762
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	BGP760
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	BGP760
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	BGP760
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	BGP760
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	BGP760
910925863563	BGP760 LED30-/830 II DW10 DGR 62	BGP760
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	BGP760
910925863567	BGP760 LED49-/740 II DX70 DGR 62	BGP760
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	BGP760
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	BGP760
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	BGP760
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	BGP760
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	BGP760
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	BGP760
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	BGP760
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	BGP760
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	BGP760
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	BGP763
910925866249	BGP763 LED300-/740 I DW50 DGR 62	BGP763
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	BGP763
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	BGP763
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	BGP763
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	BGP763
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	BGP763
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	BGP763
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	BGP761
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	BGP761
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	BGP761
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	BGP761
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	BGP761
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	BGP761
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	BGP761
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	BGP761
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	BGP761
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	BGP761
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	BGP761
910925866241	BGP761 LED90-/740 II DW10 DGR 62	BGP761
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	BGP761

Order Code	Full Product Name	Product family code
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	BGP761
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	BGP761
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	BGP761
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	BGP761


Polar normal diagrams



BGP762I - 910925866229

BGP761I - 910925866232


BGP763I - 910925866249




BGP762I - 910925866228

BGP763I - 910925866251


BGP762I - 910925866220




BGP762I - 910925866221




BGP762I - 910925866246




BGP761I - 910925866497




BGP760I - 910925863554




BGP760I - 910925863567




BGP760I - 910925863563




BGP760I - 910925863566




BGP760I - 910925863560




BGP760I - 910925864083




BGP761I - 910925866230




BGP761I - 910925866238




BGP763I - 910925866250




BGP761I - 910925866233




BGP762I - 910925866224




BGP761I - 910925866235




BGP761I - 910925866241




BGP762I - 910925866222




BGP761I - 910925866234




BGP762I - 910925866247




BGP762I - 910925866252




BGP763I - 910925866248




BGP762I - 910925866226




BGP761I - 910925866237




BGP761I - 910925866239




BGP761I - 910925866240




BGP762I - 910925866245




BGP760I - 910925863556




BGP760I - 910925863557




BGP760I - 910925863555




BGP760I - 910925864084




BGP762I - 910925866493




BGP763I - 910925866494



BGP760I - 910925866495



BGP763I - 910925866498



BGP761I - 910925866231