



# Get your city ready for the future with DigiStreet

## DigiStreet

Developed with the aim to become your long term partner, the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

### Benefits

- Prepared for the future, it is easy to upgrade directly after installation or later with future CMS nodes and sensors to enable new functionalities
- Large availability of lense optics to match international road and street geometries
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information


**Features**

- Easy luminaire identification due to the Service tag
- High efficacy up to 161 lm/W
- Choice of 30+ different beams and different internal louvers
- Surge protection, 10 kV
- L-tune tool available
- Lifetime 100Khrs up to L96 at Tq +25 °C
- Internal louver (optional)

**Application**

- Traffic routes and main access road
- Urban and residential area
- City centers and main streets
- Cycle paths, footpaths and pedestrian crossings

**Dimensional drawing**



Product details

Digistreet-BGP760-DP06.tif



Digistreet-BGP760-DP09.tif



Digistreet-BGP760-DP10.tif




Digistreet-BGP760-DP11.tif




Digistreet-BGP761-DP17.tif



Digistreet-BGP761-DP18.tif



Digistreet-BGP761-DP19.tif



Digistreet-BGP761-DP20.tif



Product details



Digistreet-BGP761-DP21.tif



Digistreet-BGP761-DP22.tif



Digistreet-BGP761-DP23.tif



Digistreet-BGP761-DP24.tif



Digistreet-BGP761-DP25.tif



Digistreet-BGP761-DP26.tif

General Information	
Driver included	Yes
Light source replaceable	Yes
Service tag	Yes
Light Technical	
Upward light output ratio	0
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Dark gray
Mech. impact protection code	IK09
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-

General Information

Order Code	Full Product Name	Gear	Lamp family code	Number of gear units
37827400	BGP762 LED120-/830 II DN11 DGR D11 76	-	LED120	1 unit
37831100	BGP762 LED159-/830 II DM70 DGR DDF27 D18	-	LED159	1 unit
37828100	BGP762 LED129-/740 I DM11 DGR 32-48	-	LED129	1 unit
37832800	BGP762 LED169-/740 I DS50 DGR 62	-	LED169	1 unit
37826700	BGP762 LED110-/740 I DN10 DGR 32-48	-	LED110	1 unit
37834200	BGP762 LED180-/740 I DX10 DGR 32-48	-	LED180	1 unit
37829800	BGP762 LED139-/830 II DM11 DGR D9 62	-	LED139	1 unit
37833500	BGP762 LED170-/830 II DW10 DGR 76	-	LED170	1 unit
37836600	BGP762 LED200-/740 I DW50 DGR 62	-	LED200	1 unit
37837300	BGP762 LED210-/740 II DX70 DGR 76	-	LED210	1 unit
37835900	BGP762 LED190-/740 II DW10 DGR SRG10 62	-	LED190	1 unit
37838000	BGP762 LED220-/740 II DW10 DGR SRG10 62	-	LED220	1 unit
05926900	BGP762 LED159/740 I DM10 DGR 62 S	-	LED159	1 unit
37680500	BGP760 LED12-/830 II DM11 DGR D9 62	EB	LED12	1 unit
37688100	BGP760 LED30-/830 II DW10 DGR 62	EB	LED30	1 unit
37692800	BGP760 LED49-/740 II DX70 DGR 62	EB	LED49	1 unit
38203500	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	-	LED24	1 unit
38204200	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	-	LED44	1 unit
37841000	BGP763 LED240-/830 II DW10 DGR SRG10 62	-	LED280	2 units
37842700	BGP763 LED300-/740 I DW50 DGR 62	-	LED300	2 units
37840300	BGP763 LED260-/740 I DX10 DGR 32-48	-	LED260	2 units
37844100	BGP763 LED340-/740 II DW10 DGR SRG10 62	-	LED340	2 units
37693500	BGP761 LED45-/740 I DM10 DGR 32-48	-	LED45	1 unit
37699700	BGP761 LED74-/740 I DM50 DGR 32-48	-	LED74	1 unit
37703100	BGP761 LED94-/740 I DX10 DGR 32-48	-	LED94	1 unit
38206600	BGP761 LED109-/740 I DM10 DGR DDF27 D18	-	LED109	1 unit
37695900	BGP761 LED55-/740 I DN10 DGR 32-48	-	LED55	1 unit
37701700	BGP761 LED84-/740 I DS50 DGR 32-48	-	LED84	1 unit
37694200	BGP761 LED50-/830 II DM11 DGR D9 62	-	LED50	1 unit
37700000	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-	LED79	1 unit
37696600	BGP761 LED59-/830 II DN11 DGR D11 62	-	LED59	1 unit
37702400	BGP761 LED90-/740 II DW10 DGR 62	-	LED90	1 unit
38597500	BGP761 LED74-/740 I DM50 DGR SRB 62	-	LED74	1 unit
05929000	BGP761 LED84/740 I DM10 DGR 62 S	-	LED84	1 unit

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
37827400	BGP762 LED120-/830 II DN11 DGR D11 76	53° x 71°	830 warm white	3000 K	80
37831100	BGP762 LED159-/830 II DM70 DGR DDF27 D18	-	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
37828100	BGP762 LED129-/740 I DM11 DGR 32-48	160° - 42° x 54°	740 neutral white	4000 K	70
37832800	BGP762 LED169-/740 I DS50 DGR 62	32° x 29°	740 neutral white	4000 K	70
37826700	BGP762 LED110-/740 I DN10 DGR 32-48	68° x 158°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
37834200	BGP762 LED180-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
37829800	BGP762 LED139-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
37833500	BGP762 LED170-/830 II DW10 DGR 76	61° x 150°	830 warm white	3000 K	80
37836600	BGP762 LED200-/740 I DW50 DGR 62	152° - 24° x 66°	740 neutral white	4000 K	70
37837300	BGP762 LED210-/740 II DX70 DGR 76	106° x 86°	740 neutral white	4000 K	70
37835900	BGP762 LED190-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
37838000	BGP762 LED220-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
05926900	BGP762 LED159/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
37680500	BGP760 LED12-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
37688100	BGP760 LED30-/830 II DW10 DGR 62	61° x 150°	830 warm white	3000 K	80
37692800	BGP760 LED49-/740 II DX70 DGR 62	106° x 44°	740 neutral white	4000 K	70
38203500	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	157° - 33° x 55°	740 neutral white	4000 K	70
38204200	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	157° - 33° x 55°	740 neutral white	4000 K	70
37841000	BGP763 LED240-/830 II DW10 DGR SRG10 62	61° x 150°	830 warm white	3000 K	80
37842700	BGP763 LED300-/740 I DW50 DGR 62	152° - 24° x 66°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
37840300	BGP763 LED260-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
37844100	BGP763 LED340-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
37693500	BGP761 LED45-/740 I DM10 DGR 32-48	157° - 33° x 55°	740 neutral white	4000 K	70
37699700	BGP761 LED74-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70
37703100	BGP761 LED94-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
38206600	BGP761 LED109-/740 I DM10 DGR DDF27 D18	157° - 33° x 55°	740 neutral white	4000 K	70
37695900	BGP761 LED55-/740 I DN10 DGR 32-48	68° x 157°	740 neutral white	4000 K	70
37701700	BGP761 LED84-/740 I DS50 DGR 32-48	32° x 29°	740 neutral white	4000 K	70
37694200	BGP761 LED50-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
37700000	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-	830 warm white	3000 K	80
37696600	BGP761 LED59-/830 II DN11 DGR D11 62	53° x 71°	830 warm white	3000 K	80
37702400	BGP761 LED90-/740 II DW10 DGR 62	61° x 150°	740 neutral white	4000 K	70
38597500	BGP761 LED74-/740 I DM50 DGR SRB 62	154° - 31° x 54°	740 neutral white	4000 K	70
05929000	BGP761 LED84/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
37827400	BGP762 LED120-/830 II DN11 DGR D11 76	10,800 lm	-	Distribution narrow 11
37831100	BGP762 LED159-/830 II DM70 DGR DDF27 D18	13,920 lm	-	Distribution medium 70
37828100	BGP762 LED129-/740 I DM11 DGR 32-48	11,830 lm	-	Distribution medium 11
37832800	BGP762 LED169-/740 I DS50 DGR 62	14,960 lm	-	Distribution symmetrical 50
37826700	BGP762 LED110-/740 I DN10 DGR 32-48	10,010 lm	-	Distribution narrow 10
37834200	BGP762 LED180-/740 I DX10 DGR 32-48	15,480 lm	-	Distribution extra wide 10
37829800	BGP762 LED139-/830 II DM11 DGR D9 62	12,740 lm	-	Distribution medium 11
37833500	BGP762 LED170-/830 II DW10 DGR 76	15,300 lm	-	Distribution wide 10
37836600	BGP762 LED200-/740 I DW50 DGR 62	17,200 lm	-	Distribution wide 50
37837300	BGP762 LED210-/740 II DX70 DGR 76	18,060 lm	-	Distribution extra wide 70
37835900	BGP762 LED190-/740 II DW10 DGR SRG10 62	17,100 lm	-	Distribution wide 10
37838000	BGP762 LED220-/740 II DW10 DGR SRG10 62	19,800 lm	-	Distribution wide 10
05926900	BGP762 LED159/740 I DM10 DGR 62 S	14,240 lm	-	Distribution medium 10
37680500	BGP760 LED12-/830 II DM11 DGR D9 62	1,092 lm	1	Distribution medium 11
37688100	BGP760 LED30-/830 II DW10 DGR 62	2,730 lm	1	Distribution wide 10
37692800	BGP760 LED49-/740 II DX70 DGR 62	4,263 lm	1	Distribution extra wide 70
38203500	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	2,070 lm	-	Distribution medium 10

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
38204200	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	3,827 lm	-	Distribution medium 10
37841000	BGP763 LED240-/830 II DW10 DGR SRG10 62	21,360 lm	-	Distribution wide 10
37842700	BGP763 LED300-/740 I DW50 DGR 62	25,200 lm	-	Distribution wide 50
37840300	BGP763 LED260-/740 I DX10 DGR 32-48	22,100 lm	-	Distribution extra wide 10
37844100	BGP763 LED340-/740 II DW10 DGR SRG10 62	29,920 lm	-	Distribution wide 10
37693500	BGP761 LED45-/740 I DM10 DGR 32-48	4,050 lm	-	Distribution medium 10
37699700	BGP761 LED74-/740 I DM50 DGR 32-48	6,660 lm	-	Distribution medium 50
37703100	BGP761 LED94-/740 I DX10 DGR 32-48	8,084 lm	-	Distribution extra wide 10
38206600	BGP761 LED109-/740 I DM10 DGR DDF27 D18	9,790 lm	-	Distribution medium 10
37695900	BGP761 LED55-/740 I DN10 DGR 32-48	5,096 lm	-	Distribution narrow 10
37701700	BGP761 LED84-/740 I DS50 DGR 32-48	7,392 lm	-	Distribution symmetrical 50
37694200	BGP761 LED50-/830 II DM11 DGR D9 62	4,550 lm	-	Distribution medium 11
37700000	BGP761 LED79-/830 II DM70 DGR DDF27 D18	6,688 lm	-	Distribution medium 70
37696600	BGP761 LED59-/830 II DN11 DGR D11 62	5,400 lm	-	Distribution narrow 11
37702400	BGP761 LED90-/740 II DW10 DGR 62	8,100 lm	-	Distribution wide 10
38597500	BGP761 LED74-/740 I DM50 DGR SRB 62	6,660 lm	-	Distribution medium 50
05929000	BGP761 LED84/740 I DM10 DGR 62 S	7,476 lm	-	Distribution medium 10

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
37827400	BGP762 LED120-/830 II DN11 DGR D11 76	81 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37831100	BGP762 LED159-/830 II DM70 DGR DDF27 D18	106 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37828100	BGP762 LED129-/740 I DM11 DGR 32-48	72 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
37832800	BGP762 LED169-/740 I DS50 DGR 62	98 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37826700	BGP762 LED110-/740 I DN10 DGR 32-48	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37834200	BGP762 LED180-/740 I DX10 DGR 32-48	100 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
37829800	BGP762 LED139-/830 II DM11 DGR D9 62	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37833500	BGP762 LED170-/830 II DW10 DGR 76	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37836600	BGP762 LED200-/740 I DW50 DGR 62	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37837300	BGP762 LED210-/740 II DX70 DGR 76	120 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37835900	BGP762 LED190-/740 II DW10 DGR SRG10 62	106 W	Surge protection level until 10 kV differential mode and 10 kV common mode
37838000	BGP762 LED220-/740 II DW10 DGR SRG10 62	126 W	Surge protection level until 10 kV differential mode and 10 kV common mode
05926900	BGP762 LED159/740 I DM10 DGR 62 S	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37680500	BGP760 LED12-/830 II DM11 DGR D9 62	8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37688100	BGP760 LED30-/830 II DW10 DGR 62	21 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37692800	BGP760 LED49-/740 II DX70 DGR 62	29.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
38203500	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	15 W	Surge protection level until 10 kV differential mode and 10 kV common mode
38204200	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	26 W	Surge protection level until 10 kV differential mode and 10 kV common mode
37841000	BGP763 LED240-/830 II DW10 DGR SRG10 62	160 W	Surge protection level until 10 kV differential mode and 10 kV common mode
37842700	BGP763 LED300-/740 I DW50 DGR 62	176 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
37840300	BGP763 LED260-/740 I DX10 DGR 32-48	150 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37844100	BGP763 LED340-/740 II DW10 DGR SRG10 62	196 W	Surge protection level until 10 kV differential mode and 10 kV common mode
37693500	BGP761 LED45-/740 I DM10 DGR 32-48	27 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37699700	BGP761 LED74-/740 I DM50 DGR 32-48	43.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37703100	BGP761 LED94-/740 I DX10 DGR 32-48	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
38206600	BGP761 LED109-/740 I DM10 DGR DDF27 D18	63 W	Surge protection level until 10 kV differential mode and 10 kV common mode
37695900	BGP761 LED55-/740 I DN10 DGR 32-48	31.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37701700	BGP761 LED84-/740 I DS50 DGR 32-48	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37694200	BGP761 LED50-/830 II DM11 DGR D9 62	34 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37700000	BGP761 LED79-/830 II DM70 DGR DDF27 D18	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37696600	BGP761 LED59-/830 II DN11 DGR D11 62	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
37702400	BGP761 LED90-/740 II DW10 DGR 62	51 W	Surge protection level until 6 kV differential mode and 8 kV common mode
38597500	BGP761 LED74-/740 I DM50 DGR SRB 62	43.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
05929000	BGP761 LED84/740 I DM10 DGR 62 S	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode

**Controls and Dimming**

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
37827400	BGP762 LED120-/830 II DN11 DGR D11 76	Yes	Not applicable
37831100	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Yes	50%
37828100	BGP762 LED129-/740 I DM11 DGR 32-48	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
37832800	BGP762 LED169-/740 I DS50 DGR 62	No	Not applicable
37826700	BGP762 LED110-/740 I DN10 DGR 32-48	No	Not applicable
37834200	BGP762 LED180-/740 I DX10 DGR 32-48	No	Not applicable
37829800	BGP762 LED139-/830 II DM11 DGR D9 62	Yes	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
37833500	BGP762 LED170-/830 II DW10 DGR 76	No	Not applicable
37836600	BGP762 LED200-/740 I DW50 DGR 62	No	Not applicable
37837300	BGP762 LED210-/740 II DX70 DGR 76	No	Not applicable
37835900	BGP762 LED190-/740 II DW10 DGR SRG10 62	No	Not applicable
37838000	BGP762 LED220-/740 II DW10 DGR SRG10 62	No	Not applicable
05926900	BGP762 LED159/740 I DM10 DGR 62 S	No	Not applicable
37680500	BGP760 LED12-/830 II DM11 DGR D9 62	Yes	Not applicable
37688100	BGP760 LED30-/830 II DW10 DGR 62	No	Not applicable
37692800	BGP760 LED49-/740 II DX70 DGR 62	No	Not applicable
38203500	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	Yes	50%
38204200	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	Yes	50%
37841000	BGP763 LED240-/830 II DW10 DGR SRG10 62	No	Not applicable
37842700	BGP763 LED300-/740 I DW50 DGR 62	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
37840300	BGP763 LED260-/740 I DX10 DGR 32-48	No	Not applicable
37844100	BGP763 LED340-/740 II DW10 DGR SRG10 62	No	Not applicable
37693500	BGP761 LED45-/740 I DM10 DGR 32-48	No	Not applicable
37699700	BGP761 LED74-/740 I DM50 DGR 32-48	No	Not applicable
37703100	BGP761 LED94-/740 I DX10 DGR 32-48	No	Not applicable
38206600	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Yes	50%
37695900	BGP761 LED55-/740 I DN10 DGR 32-48	No	Not applicable
37701700	BGP761 LED84-/740 I DS50 DGR 32-48	No	Not applicable
37694200	BGP761 LED50-/830 II DM11 DGR D9 62	Yes	Not applicable
37700000	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Yes	50%
37696600	BGP761 LED59-/830 II DN11 DGR D11 62	Yes	Not applicable
37702400	BGP761 LED90-/740 II DW10 DGR 62	No	Not applicable
38597500	BGP761 LED74-/740 I DM50 DGR SRB 62	Yes	Not applicable
05929000	BGP761 LED84/740 I DM10 DGR 62 S	No	Not applicable

Approval and Application

Order Code	Full Product Name	Glow-wire test
37827400	BGP762 LED120-/830 II DN11 DGR D11 76	-
37831100	BGP762 LED159-/830 II DM70 DGR DDF27 D18	-
37828100	BGP762 LED129-/740 I DM11 DGR 32-48	-
37832800	BGP762 LED169-/740 I DS50 DGR 62	-
37826700	BGP762 LED110-/740 I DN10 DGR 32-48	-
37834200	BGP762 LED180-/740 I DX10 DGR 32-48	-
37829800	BGP762 LED139-/830 II DM11 DGR D9 62	-
37833500	BGP762 LED170-/830 II DW10 DGR 76	-
37836600	BGP762 LED200-/740 I DW50 DGR 62	-
37837300	BGP762 LED210-/740 II DX70 DGR 76	-
37835900	BGP762 LED190-/740 II DW10 DGR SRG10 62	-
37838000	BGP762 LED220-/740 II DW10 DGR SRG10 62	-
05926900	BGP762 LED159/740 I DM10 DGR 62 S	-
37680500	BGP760 LED12-/830 II DM11 DGR D9 62	Temperature 650 °C, duration 5 s
37688100	BGP760 LED30-/830 II DW10 DGR 62	Temperature 650 °C, duration 5 s
37692800	BGP760 LED49-/740 II DX70 DGR 62	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Glow-wire test
38203500	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	-
38204200	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	-
37841000	BGP763 LED240-/830 II DW10 DGR SRG10 62	-
37842700	BGP763 LED300-/740 I DW50 DGR 62	-
37840300	BGP763 LED260-/740 I DX10 DGR 32-48	-
37844100	BGP763 LED340-/740 II DW10 DGR SRG10 62	-
37693500	BGP761 LED45-/740 I DM10 DGR 32-48	-
37699700	BGP761 LED74-/740 I DM50 DGR 32-48	-
37703100	BGP761 LED94-/740 I DX10 DGR 32-48	-
38206600	BGP761 LED109-/740 I DM10 DGR DDF27 D18	-
37695900	BGP761 LED55-/740 I DN10 DGR 32-48	-
37701700	BGP761 LED84-/740 I DS50 DGR 32-48	-
37694200	BGP761 LED50-/830 II DM11 DGR D9 62	-
37700000	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-
37696600	BGP761 LED59-/830 II DN11 DGR D11 62	-
37702400	BGP761 LED90-/740 II DW10 DGR 62	-
38597500	BGP761 LED74-/740 I DM50 DGR SRB 62	-
05929000	BGP761 LED84/740 I DM10 DGR 62 S	-

Product Data




Order Code	Full Product Name	Product family code
37827400	BGP762 LED120-/830 II DN11 DGR D11 76	BGP762
37831100	BGP762 LED159-/830 II DM70 DGR DDF27 D18	BGP762
37828100	BGP762 LED129-/740 I DM11 DGR 32-48	BGP762
37832800	BGP762 LED169-/740 I DS50 DGR 62	BGP762
37826700	BGP762 LED110-/740 I DN10 DGR 32-48	BGP762

Order Code	Full Product Name	Product family code
37834200	BGP762 LED180-/740 I DX10 DGR 32-48	BGP762
37829800	BGP762 LED139-/830 II DM11 DGR D9 62	BGP762
37833500	BGP762 LED170-/830 II DW10 DGR 76	BGP762
37836600	BGP762 LED200-/740 I DW50 DGR 62	BGP762
37837300	BGP762 LED210-/740 II DX70 DGR 76	BGP762

Order Code	Full Product Name	Product family code
37835900	BGP762 LED190-/740 II DW10 DGR SRG10 62	BGP762
37838000	BGP762 LED220-/740 II DW10 DGR SRG10 62	BGP762
05926900	BGP762 LED159/740 I DM10 DGR 62 S	BGP762
37680500	BGP760 LED12-/830 II DM11 DGR D9 62	BGP760
37688100	BGP760 LED30-/830 II DW10 DGR 62	BGP760
37692800	BGP760 LED49-/740 II DX70 DGR 62	BGP760
38203500	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	BGP760
38204200	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	BGP760
37841000	BGP763 LED240-/830 II DW10 DGR SRG10 62	BGP763
37842700	BGP763 LED300-/740 I DW50 DGR 62	BGP763
37840300	BGP763 LED260-/740 I DX10 DGR 32-48	BGP763
37844100	BGP763 LED340-/740 II DW10 DGR SRG10 62	BGP763

Order Code	Full Product Name	Product family code
37693500	BGP761 LED45-/740 I DM10 DGR 32-48	BGP761
37699700	BGP761 LED74-/740 I DM50 DGR 32-48	BGP761
37703100	BGP761 LED94-/740 I DX10 DGR 32-48	BGP761
38206600	BGP761 LED109-/740 I DM10 DGR DDF27 D18	BGP761
37695900	BGP761 LED55-/740 I DN10 DGR 32-48	BGP761
37701700	BGP761 LED84-/740 I DS50 DGR 32-48	BGP761
37694200	BGP761 LED50-/830 II DM11 DGR D9 62	BGP761
37700000	BGP761 LED79-/830 II DM70 DGR DDF27 D18	BGP761
37696600	BGP761 LED59-/830 II DN11 DGR D11 62	BGP761
37702400	BGP761 LED90-/740 II DW10 DGR 62	BGP761
38597500	BGP761 LED74-/740 I DM50 DGR SRB 62	BGP761
05929000	BGP761 LED84/740 I DM10 DGR 62 S	BGP761




Polar Wide Diagrams



Polar Normal (separate) - BGP762I - 910925866229

Polar Normal (separate) - BGP761I - 910925866232

Polar Normal (separate) - BGP761I - 910925866242




Polar Normal (separate) - BGP763I - 910925866249


Polar Normal (separate) - BGP762I - 910925866228

Polar Normal (separate) - BGP763I - 910925866251


Polar Wide Diagrams




Polar Normal (separate) - BGP7621 - 910925866220




Polar Normal (separate) - BGP7621 - 910925866221




Polar Normal (separate) - BGP7621 - 910925866246




Polar Normal (separate) - BGP7601 - 910925863567




Polar Normal (separate) - BGP7601 - 910925863563




Polar Normal (separate) - BGP7601 - 910925864083



Polar Normal (separate) - BGP7621 - 910925866223




Polar Normal (separate) - BGP7611 - 910925866230




Polar Normal (separate) - BGP7611 - 910925866238




Polar Wide Diagrams




Polar Normal (separate) - BGP7631 - 910925866248




Polar Normal (separate) - BGP7621 - 910925866226




Polar Normal (separate) - BGP7611 - 910925866237




Polar Normal (separate) - BGP7611 - 910925866239




Polar Normal (separate) - BGP7611 - 910925866240




Polar Normal (separate) - BGP7621 - 910925866245



Polar Normal (separate) - BGP7601 - 910925863555



Polar Normal (separate) - BGP7601 - 910925864084



Polar Normal (separate) - BGP7621 - 910925866493

