



Sleek, reliable and cost-efficient LED lighting

SmartBright Road

The SmartBright road is ideal for new streets and for renovating existing installations, this affordable range of lighting solutions combines clean, high-quality light with significant energy savings and reduced maintenance.

Benefits

- Perfect for one to one replacement of conventional SON or HPL luminaires.
- Offer initial investment with good-quality and energy-efficient lighting.
- Fit wide application areas and suitable to use for residential street, main road and parking area

Features

- One to one replacement for 100W, 150W and 250W conventional SON or HPL luminaires
- Reliable design with diecast aluminum housing
- Fully IP66 Ingress and IK08 mechanical impacts protection
- 10kV/Ka replaceable surge protection device
- 30,000 hours L70 at 35C Ta rated lifetime
- 130lm/w luminous efficacy
- Operating temperature range - 40°C < Ta < 50°C
- Optimized optic for road and street lighting

Application

- Road and Residential street
- Parking area
- Walking/cycling path

Specifications

SmartBright Road

Material	Housing: die-cast aluminium Optic cover: polycarbonate
Light Source	3030 LED
Installation	Side entry 42-60mm Optional adjustable spigot
Luminous flux	System flux up to 18200lm
Correlated color temperature - CCT	5700K 4000K 3000K
Luminaire efficacy	4000K: 130lm/W
Color Rendering index - CRI	70




Power	up to 140W
Mains Voltage	220-240V / 50-60Hz
Control system input	N/A
Dimming	non-dimmable
Operating Temperature range	-40 to +50C Ta
Ingress protection	IP66
Certification	IECEE CB, CE, CQC, RCM

Versions



SmartBright Road

Dimensional drawing



Product details

BRP13 front



General Information		Light Technical			
Driver included	Yes	Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)
Service tag	Yes	911401676507	BRP132 LED175/WW 140W 220-240V DM GM	Warm white	3000 K
				DM GM	17,500 lm
Color rendering index (CRI)	>70	911401676607	BRP132 LED175/NW 140W 220-240V DM GM	Neutral white	4000 K
				DM GM	17,500 lm
Controls and Dimming		911401676707	BRP132 LED175/CW 140W 220-240V DM GM	Cool white	5700 K
Dimmable	No			DM GM	17,500 lm
Mechanical and Housing		911401676207	BRP131 LED125/WW 100W 220-240V DM GM	Warm white	3000 K
Optical cover type	Transparent bowl with transparent cover			DM GM	12,500 lm
Housing Color	Gray	911401676307	BRP131 LED125/NW 100W 220-240V DM GM	Neutral white	4000 K
Mech. impact protection code	IK08			DM GM	12,500 lm
Ingress protection code	IP66	911401676407	BRP131 LED125/CW 100W 220-240V DM GM	Cool white	5700 K
Approval and Application				DM GM	12,500 lm
CE mark	Yes	911401675907	BRP130 LED88/WW 70W 220-240V DM GM	Warm white	3000 K
Flammability mark	For mounting on normally flammable surfaces			DM GM	8,800 lm
		911401676007	BRP130 LED88/NW 70W 220-240V DM GM	Neutral white	4000 K
				DM GM	8,800 lm
		911401676107	BRP130 LED88/CW 70W 220-240V DM GM	Cool white	5700 K
				DM GM	8,800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401676507	BRP132 LED175/WW 140W 220-240V DM GM	140 W	911401676407	BRP131 LED125/CW 100W 220-240V DM GM	100 W
911401676607	BRP132 LED175/NW 140W 220-240V DM GM	140 W	911401675907	BRP130 LED88/WW 70W 220-240V DM GM	70 W
911401676707	BRP132 LED175/CW 140W 220-240V DM GM	140 W	911401676007	BRP130 LED88/NW 70W 220-240V DM GM	70 W
911401676207	BRP131 LED125/WW 100W 220-240V DM GM	100 W	911401676107	BRP130 LED88/CW 70W 220-240V DM GM	70 W
911401676307	BRP131 LED125/NW 100W 220-240V DM GM	100 W			

