



Make roads safer and sustainable.

GreenVision Xceed Gen2

Sustainability, citizen well-being and connectivity are key players in the game of differentiation among cities all over the world. And a way of achieving these goals is lighting. Lighting up streets and roads enhance the comfort, security and overall safety of our rapidly growing urban environments. Our GreenVision Xceed Gen2 makes an affordable LED road lighting solution that ensures sufficient light on your roads and streets. The GreenVision Xceed Gen2 family from Signify provides your city with a flexible lighting system which can be deployed anywhere in urban spaces, roadways and rural areas – our luminaires provide optimal light for all application areas. Additionally, the GreenVision Xceed Gen2 is ready to be connected to, and work with, smart city ecosystems. Our new GreenVision Xceed Gen2 range is enhanced to give city lighting departments even more control – to choose the right light

Benefits

- Robust & Reliable with a long service lifetime
- Elegant finless design
- Equipped with a Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation, and spare part information

Features

- System efficacy 140lm/W $\pm 10\%$
- Long service lifetime 100Khrs L70@Ta 35°C
- With 10kV or 15kV Surge protection Device

GreenVision Xceed Gen2

Application

- Pedestrian category roads (P1-P6)
- Vehicle category roads (M1-M6)
- Traffic routes and main access road
- Urban and residential area

Specifications

Material	Housing: die-cast aluminium Optic: polycarbonate Optic cover: glass
Light Source	3030 LED5050 LED High Power LED
Installation	Side entry 42-60mm Optional adjustable spigot
Luminous flux	System flux up to 55000lm
Correlated color temperature - CCT	5700K4000K3000K2700K2200K
Luminaire efficacy	4000K: 140lm/W Optional 4000K 160lm/W
Color Rendering index - 70 CRI	

Power	up to 390W
Mains Voltage	220-240V / 50-60Hz Optional 120-277V / 50-60Hz
Control system input	DALI / 1-10V / D4i
Dimming	PSR: 1-10V PSD: DALI PSC: Coded mains SPRD: 1-10V, Step dimming, AOCSSR: D4i
Operating Temperature range	-40 to +50C Ta
Ingress protection	IP66
Certification	IECEE CB, CE, CQC, RCM, D4i



Versions



BRP383


BRP382

Dimensional drawing



GreenVision Xceed Gen2

Dimensional drawing



General Information	
Driver included	Yes
Light source replaceable	No
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>70
Controls and Dimming	
Dimmable	Yes
Maximum dim level	10%
Mechanical and Housing	
Optical cover type	Polycarbonate micro lens optic
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
72468600	BRP383 LED386/NW 280W 220-240V DM PSR	740 neutral white	4000 K		38,600 lm
72398600	BRP381 LED145/NW 105W 220-240V DM PSR	740 neutral white	4000 K		14,500 lm
54603500	BRP381 LED133/NW 95W 220-240V DM PSR	740 neutral white	4000 K		13,300 lm
52041700	BRP381 LED99/NW 70W 220-240V DM PSR	740 neutral white	4000 K		9,900 lm
52033200	BRP381 LED127/WW 95W 220-240V DM PSR	730 warm white	3000 K		12,700 lm
72436500	BRP381 LED83/WW 60W 220-240V DM PSR	730 warm white	3000 K		8,300 lm
72385600	BRP381 LED75/NW 55W 220-240V DM PSR	740 neutral white	4000 K		7,500 lm
72374000	BRP381 LED71/WW 55W 220-240V DM PSR	730 warm white	3000 K		7,100 lm
72425900	BRP382 LED193/NW 140W 220-240V DM PSR	740 neutral white	4000 K		19,300 lm
72451800	BRP382 LED170/NW 120W 220-240V DM PSR	740 neutral white	4000 K		17,000 lm
72455600	BRP382 LED184/WW 140W 220-240V DM PSR	730 warm white	3000 K		18,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
72468600	BRP383 LED386/NW 280W 220-240V DM PSR	280 W
72398600	BRP381 LED145/NW 105W 220-240V DM PSR	105 W
54603500	BRP381 LED133/NW 95W 220-240V DM PSR	95 W
52041700	BRP381 LED99/NW 70W 220-240V DM PSR	70 W
52033200	BRP381 LED127/WW 95W 220-240V DM PSR	95 W
72436500	BRP381 LED83/WW 60W 220-240V DM PSR	60 W

Order Code	Full Product Name	Power Consumption
72385600	BRP381 LED75/NW 55W 220-240V DM PSR	55 W
72374000	BRP381 LED71/WW 55W 220-240V DM PSR	55 W
72425900	BRP382 LED193/NW 140W 220-240V DM PSR	140 W
72451800	BRP382 LED170/NW 120W 220-240V DM PSR	120 W
72455600	BRP382 LED184/WW 140W 220-240V DM PSR	140 W

