



# Make roads safer and sustainable.

## GreenVision Xceed Gen2

Sustainability, citizen well-being and connectivity are key players in the game of differentiation among cities all over the world. And a way of achieving these goals is lighting. Lighting up streets and roads enhance the comfort, security and overall safety of our rapidly growing urban environments. Our GreenVision Xceed Gen2 makes an affordable LED road lighting solution that ensures sufficient light on your roads and streets. The GreenVision Xceed Gen2 family from Signify provides your city with a flexible lighting system which can be deployed anywhere in urban spaces, roadways and rural areas – our luminaires provide optimal light for all application areas. Additionally, the GreenVision Xceed Gen2 is ready to be connected to, and work with, smart city ecosystems. Our new GreenVision Xceed Gen2 range is enhanced to give city lighting departments even more control – to choose the right light

### Benefits

- Robust & Reliable with a long service lifetime
- Elegant finless design
- Equipped with a Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation, and spare part information

### Features

- System efficacy 140lm/W  $\pm$ 10%
- Long service lifetime 100Khrs L70@Ta 35°C
- With 10kV or 15kV Surge protection Device

# GreenVision Xceed Gen2

## Application

- Pedestrian category roads (P1-P6)
- Vehicle category roads (M1-M6)
- Traffic routes and main access road
- Urban and residential area

## Specifications

<b>Material</b>	Housing: die-cast aluminium Optic: polycarbonate Optic cover: glass
<b>Light Source</b>	3030 LED5050 LED High Power LED
<b>Installation</b>	Side entry 42-60mm Optional adjustable spigot
<b>Luminous flux</b>	System flux up to 55000lm
<b>Correlated color temperature - CCT</b>	5700K4000K3000K2700K2200K
<b>Luminaire efficacy</b>	4000K: 140lm/W Optional 4000K 160lm/W
<b>Color Rendering index - 70 CRI</b>	

<b>Power</b>	up to 390W
<b>Mains Voltage</b>	220-240V / 50-60Hz Optional 120-277V / 50-60Hz
<b>Control system input</b>	DALI / 1-10V / D4i
<b>Dimming</b>	PSR: 1-10V PSD: DALI PSC: Coded mains SPRD: 1-10V, Step dimming, AOCSSR: D4i
<b>Operating Temperature range</b>	-40 to +50C Ta
<b>Ingress protection</b>	IP66
<b>Certification</b>	IECEE CB, CE, CQC, RCM, D4i



## Versions



BRP381

BRP382

## Dimensional drawing



# GreenVision Xceed Gen2

## General Information

Driver included	Yes
Light source replaceable	No
Service tag	Yes

## Light Technical

Color rendering index (CRI)	>70
-----------------------------	-----

## Controls and Dimming

Dimmable	Yes
Maximum dim level	10%

## Mechanical and Housing

Optical cover type	Polycarbonate micro lens optic
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP66

## Approval and Application

CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

## Light Technical

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401878298	BRP381 LED71/WW 55W 220-240V DM PSR	730 warm white	3000 K	7,100 lm
911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	740 neutral white	4000 K	19,300 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401878298	BRP381 LED71/WW 55W 220-240V DM PSR	55 W	911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	140 W

