

RoadFlair ECO

BRP490



LED road lighting easy transformer

RoadFlair ECO is a newly designed road lighting product, set to meet customers' requirements, including high lumen efficacy for energy saving and sustainability, aesthetic design for nice shape and appearance, quality material and components for product reliability and long lifetime, professional optic for lighting application fulfilment, dimming and system control interface for improving municipal operations and offering future-proof features. RoadFlair ECO's competitive price would help on the acceleration of road lighting LED transformation, to more sustainable society and smarter city.

Benefits

- High lumen efficacy for energy saving
- Robust quality and reliability
- Professional optic for various road applications
- Control interface for system compatibility
- Economical LED alternative to conventional street lights

Applications

- Pedestrian Road
- Residential Road

- Interchange
- Highway Road


Features

- Two housing types covering up to 18Klm
- Typical 150lm/W, high lumen efficacy for energy saving
- Robust quality and reliability, 100Khrs lifetime
- Professional optic for road applications
- 1-10V dimming interface for system compatibility


Versions



Road Flair Eco




Road Flair Eco




Road Flair Eco


Dimensional drawing



BRP490 LED48/NW 30W DW2n PSA GC



BRP490L LED157/NW 100W DW2n PSA SP1 GC



BRP490 LED73/WW 50W DW2n PSA SP1 P5 GC

General Information

Gear	-
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	70
-----------------------------	----

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing Color	RAL7040
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Polycarbonate bowl/cover UV-resistant

Approval and Application

Flammability mark	-
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
911401647509	BRP490 LED99/NW 70W DW2n PSA SP1 GC	9,900 lm	4000 K	740 neutral white
911401647709	BRP490 LED48/NW 30W DW2n PSA GC	4,800 lm	4000 K	740 neutral white
911401648409	BRP490 LED73/WW 50W DW2n PSA SP1 P5 GC	7,300 lm	3000 K	730 warm white
911401647309	BRP490L LED157/NW 100W DW2n PSA SP1 GC	15,700 lm	4000 K	740 neutral white

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401647509	BRP490 LED99/NW 70W DW2n PSA SP1 GC	70 W
911401647709	BRP490 LED48/NW 30W DW2n PSA GC	30 W
911401648409	BRP490 LED73/WW 50W DW2n PSA SP1 P5 GC	50 W
911401647309	BRP490L LED157/NW 100W DW2n PSA SP1 GC	100 W