



# Install smarter, finish sooner Choose long-lasting reliability and performance

## Coreline tempo small gen2

Coreline tempo small gen2 delivers on the Coreline promise of innovative, easy to use and high-quality floodlight. A limited range of options makes it easy to find the best lux-for-lux replacement for conventional technologies and direct replacement of 70W and 100W HID lamps. The CoreLine tempo small gen2 offers 2 lumen packages for different application areas as well as 2 high-performance asymmetrical and symmetrical optics. Installing this LED floodlight is made easy thanks to the U-shaped mounting bracket and the external quick 3-poles connector. It is an ideal flood lighting solution for outdoor environments such as industrial/commercial areas, parking lots, etc.

### Benefits

- Same light levels as your existing conventional solution while saving on energy
- Additional lumen pack for more light/ application covering
- Better energy savings thanks to availability of controls
- Reinforced reliability and durability
- Easy to install

# Coreline tempo small gen2


## Features

- Symmetric and Asymmetric optics available
- DALI, Dynnadimmer, Lumistep control options
- 3000K, 4000K
- IP66, IK08
- Long lifetime of 100KHrs
- 1m cable with waterproof connector
- Marine protection coating option

## Application

- Warehouses
- Offices
- Outdoor car parks
- Indoor sports facilities

## Dimensional drawing



## Product details



Front view



Side view

# Coreline tempo small gen2

General Information	
Driver included	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Grey
Mech. impact protection code	IK08
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Emergency Operation	
Central Emergency	No
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Product Data	
Product family code	BVP111

## General Information

Order Code	Full Product Name	Lamp family code
912300060466	BVP111 LED51-4S/740 OFA52	LED51
912300060467	BVP111 LED51-4S/740 S	LED51
912300060468	BVP111 LED49-4S/730 OFA52	LED49
912300060469	BVP111 LED73-4S/740 OFA52	LED73
912300060470	BVP111 LED49-4S/730 S	LED49
912300060601	BVP111 LED51-4S/840 PSU OFA52 ALU C1KC3	LED51
912300060609	BVP111 LED49-4S/830 PSU OFA52 ALU C1KC3	LED49

## Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
912300060466	BVP111 LED51-4S/740 OFA52	60° x 120°	740 neutral white	4000 K	70
912300060467	BVP111 LED51-4S/740 S	10° x 60°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
912300060468	BVP111 LED49-4S/730 OFA52	60° x 120°	730 warm white	3000 K	70
912300060469	BVP111 LED73-4S/740 OFA52	60° x 120°	740 neutral white	4000 K	70

# Coreline tempo small gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
912300060470	BVP111 LED49-4S/730 S	10° x 60°	730 warm white	3000 K	70
912300060601	BVP111 LED51-4S/840 PSU OFA52 ALU C1KC3	60° x 120°	840 neutral white	4000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
912300060609	BVP111 LED49-4S/830 PSU OFA52 ALU C1KC3	60° x 120°	830 warm white	3000 K	80

## Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
912300060466	BVP111 LED51-4S/740 OFA52	4,437 lm	Asymmetrical
912300060467	BVP111 LED51-4S/740 S	4,437 lm	Symmetrical
912300060468	BVP111 LED49-4S/730 OFA52	4,263 lm	Asymmetrical
912300060469	BVP111 LED73-4S/740 OFA52	6,278 lm	Asymmetrical
912300060470	BVP111 LED49-4S/730 S	4,263 lm	Symmetrical




Order Code	Full Product Name	Luminous Flux	Optic type outdoor
912300060601	BVP111 LED51-4S/840 PSU OFA52 ALU C1KC3	4,101 lm	Asymmetrical
912300060609	BVP111 LED49-4S/830 PSU OFA52 ALU C1KC3	3,903 lm	Asymmetrical

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300060466	BVP111 LED51-4S/740 OFA52	31 W
912300060467	BVP111 LED51-4S/740 S	31 W
912300060468	BVP111 LED49-4S/730 OFA52	31 W
912300060469	BVP111 LED73-4S/740 OFA52	43 W

Order Code	Full Product Name	Power Consumption
912300060470	BVP111 LED49-4S/730 S	31 W
912300060601	BVP111 LED51-4S/840 PSU OFA52 ALU C1KC3	33 W
912300060609	BVP111 LED49-4S/830 PSU OFA52 ALU C1KC3	36 W

## Polar Wide Diagrams




Polar Normal (separate) - BVP111 - 912300060466

Polar Normal (separate) - BVP111 - 912300060467


Polar Normal (separate) - BVP111 - 912300060470

# Coreline tempo small gen2


## Polar Wide Diagrams




**Polar Normal (separate) - BVP1111 - 912300060468**



**Polar Normal (separate) - BVP1111 - 912300060469**



**Polar Normal (separate) - BVP1111 - 912300060609**



**Polar Normal (separate) - BVP1111 - 912300060601**

